

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565082

Luminaire Tested: **SQ4-PW1-125U-125D-840-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565082
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-125D-840-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9918.4 lumens
Efficiency: N/A
Efficacy: 131.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565082
CATALOG NUMBER: SQ4-PW1-125U-125D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P565082

CATALOG NUMBER: SQ4-PW1-125U-125D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49				
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42				
2	89	82	76	70	82	75	70	66	64	60	57	53	50	48	43	41	40	35				
3	81	72	65	59	75	66	60	55	56	52	48	47	44	41	38	36	34	30				
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25				
5	68	57	49	43	63	53	45	40	45	39	35	38	33	30	31	28	25	22				
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19				
7	58	46	38	32	53	43	36	31	37	31	27	31	27	23	26	22	20	17				
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	15				
9	50	38	31	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17649	17649	17649
5°	17763	17623	17545
10°	17621	17479	17384
15°	17435	17241	17177
20°	17226	16961	16928
25°	16985	16677	16625
30°	16627	16375	16267
35°	16154	15926	15831
40°	15650	15407	15345
45°	15042	14843	14778
50°	14418	14297	14200
55°	13745	13745	13528
60°	12906	13155	12688
65°	11811	12400	11516
70°	10410	11411	10137
75°	8890	10213	8652
80°	6896	8597	6987
85°	4457	6606	5886



TEST NUMBER: P565082

CATALOG NUMBER: SQ4-PW1-125U-125D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.1	1.8
10°-20°	508.6	5.1
20°-30°	754.4	7.6
30°-40°	882.7	8.9
40°-50°	878.7	8.9
50°-60°	758.8	7.7
60°-70°	546.2	5.5
70°-80°	286.4	2.9
80°-90°	72.9	0.7
90°-100°	365.9	3.7
100°-110°	985.7	9.9
110°-120°	1034.5	10.4
120°-130°	839.4	8.5
130°-140°	658.3	6.6
140°-150°	505.4	5.1
150°-160°	363.4	3.7
160°-170°	222.0	2.2
170°-180°	74.9	0.8
0°-30°	1443.0	14.5
0°-40°	2325.7	23.4
0°-60°	3963.3	40.0
0°-90°	4868.7	49.1
90°-120°	2386.1	24.1
90°-150°	4389.3	44.3
90°-180°	5050.0	50.9
0°-180°	9918.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1913	1913	1913	1913	1913	
5°	1918	1896	1903	1898	1894	182
15°	1825	1802	1805	1802	1798	514
25°	1668	1640	1638	1628	1633	767
35°	1434	1414	1414	1401	1406	897
45°	1153	1143	1138	1134	1133	889
55°	854	853	854	843	841	762
65°	541	558	568	546	528	536
75°	249	272	286	267	243	267
85°	42	55	62	59	56	56
90°	2	6	12	13	13	5
95°	56	199	600	307	212	58
105°	182	284	1090	1631	1530	192
115°	322	394	908	1754	1984	317
125°	439	505	815	1378	1621	392
135°	529	590	792	1111	1258	408
145°	612	660	782	950	1020	384
155°	694	720	775	853	880	320
165°	753	762	778	809	813	212
175°	783	782	779	790	788	74
180°	782	782	782	782	782	

TEST NUMBER: P565082

CATALOG NUMBER: SQ4-PW1-125U-125D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1912.9	1912.9	1912.9	1912.9	1912.9
2.5°	1923.7	1907.9	1912.9	1908.6	1899.4
5°	1918.0	1896.5	1902.8	1897.7	1894.4
7.5°	1898.4	1878.6	1883.2	1877.8	1875.8
10°	1880.9	1861.1	1865.7	1858.9	1855.6
12.5°	1860.6	1839.6	1844.1	1837.3	1835.4
15°	1825.3	1802.2	1805.0	1801.6	1798.3
17.5°	1784.1	1760.7	1761.2	1755.8	1755.1
20°	1754.5	1729.8	1727.5	1720.8	1724.1
22.5°	1722.1	1696.1	1693.8	1684.5	1689.1
25°	1668.5	1640.5	1638.2	1628.2	1633.1
27.5°	1606.5	1578.8	1578.9	1564.8	1570.1
30°	1560.7	1534.3	1537.1	1520.4	1526.9
32.5°	1512.1	1488.4	1489.9	1473.2	1479.8
35°	1434.2	1414.5	1414.0	1400.7	1405.6
37.5°	1354.7	1337.2	1334.5	1326.8	1328.1
40°	1299.4	1284.6	1279.2	1274.1	1274.1
42.5°	1241.4	1227.9	1222.6	1218.8	1217.5
45°	1152.8	1142.9	1137.6	1134.2	1132.6
47.5°	1065.2	1055.9	1051.3	1048.9	1047.3
50°	1004.5	997.9	996.1	991.0	989.3
52.5°	943.8	939.9	938.1	931.6	930.0
55°	854.5	852.8	854.5	842.6	841.0
57.5°	761.5	764.1	769.5	753.6	749.7
60°	699.4	706.0	712.9	694.2	687.6
62.5°	636.1	646.6	656.3	634.8	625.6
65°	541.0	557.5	568.0	545.6	527.5
67.5°	449.3	469.8	482.4	458.3	437.9
70°	385.9	409.0	423.0	398.9	375.8
72.5°	330.7	356.4	367.7	345.0	321.9
75°	249.4	272.5	286.5	267.4	242.7
77.5°	177.0	198.7	210.3	193.7	173.3
80°	129.8	152.8	161.8	147.9	131.5
82.5°	92.0	111.1	117.3	109.0	97.8
85°	42.1	55.3	62.4	58.9	55.6
87.5°	11.2	21.2	28.0	28.2	29.6
90°	2.0	5.9	12.0	13.0	13.0
92.5°	24.3	85.9	169.8	81.7	56.8
95°	55.8	199.0	599.9	306.8	212.2
97.5°	89.1	227.8	940.8	786.0	592.7
100°	114.6	239.3	1049.3	1097.8	910.8
102.5°	139.3	255.4	1085.1	1331.4	1177.8
105°	182.3	283.7	1090.1	1630.9	1530.5
107.5°	223.0	313.4	1043.7	1784.8	1810.7
110°	250.1	335.8	1001.4	1832.6	1927.1



TEST NUMBER: P565082

CATALOG NUMBER: SQ4-PW1-125U-125D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	278.8	358.3	960.8	1822.0	1977.3
115°	321.9	394.0	907.8	1754.0	1983.9
117.5°	361.1	428.7	866.7	1645.4	1901.4
120°	386.6	451.9	846.0	1567.4	1830.5
122.5°	408.9	473.4	830.8	1487.7	1750.0
125°	439.4	504.7	815.1	1377.6	1621.2
127.5°	468.7	533.0	805.1	1280.6	1498.1
130°	486.3	550.6	801.1	1225.0	1416.0
132.5°	503.8	567.3	797.2	1176.0	1351.4
135°	529.1	590.5	792.2	1111.4	1258.5
137.5°	553.2	612.1	789.6	1056.6	1177.4
140°	570.0	626.5	787.2	1022.8	1132.0
142.5°	587.5	640.1	785.6	991.4	1083.3
145°	611.8	659.6	782.2	950.2	1020.4
147.5°	638.1	679.6	778.8	915.6	970.7
150°	655.7	691.7	777.2	893.9	939.6
152.5°	671.6	703.0	776.4	876.1	913.3
155°	694.5	719.9	775.2	852.6	879.9
157.5°	714.7	734.3	775.4	836.0	854.4
160°	727.4	744.0	776.2	826.4	840.0
162.5°	738.6	752.0	777.0	818.3	828.0
165°	753.3	762.1	778.2	809.2	813.1
167.5°	765.3	770.3	779.2	802.2	803.7
170°	773.2	775.2	779.2	798.2	798.2
172.5°	778.0	778.4	780.0	794.2	794.2
175°	783.2	782.2	779.2	790.1	788.2
177.5°	785.4	783.8	779.8	786.2	784.6
180°	782.2	782.2	782.2	782.2	782.2

(END OF REPORT)