

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519755

Luminaire Tested: **SQ4-125U-0D-935-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519755
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13031.6 lumens
Efficiency: N/A
Efficacy: 140.1 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 93
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519755
CATALOG NUMBER: SQ4-125U-0D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519755

CATALOG NUMBER: SQ4-125U-0D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	5081	54627	19326
100°	5237	47957	41627
105°	5592	33429	46934
110°	5804	23239	44720
115°	6044	17048	37258
120°	6137	13428	29056
125°	6080	11279	22433
130°	6004	9892	17483
135°	5939	8892	14126
140°	5905	8156	11728
145°	5928	7579	9886
150°	6009	7123	8612
155°	6082	6789	7705
160°	6144	6556	7095
165°	6190	6395	6681
170°	6232	6280	6432
175°	6240	6208	6280



TEST NUMBER: P519755

CATALOG NUMBER: SQ4-125U-0D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	944.3	7.2
100°-110°	2543.8	19.5
110°-120°	2669.6	20.5
120°-130°	2166.3	16.6
130°-140°	1699.0	13.0
140°-150°	1304.4	10.0
150°-160°	937.9	7.2
160°-170°	573.0	4.4
170°-180°	193.2	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	6157.8	47.3
90°-150°	11327.5	86.9
90°-180°	13032.0	100.0
0°-180°	13031.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	5	15	31	33	33	
95°	144	514	1548	792	548	160
105°	471	732	2813	4209	3950	495
115°	831	1017	2343	4526	5120	817
125°	1134	1302	2104	3555	4184	1013
135°	1366	1524	2044	2868	3248	1054
145°	1579	1702	2019	2452	2633	990
155°	1792	1858	2001	2200	2271	825
165°	1944	1967	2008	2088	2098	548
175°	2021	2019	2011	2039	2034	192
180°	2019	2019	2019	2019	2019	



TEST NUMBER: P519755

CATALOG NUMBER: SQ4-125U-0D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	5.1	15.2	30.9	33.4	33.4
92.5°	62.7	221.7	438.2	210.9	146.6
95°	144.0	513.6	1548.1	791.6	547.7
97.5°	229.9	587.9	2428.0	2028.4	1529.6
100°	295.7	617.6	2707.8	2833.2	2350.4
102.5°	359.5	659.2	2800.4	3435.8	3039.6
105°	470.6	732.1	2813.3	4208.9	3949.9
107.5°	575.5	808.8	2693.4	4606.1	4673.0
110°	645.5	866.7	2584.4	4729.5	4973.4
112.5°	719.5	924.7	2479.5	4702.2	5103.0
115°	830.6	1016.7	2342.7	4526.5	5119.9
117.5°	931.9	1106.4	2236.7	4246.2	4907.0
120°	997.8	1166.2	2183.2	4045.0	4723.9
122.5°	1055.4	1221.8	2144.2	3839.3	4516.1
125°	1134.0	1302.5	2103.5	3555.3	4183.9
127.5°	1209.7	1375.6	2077.8	3304.8	3866.1
130°	1254.9	1420.9	2067.5	3161.3	3654.2
132.5°	1300.2	1464.1	2057.2	3034.9	3487.5
135°	1365.5	1523.9	2044.4	2868.2	3247.9
137.5°	1427.7	1579.6	2037.7	2726.7	3038.5
140°	1470.9	1616.8	2031.5	2639.7	2921.3
142.5°	1516.2	1652.0	2027.4	2558.4	2795.8
145°	1578.9	1702.1	2018.7	2452.2	2633.3
147.5°	1646.8	1753.9	2009.9	2362.9	2505.2
150°	1692.1	1785.1	2005.8	2306.8	2425.0
152.5°	1733.2	1814.2	2003.7	2261.0	2357.1
155°	1792.4	1857.7	2000.7	2200.3	2270.7
157.5°	1844.3	1895.1	2001.2	2157.6	2204.8
160°	1877.2	1920.0	2003.2	2132.6	2167.8
162.5°	1906.0	1940.7	2005.3	2111.8	2137.0
165°	1944.1	1966.7	2008.4	2088.3	2098.4
167.5°	1974.9	1988.0	2010.9	2070.2	2074.2
170°	1995.5	2000.5	2010.9	2059.8	2059.8
172.5°	2007.9	2008.9	2013.0	2049.5	2049.5
175°	2021.2	2018.7	2010.9	2039.1	2034.1
177.5°	2026.9	2022.9	2012.5	2028.9	2024.8
180°	2018.7	2018.7	2018.7	2018.7	2018.7

(END OF REPORT)