

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518459

Luminaire Tested: **SQ4-BB-050U-100D-935-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518459
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-050U-100D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11563.1 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 134.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518459
CATALOG NUMBER: SQ4-BB-050U-100D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P518459

CATALOG NUMBER: SQ4-BB-050U-100D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55																				
1	101	97	94	91	94	91	88	86	78	77	75	67	66	65	57	56	55	50																				
2	94	87	82	78	87	82	77	74	71	68	65	61	59	57	52	51	50	45																				
3	87	79	72	67	81	74	68	64	65	61	57	56	53	51	48	46	45	41																				
4	80	71	64	59	75	67	61	56	59	54	51	52	48	46	45	42	40	37																				
5	75	65	57	52	70	61	55	50	54	49	45	47	44	41	41	39	37	34																				
6	70	59	52	46	65	56	49	45	49	44	41	44	40	37	38	36	33	31																				
7	65	54	47	42	61	51	45	40	46	41	37	41	37	34	36	33	31	28																				
8	61	50	43	38	57	47	41	36	42	37	34	38	34	31	33	30	28	26																				
9	57	46	39	34	53	44	37	33	39	34	31	35	31	28	31	28	26	24																				
10	54	42	36	31	50	40	34	30	36	32	28	33	29	26	29	26	24	22																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16416	16416	16416
5°	16152	16112	16232
10°	15113	15315	15742
15°	13739	14175	14965
20°	12196	12830	13954
25°	10621	11462	12821
30°	9097	10097	11748
35°	7543	8571	10452
40°	5796	6853	8906
45°	4190	5189	7166
50°	2854	3867	5683
55°	1856	2797	4417
60°	1064	1969	3193
65°	282	1203	1616
70°	139	371	464
75°	62	31	0
80°	46	0	0
85°	0	0	0



TEST NUMBER: P518459

CATALOG NUMBER: SQ4-BB-050U-100D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	487.2	4.2
10°-20°	1245.8	10.8
20°-30°	1559.6	13.5
30°-40°	1440.6	12.5
40°-50°	968.0	8.4
50°-60°	500.0	4.3
60°-70°	156.6	1.4
70°-80°	9.9	0.1
80°-90°	3.2	0.0
90°-100°	381.7	3.3
100°-110°	1037.0	9.0
110°-120°	1066.3	9.2
120°-130°	852.5	7.4
130°-140°	669.8	5.8
140°-150°	513.6	4.4
150°-160°	369.4	3.2
160°-170°	225.9	2.0
170°-180°	76.1	0.7
0°-30°	3292.6	28.5
0°-40°	4733.1	40.9
0°-60°	6201.1	53.6
0°-90°	6370.8	55.1
90°-120°	2485.0	21.5
90°-150°	4521.0	39.1
90°-180°	5192.0	44.9
0°-180°	11563.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5338	5338	5338	5338	5338	
5°	5232	5179	5219	5238	5258	485
15°	4315	4300	4452	4602	4700	1202
25°	3130	3155	3378	3609	3778	1435
35°	2009	2060	2283	2552	2784	1245
45°	963	1021	1193	1425	1648	757
55°	346	404	522	670	824	323
65°	39	74	165	199	222	65
75°	5	5	3	0	0	7
85°	0	0	0	0	0	1
90°	3	10	18	23	23	4
95°	56	209	665	289	194	60
105°	184	287	1140	1736	1634	196
115°	327	397	913	1816	2069	323
125°	450	512	826	1392	1642	401
135°	542	602	803	1134	1278	419
145°	626	672	793	963	1036	393
155°	708	733	788	865	890	327
165°	767	777	790	823	826	217
175°	795	798	793	803	800	76
180°	795	795	795	795	795	



TEST NUMBER: P518459

CATALOG NUMBER: SQ4-BB-050U-100D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5338.0	5338.0	5338.0	5338.0	5338.0
2.5°	5350.4	5299.9	5313.2	5312.9	5298.7
5°	5232.1	5179.1	5219.2	5237.7	5257.9
7.5°	5011.1	4969.6	5046.7	5104.5	5146.4
10°	4839.6	4804.2	4904.1	4982.9	5041.0
12.5°	4641.2	4614.0	4734.7	4842.8	4917.1
15°	4315.3	4300.2	4452.2	4601.6	4700.1
17.5°	3966.2	3965.7	4139.2	4324.7	4443.4
20°	3726.5	3734.1	3920.2	4124.8	4263.7
22.5°	3486.9	3504.5	3703.3	3916.6	4075.7
25°	3130.0	3155.2	3377.9	3609.0	3778.2
27.5°	2787.0	2823.9	3058.2	3298.4	3504.4
30°	2561.8	2604.8	2843.3	3096.1	3308.2
32.5°	2340.8	2391.8	2624.3	2891.6	3107.8
35°	2009.2	2059.7	2282.9	2551.6	2783.9
37.5°	1666.7	1716.2	1934.3	2198.8	2449.7
40°	1443.6	1499.2	1707.0	1963.3	2218.4
42.5°	1241.1	1296.7	1492.2	1744.0	1984.9
45°	963.3	1021.3	1193.1	1425.4	1647.6
47.5°	732.9	796.0	946.7	1156.9	1359.4
50°	596.6	659.7	808.3	993.5	1187.9
52.5°	487.1	548.2	682.3	856.8	1035.1
55°	346.1	404.1	521.7	669.8	823.8
57.5°	239.1	289.1	394.6	518.2	638.9
60°	173.0	221.0	320.2	420.6	519.1
62.5°	115.2	159.1	256.2	333.1	399.3
65°	38.7	74.1	165.3	199.4	222.1
67.5°	19.6	23.7	86.8	91.6	99.2
70°	15.5	15.5	41.3	44.1	51.6
72.5°	11.4	11.4	16.5	21.2	22.7
75°	5.2	5.2	2.6	0.0	0.0
77.5°	2.6	2.6	2.1	0.0	0.0
80°	2.6	2.6	0.0	0.0	0.0
82.5°	0.5	0.5	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.5	2.0	3.6	4.6	4.6
90°	2.6	10.1	17.9	23.0	23.0
92.5°	23.0	104.5	181.5	78.0	66.0
95°	56.3	208.8	664.8	289.3	194.3
97.5°	93.1	230.6	1019.2	792.9	556.9
100°	117.6	245.1	1127.6	1143.1	923.1
102.5°	142.2	259.7	1156.3	1413.7	1219.7
105°	184.1	286.6	1140.4	1736.4	1633.9
107.5°	227.6	318.1	1074.5	1903.1	1931.6
110°	258.3	340.8	1025.4	1935.9	2058.4



TEST NUMBER: P518459

CATALOG NUMBER: SQ4-BB-050U-100D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.9	363.4	976.3	1908.7	2093.2
115°	327.3	397.3	912.9	1816.1	2068.6
117.5°	367.2	434.2	872.5	1684.9	1969.4
120°	393.8	458.8	854.0	1596.9	1879.4
122.5°	416.3	481.3	841.8	1508.7	1781.2
125°	450.0	512.5	825.9	1391.6	1641.6
127.5°	480.2	542.2	817.2	1302.8	1517.3
130°	498.6	558.6	813.1	1247.1	1439.6
132.5°	517.0	577.0	809.0	1199.5	1370.0
135°	542.1	602.1	802.9	1133.5	1278.5
137.5°	569.2	623.7	799.8	1075.2	1197.2
140°	585.6	638.1	797.8	1038.1	1148.1
142.5°	601.9	650.4	795.7	1009.0	1101.0
145°	626.5	671.5	792.7	963.1	1035.6
147.5°	654.1	692.6	790.1	926.9	983.9
150°	672.5	705.0	790.1	906.2	951.2
152.5°	686.8	715.3	788.1	887.6	924.6
155°	708.3	733.3	787.6	864.8	889.8
157.5°	729.3	748.8	787.6	849.4	868.4
160°	741.5	759.0	787.6	839.0	854.0
162.5°	753.8	767.3	789.6	830.8	841.8
165°	767.1	777.1	790.1	823.4	825.9
167.5°	780.9	785.9	792.7	814.7	816.7
170°	785.0	790.0	792.7	810.6	810.6
172.5°	789.1	792.1	792.7	806.5	806.5
175°	795.2	797.7	792.7	802.8	800.3
177.5°	797.3	797.3	791.1	799.2	795.2
180°	795.2	795.2	795.2	795.2	795.2

(END OF REPORT)