

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519725

Luminaire Tested: **SQ4-100U-0D-840-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519725
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-100U-0D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6085.1 lumens
Efficiency: N/A
Efficacy: 161.8 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519725
CATALOG NUMBER: SQ4-100U-0D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519725

CATALOG NUMBER: SQ4-100U-0D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	4545	56155	15018
100°	4885	46759	38269
105°	5128	31657	45510
110°	5444	21586	43224
115°	5627	15615	35155
120°	5677	12369	27134
125°	5689	10429	20713
130°	5621	9162	16189
135°	5552	8224	13073
140°	5535	7544	10852
145°	5558	7009	9170
150°	5619	6598	7960
155°	5664	6284	7129
160°	5718	6071	6572
165°	5754	5925	6202
170°	5774	5821	5971
175°	5782	5754	5819



TEST NUMBER: P519725

CATALOG NUMBER: SQ4-100U-0D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	438.6	7.2
100°-110°	1210.8	19.9
110°-120°	1248.7	20.5
120°-130°	1003.5	16.5
130°-140°	788.6	13.0
140°-150°	604.8	9.9
150°-160°	434.7	7.1
160°-170°	265.8	4.4
170°-180°	89.6	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2898.1	47.6
90°-150°	5295.0	87.0
90°-180°	6085.0	100.0
0°-180°	6085.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	3	6	12	14	15	
95°	64	237	796	327	213	73
105°	216	333	1332	2034	1915	230
115°	387	467	1073	2124	2416	380
125°	530	604	972	1646	1932	472
135°	638	707	946	1333	1503	494
145°	740	792	934	1135	1221	463
155°	835	862	926	1018	1050	385
165°	904	915	930	967	974	255
175°	936	938	932	946	942	89
180°	936	936	936	936	936	



TEST NUMBER: P519725

CATALOG NUMBER: SQ4-100U-OD-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	3.0	5.9	12.0	13.5	15.0
92.5°	27.0	112.0	200.2	73.1	56.9
95°	64.4	237.3	795.7	327.1	212.8
97.5°	106.7	265.8	1178.7	907.5	657.2
100°	137.9	282.9	1320.1	1329.5	1080.4
102.5°	167.8	302.3	1347.7	1642.6	1406.4
105°	215.8	333.0	1332.1	2033.7	1915.0
107.5°	266.7	371.0	1257.8	2222.3	2265.7
110°	302.7	396.5	1200.3	2262.9	2403.5
112.5°	335.1	425.3	1146.3	2230.8	2438.3
115°	386.6	467.2	1072.9	2123.9	2415.5
117.5°	431.6	511.8	1024.6	1973.5	2305.2
120°	461.5	540.6	1005.5	1871.7	2205.7
122.5°	490.3	565.9	989.9	1776.6	2093.0
125°	530.5	603.7	972.5	1645.8	1931.5
127.5°	564.6	637.9	962.3	1535.2	1781.7
130°	587.4	660.7	957.5	1467.6	1691.8
132.5°	609.0	678.7	952.7	1410.8	1613.8
135°	638.3	707.2	945.5	1333.0	1502.9
137.5°	671.3	734.0	941.9	1267.7	1412.7
140°	689.3	750.8	939.5	1224.1	1351.6
142.5°	709.7	766.5	937.1	1185.4	1297.7
145°	740.2	791.5	933.5	1134.8	1221.2
147.5°	769.6	814.4	930.2	1092.1	1159.2
150°	791.2	827.8	929.0	1066.6	1120.8
152.5°	808.0	842.2	927.8	1044.8	1089.7
155°	834.6	862.5	926.0	1018.2	1050.4
157.5°	859.2	880.6	926.3	998.8	1020.7
160°	873.6	892.6	927.5	987.8	1004.0
162.5°	885.6	902.3	928.7	978.2	990.8
165°	903.6	915.3	930.5	966.7	974.0
167.5°	917.4	924.4	932.0	959.7	962.0
170°	924.5	930.4	932.0	956.0	956.0
172.5°	930.5	934.1	932.0	951.2	950.0
175°	936.5	938.0	932.0	945.5	942.5
177.5°	938.9	937.8	931.7	940.1	937.7
180°	936.5	936.5	936.5	936.5	936.5

(END OF REPORT)