

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936369

Luminaire Tested: SQ4-FB-025U-075D-935-1D-UNV-STD-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936369
REPORT IS A COMBINATION OF REPORTS P933430 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-075D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8623.9 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 90
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936369
CATALOG NUMBER: SQ4-FB-025U-075D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P936369

CATALOG NUMBER: SQ4-FB-025U-075D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	102	97	93	89	96	92	88	85	82	79	77	74	71	69	66	64	62	58
2	92	84	77	71	87	79	73	68	71	66	62	64	60	57	57	54	51	48
3	83	73	65	58	79	69	62	56	62	56	51	56	51	47	50	46	43	39
4	76	64	55	49	71	61	53	47	55	48	43	49	44	39	44	40	36	33
5	69	57	48	41	65	54	46	40	49	42	37	44	38	34	39	34	31	28
6	64	51	42	35	60	48	40	34	43	37	32	39	33	29	35	30	27	24
7	59	45	37	31	55	43	35	30	39	32	27	35	30	25	32	27	23	21
8	54	41	33	27	51	39	31	26	36	29	24	32	26	22	29	24	21	18
9	51	37	29	24	48	36	28	23	32	26	21	29	24	20	26	22	18	16
10	47	34	26	21	45	33	25	21	30	23	19	27	22	18	24	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2459	2459	2459
5°	2403	2843	3305
10°	2180	4145	5479
15°	1854	5416	6616
20°	1510	6278	6743
25°	1260	6571	6606
30°	1063	6615	6593
35°	940	6506	6764
40°	820	6366	6940
45°	743	6263	6967
50°	682	6171	6852
55°	654	6035	6548
60°	670	5773	6069
65°	698	5373	5410
70°	745	4689	4570
75°	830	3827	3567
80°	913	2657	2403
85°	830	1412	1230

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 6967 cd/sqm



TEST NUMBER: P936369

CATALOG NUMBER: SQ4-FB-025U-075D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.8	1.2
10°-20°	455.7	5.3
20°-30°	797.2	9.2
30°-40°	1026.2	11.9
40°-50°	1146.2	13.3
50°-60°	1097.8	12.7
60°-70°	870.0	10.1
70°-80°	511.6	5.9
80°-90°	143.6	1.7
90°-100°	185.9	2.2
100°-110°	488.8	5.7
110°-120°	506.9	5.9
120°-130°	406.6	4.7
130°-140°	319.0	3.7
140°-150°	244.9	2.8
150°-160°	176.3	2.0
160°-170°	107.9	1.3
170°-180°	36.5	0.4
0°-30°	1355.7	15.7
0°-40°	2381.9	27.6
0°-60°	4626.0	53.6
0°-90°	6151.2	71.3
90°-120°	1181.6	13.7
90°-150°	2152.0	25.0
90°-180°	2473.0	28.7
0°-180°	8623.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	795	795	795	795	795	
5°	774	831	936	1058	1097	71
15°	580	1071	1805	2188	2257	161
25°	371	1214	2150	2244	2247	171
35°	250	1160	2024	2140	2224	156
45°	171	925	1789	2050	2142	132
55°	123	588	1518	1764	1812	112
65°	97	312	1127	1268	1286	96
75°	72	192	619	680	682	75
85°	26	59	153	169	171	27
90°	3	7	19	10	10	4
95°	24	96	320	165	112	27
105°	88	133	540	820	765	93
115°	156	190	433	864	986	154
125°	218	244	394	665	785	193
135°	259	285	381	537	609	201
145°	301	320	377	458	494	188
155°	340	349	377	414	426	156
165°	367	372	377	391	396	104
175°	381	381	379	384	384	36
180°	381	381	381	381	381	



TEST NUMBER: P936369

CATALOG NUMBER: SQ4-FB-025U-075D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9	794.9
2.5°	794.9	794.9	800.0	802.6	807.7	810.3	815.4	820.5	835.8	838.4	843.5
5°	774.5	784.7	817.9	830.7	866.5	915.0	935.5	968.8	1037.8	1058.3	1071.0
7.5°	743.8	766.8	848.6	869.0	958.5	1086.4	1140.1	1211.6	1321.5	1375.2	1418.7
10°	695.2	743.8	889.5	938.1	1083.8	1278.1	1377.8	1477.5	1643.6	1717.7	1745.8
12.5°	641.6	720.8	932.9	999.5	1209.1	1492.8	1612.9	1722.8	1912.0	2011.7	2027.0
15°	580.2	687.6	973.9	1071.0	1342.0	1671.7	1804.6	1940.1	2116.5	2188.0	2205.9
17.5°	526.5	662.0	1012.3	1114.5	1444.2	1832.7	1968.2	2080.7	2223.8	2272.4	2285.1
20°	460.1	621.1	1037.8	1170.7	1551.6	1950.3	2080.7	2167.6	2264.7	2295.4	2300.5
22.5°	411.5	577.7	1053.2	1191.2	1623.1	2021.9	2131.8	2200.8	2267.3	2277.5	2280.0
25°	370.6	529.1	1050.6	1214.2	1684.5	2065.3	2149.7	2200.8	2239.1	2244.3	2244.3
27.5°	332.3	475.4	1040.4	1219.3	1730.5	2075.6	2142.0	2177.8	2195.7	2205.9	2205.9
30°	299.1	424.3	1014.8	1209.1	1750.9	2065.3	2119.0	2136.9	2154.8	2170.1	2177.8
32.5°	273.5	375.7	976.5	1188.6	1753.5	2039.8	2078.1	2088.3	2113.9	2149.7	2162.5
35°	250.5	327.2	932.9	1160.5	1738.2	1998.9	2024.4	2034.7	2085.8	2139.5	2157.3
37.5°	227.5	291.4	876.7	1111.9	1715.2	1950.3	1968.2	1986.1	2065.3	2129.2	2149.7
40°	204.5	260.7	810.3	1058.3	1679.4	1891.5	1906.9	1935.0	2039.8	2113.9	2134.3
42.5°	186.6	235.2	738.7	1002.0	1633.4	1825.1	1848.1	1889.0	2009.1	2088.3	2111.3
45°	171.3	209.6	662.0	925.3	1574.6	1756.1	1789.3	1845.5	1973.3	2050.0	2070.4
47.5°	155.9	191.7	582.8	846.0	1510.7	1687.0	1730.5	1794.4	1924.8	1998.9	2016.8
50°	143.1	173.8	503.5	761.7	1441.7	1612.9	1664.0	1730.5	1863.4	1932.4	1955.4
52.5°	132.9	158.5	429.4	677.3	1362.4	1536.2	1595.0	1664.0	1789.3	1855.7	1871.1
55°	122.7	145.7	365.5	587.9	1280.6	1454.4	1518.3	1584.8	1707.5	1763.7	1773.9
57.5°	117.6	135.5	311.8	503.5	1193.7	1362.4	1434.0	1495.3	1610.4	1653.8	1664.0
60°	109.9	127.8	270.9	432.0	1099.2	1275.5	1336.9	1398.2	1495.3	1531.1	1538.8
62.5°	102.2	122.7	240.3	363.0	1002.0	1173.3	1234.6	1290.9	1372.7	1398.2	1408.4
65°	97.1	117.6	217.3	311.8	902.3	1065.9	1127.3	1175.8	1242.3	1267.9	1273.0
67.5°	92.0	112.5	199.4	268.4	802.6	958.5	1004.6	1050.6	1101.7	1127.3	1129.8
70°	84.3	107.4	184.0	237.7	700.3	835.8	874.2	922.7	963.6	976.5	984.1
72.5°	79.2	99.7	173.8	214.7	595.5	718.2	754.0	782.1	817.9	830.7	830.7
75°	71.6	89.5	163.6	191.7	488.2	587.9	618.6	646.7	674.8	679.9	672.2
77.5°	63.9	79.2	140.6	161.0	380.8	465.2	490.8	506.1	529.1	534.2	536.8
80°	53.7	69.0	109.9	125.2	276.0	342.5	360.4	373.2	393.6	393.6	398.7
82.5°	40.9	53.7	79.2	89.5	186.6	235.2	250.5	258.2	270.9	270.9	270.9
85°	25.6	33.2	51.1	58.8	112.5	143.1	153.4	155.9	166.1	168.7	168.7
87.5°	12.8	17.9	33.2	35.8	58.8	74.1	74.1	79.2	79.2	76.7	74.1
90°	2.6	4.6	6.6	7.2	11.2	16.7	19.4	17.3	13.0	9.7	9.7
92.5°	10.2	27.6	45.1	49.4	69.4	96.2	109.6	96.0	68.9	48.6	46.7
95°	24.5	56.4	88.3	96.3	170.9	270.5	320.3	285.8	216.8	165.1	159.2
97.5°	42.5	70.6	98.7	105.7	230.2	396.3	479.2	457.4	413.9	381.2	370.0
100°	56.3	81.8	107.3	113.7	251.9	436.1	528.2	529.8	532.9	535.3	522.0
102.5°	68.1	91.8	115.6	121.6	261.7	448.6	542.0	569.7	625.2	666.9	655.4
105°	88.1	108.2	128.3	133.3	269.1	449.9	540.4	602.6	727.1	820.5	814.3
107.5°	108.5	127.3	146.1	150.8	270.4	429.9	509.7	596.5	770.1	900.4	901.8
110°	122.3	139.3	156.3	160.5	268.4	412.2	484.1	581.1	775.2	920.8	927.2



TEST NUMBER: P936369

CATALOG NUMBER: SQ4-FB-025U-075D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	136.0	152.1	168.3	172.3	268.5	396.7	460.8	560.2	758.8	907.8	917.6
115°	156.4	171.3	186.2	190.0	270.9	378.9	432.9	528.6	719.9	863.5	877.0
117.5°	176.6	190.2	203.7	207.1	276.0	367.8	413.7	500.1	672.8	802.3	817.4
120°	188.4	201.2	213.9	217.1	280.1	364.0	406.0	484.9	642.7	761.1	775.7
122.5°	200.0	212.8	225.6	228.8	285.9	362.0	400.1	471.2	613.3	719.9	734.3
125°	217.6	229.4	241.1	244.0	293.9	360.5	393.7	454.0	574.8	665.3	678.6
127.5°	231.9	243.8	255.6	258.6	301.9	359.5	388.3	440.1	543.8	621.5	632.8
130°	239.6	252.4	265.1	268.3	307.7	360.1	386.3	432.5	524.7	593.9	604.3
132.5°	247.6	260.3	273.1	276.2	312.3	360.5	384.5	425.8	508.5	570.4	579.7
135°	259.3	270.9	282.5	285.4	317.5	360.1	381.4	416.0	485.2	537.1	545.1
137.5°	271.4	282.9	294.3	297.2	325.1	362.4	380.9	410.2	468.6	512.5	519.0
140°	281.3	291.9	302.5	305.2	329.8	362.7	379.1	404.4	454.9	492.8	498.9
142.5°	289.0	298.8	308.6	311.1	333.7	364.0	379.1	401.3	445.7	479.0	484.3
145°	300.8	309.4	317.9	320.0	338.8	364.0	376.6	394.7	431.0	458.2	462.2
147.5°	312.6	320.9	329.2	331.3	346.3	366.5	376.6	390.9	419.4	440.8	444.1
150°	320.3	327.8	335.3	337.1	350.3	367.8	376.6	388.7	412.8	430.9	433.5
152.5°	328.2	333.9	339.5	341.0	352.8	368.7	376.6	386.9	407.5	422.9	425.0
155°	339.9	344.1	348.4	349.4	358.4	370.5	376.6	384.8	401.2	413.5	414.8
157.5°	348.6	352.7	356.9	357.9	364.1	372.4	376.6	383.0	395.7	405.2	406.1
160°	354.6	357.8	361.0	361.8	366.7	373.3	376.6	382.0	392.9	401.1	401.6
162.5°	360.5	362.9	365.3	365.8	369.4	374.2	376.6	381.2	390.4	397.3	397.8
165°	366.9	369.0	371.2	371.7	373.3	375.5	376.6	379.9	386.5	391.4	391.9
167.5°	372.8	373.8	374.8	375.1	376.4	378.2	379.1	381.3	385.6	388.9	389.1
170°	376.6	377.6	378.6	378.9	379.0	379.1	379.1	381.3	385.6	388.9	388.9
172.5°	378.6	378.9	379.1	379.1	379.1	379.1	379.1	380.8	384.3	386.8	386.6
175°	381.4	381.4	381.4	381.4	380.7	379.7	379.1	380.2	382.4	384.0	384.0
177.5°	381.4	381.4	381.4	381.4	380.8	380.1	379.7	380.5	382.2	383.5	383.2
180°	381.4	381.4	381.4	381.4	381.4	381.4	381.4	381.4	381.4	381.4	381.4



TEST NUMBER: P936369

CATALOG NUMBER: SQ4-FB-025U-075D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	794.9	794.9
2.5°	848.6	843.5
5°	1091.5	1096.6
7.5°	1469.8	1467.2
10°	1827.6	1850.6
12.5°	2088.3	2093.4
15°	2246.8	2257.0
17.5°	2308.2	2310.7
20°	2310.7	2305.6
22.5°	2282.6	2277.5
25°	2249.4	2246.8
27.5°	2218.7	2221.2
30°	2205.9	2213.6
32.5°	2205.9	2218.7
35°	2211.0	2223.8
37.5°	2208.5	2223.8
40°	2198.2	2216.1
42.5°	2170.1	2182.9
45°	2126.7	2142.0
47.5°	2070.4	2080.7
50°	1998.9	2009.1
52.5°	1909.4	1912.0
55°	1802.1	1812.3
57.5°	1687.0	1689.6
60°	1559.2	1566.9
62.5°	1423.8	1423.8
65°	1280.6	1285.8
67.5°	1132.4	1145.2
70°	981.6	984.1
72.5°	833.3	833.3
75°	679.9	682.5
77.5°	534.2	534.2
80°	396.2	398.7
82.5°	273.5	278.6
85°	171.3	171.3
87.5°	79.2	71.6
90°	9.7	9.7
92.5°	39.0	31.3
95°	135.8	112.4
97.5°	325.5	280.8
100°	468.9	415.8
102.5°	609.9	564.4
105°	789.9	765.4
107.5°	907.8	913.7
110°	952.7	978.2



TEST NUMBER: P936369

CATALOG NUMBER: SQ4-FB-025U-075D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	956.7	995.8
115°	931.3	985.6
117.5°	877.6	937.7
120°	834.2	892.6
122.5°	792.0	849.7
125°	731.7	784.9
127.5°	677.6	722.4
130°	645.7	687.1
132.5°	616.8	653.8
135°	577.1	609.0
137.5°	545.2	571.4
140°	523.4	547.8
142.5°	505.3	526.4
145°	478.1	494.1
147.5°	457.4	470.6
150°	444.2	454.9
152.5°	433.0	441.1
155°	420.1	425.5
157.5°	410.0	413.7
160°	403.8	406.0
162.5°	399.8	401.9
165°	394.1	396.3
167.5°	390.0	390.9
170°	388.9	388.9
172.5°	385.8	385.0
175°	384.0	384.0
177.5°	382.4	381.4
180°	381.4	381.4



TEST NUMBER: P936369
 CATALOG NUMBER: SQ4-FB-025U-075D-935-1D-UNV-STD-W-12

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.88	7.03	6.62	7.80	8.73	19.07	20.22	19.81	20.99	21.92
	3H	6.60	7.64	7.36	8.42	9.38	20.93	21.98	21.69	22.75	23.71
	4H	6.91	7.90	7.69	8.69	9.66	21.60	22.58	22.37	23.37	24.34
	6H	7.18	8.09	7.96	8.89	9.87	22.05	22.96	22.83	23.75	24.74
	8H	7.26	8.13	8.05	8.94	9.93	22.18	23.05	22.97	23.86	24.85
	12H	7.28	8.11	8.09	8.92	9.94	22.26	23.09	23.06	23.90	24.91
4H	2H	13.13	14.12	13.91	14.91	15.88	19.38	20.36	20.15	21.15	22.12
	3H	14.73	15.55	15.52	16.38	17.36	21.45	22.28	22.24	23.10	24.09
	4H	14.83	15.59	15.64	16.41	17.42	22.24	22.99	23.04	23.81	24.83
	6H	14.86	15.52	15.68	16.36	17.38	22.80	23.45	23.62	24.30	25.32
	8H	14.85	15.46	15.67	16.30	17.33	22.97	23.58	23.80	24.43	25.46
	12H	14.82	15.37	15.66	16.23	17.27	23.08	23.63	23.93	24.50	25.54
8H	4H	16.31	16.92	17.13	17.76	18.80	22.32	22.93	23.15	23.78	24.81
	6H	16.56	17.07	17.42	17.96	18.99	22.97	23.48	23.82	24.36	25.40
	8H	16.59	17.04	17.45	17.92	18.97	23.20	23.65	24.06	24.53	25.58
	12H	16.57	16.97	17.44	17.84	18.94	23.36	23.76	24.23	24.63	25.73
12H	4H	16.47	17.02	17.31	17.88	18.92	22.29	22.84	23.14	23.71	24.74
	6H	16.83	17.28	17.69	18.16	19.21	22.96	23.41	23.82	24.29	25.34
	8H	16.91	17.31	17.78	18.18	19.29	23.20	23.60	24.07	24.47	25.58