

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936219

Luminaire Tested: SQ4-FB-025U-050D-840-1D-UNV-STD-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936219
REPORT IS A COMBINATION OF REPORTS P933445 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-050D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3825.5 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936219
CATALOG NUMBER: SQ4-FB-025U-050D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P936219

CATALOG NUMBER: SQ4-FB-025U-050D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	68	68	68	63
1	100	95	91	87	93	89	86	82	78	75	73	68	66	64	59	57	56	59	57	56	51
2	90	82	76	70	84	77	71	66	68	63	59	59	55	52	51	48	46	51	48	46	42
3	82	72	64	57	76	67	60	55	59	53	49	51	47	43	44	41	38	44	41	38	34
4	75	63	54	48	69	59	52	46	52	46	41	45	40	37	39	35	32	39	35	32	29
5	68	56	47	41	63	52	45	39	46	40	35	40	35	31	35	31	28	35	31	28	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	24	31	27	24	21
7	58	45	36	30	54	42	34	29	37	31	26	33	27	23	28	24	21	28	24	21	18
8	53	40	32	26	50	38	31	25	34	27	23	30	24	21	26	22	18	26	22	18	16
9	50	37	29	23	46	35	27	22	31	25	20	27	22	18	24	19	16	24	19	16	14
10	46	34	26	21	43	32	25	20	28	22	18	25	20	16	22	18	15	22	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1912	1912	1912
5°	1867	2209	2570
10°	1693	3220	4261
15°	1438	4205	5145
20°	1171	4872	5243
25°	976	5097	5137
30°	823	5128	5127
35°	727	5041	5259
40°	633	4930	5396
45°	573	4847	5418
50°	525	4772	5328
55°	502	4664	5092
60°	515	4458	4719
65°	533	4144	4206
70°	567	3611	3554
75°	628	2942	2774
80°	677	2037	1868
85°	596	1081	957

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 5418 cd/sqm



TEST NUMBER: P936219

CATALOG NUMBER: SQ4-FB-025U-050D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.0	1.0
10°-20°	177.2	4.6
20°-30°	309.9	8.1
30°-40°	399.0	10.4
40°-50°	445.6	11.6
50°-60°	426.8	11.2
60°-70°	338.3	8.8
70°-80°	198.9	5.2
80°-90°	56.1	1.5
90°-100°	107.8	2.8
100°-110°	283.4	7.4
110°-120°	293.9	7.7
120°-130°	235.7	6.2
130°-140°	185.0	4.8
140°-150°	142.0	3.7
150°-160°	102.2	2.7
160°-170°	62.6	1.6
170°-180°	21.1	0.6
0°-30°	527.1	13.8
0°-40°	926.1	24.2
0°-60°	1798.5	47.0
0°-90°	2391.8	62.5
90°-120°	685.1	17.9
90°-150°	1247.8	32.6
90°-180°	1434.0	37.5
0°-180°	3825.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	309	309	309	309	309	
5°	301	323	364	411	426	28
15°	226	416	702	851	878	63
25°	144	472	836	872	874	66
35°	97	451	787	832	865	61
45°	67	360	696	797	833	52
55°	48	228	590	686	705	43
65°	38	121	438	493	500	37
75°	28	74	240	264	265	29
85°	10	23	60	66	67	11
90°	2	4	11	6	6	2
95°	14	56	186	96	65	16
105°	51	77	313	476	444	54
115°	91	110	251	501	572	90
125°	126	142	228	386	455	112
135°	150	166	221	311	353	116
145°	174	186	218	266	286	109
155°	197	203	218	240	247	91
165°	213	216	218	227	230	60
175°	221	221	220	223	223	21
180°	221	221	221	221	221	



TEST NUMBER: P936219

CATALOG NUMBER: SQ4-FB-025U-050D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	309.0	309.0	309.0	309.0	309.0	309.0	309.0	309.0	309.0	309.0	309.0
2.5°	309.0	309.0	311.0	312.0	314.1	315.1	317.0	319.0	325.0	325.9	327.9
5°	301.1	305.1	318.0	323.0	336.9	355.8	363.7	376.6	403.5	411.4	416.4
7.5°	289.2	298.2	329.9	337.9	372.7	422.4	443.2	471.1	513.8	534.7	551.6
10°	270.3	289.2	345.8	364.8	421.4	496.9	535.7	574.4	639.0	667.8	678.8
12.5°	249.5	280.3	362.7	388.6	470.1	580.4	627.1	669.9	743.4	782.1	788.0
15°	225.6	267.4	378.6	416.4	521.8	649.9	701.6	754.3	822.9	850.7	857.7
17.5°	204.7	257.4	393.5	433.3	561.5	712.5	765.2	809.0	864.6	883.5	888.4
20°	178.9	241.5	403.5	455.2	603.3	758.3	809.0	842.8	880.5	892.5	894.4
22.5°	160.0	224.6	409.4	463.1	631.0	786.1	828.8	855.6	881.5	885.4	886.4
25°	144.1	205.7	408.4	472.1	654.9	802.9	835.7	855.6	870.5	872.5	872.5
27.5°	129.2	184.9	404.5	474.0	672.8	807.0	832.8	846.7	853.6	857.7	857.7
30°	116.3	165.0	394.5	470.1	680.7	802.9	823.9	830.8	837.7	843.8	846.7
32.5°	106.3	146.1	379.6	462.1	681.7	793.1	808.0	811.9	821.8	835.7	840.8
35°	97.4	127.3	362.7	451.2	675.8	777.2	787.0	791.1	811.0	831.8	838.7
37.5°	88.4	113.3	340.9	432.3	666.8	758.3	765.2	772.2	802.9	827.8	835.7
40°	79.5	101.4	315.1	411.4	653.0	735.4	741.4	752.3	793.1	821.8	829.8
42.5°	72.5	91.4	287.2	389.6	635.0	709.6	718.5	734.4	781.1	811.9	820.8
45°	66.6	81.5	257.4	359.7	612.2	682.7	695.7	717.5	767.2	797.0	804.9
47.5°	60.7	74.5	226.5	328.9	587.4	655.9	672.8	697.6	748.3	777.2	784.1
50°	55.6	67.6	195.8	296.1	560.5	627.1	646.9	672.8	724.5	751.3	760.3
52.5°	51.7	61.7	167.0	263.4	529.7	597.2	620.2	646.9	695.7	721.5	727.5
55°	47.7	56.6	142.1	228.5	497.9	565.4	590.3	616.1	663.8	685.7	689.7
57.5°	45.7	52.7	121.2	195.8	464.1	529.7	557.5	581.3	626.1	643.0	646.9
60°	42.8	49.7	105.3	168.0	427.3	495.9	519.8	543.6	581.3	595.3	598.2
62.5°	39.7	47.7	93.5	141.1	389.6	456.2	480.0	501.9	533.6	543.6	547.5
65°	37.7	45.7	84.5	121.2	350.8	414.4	438.3	457.1	482.9	492.9	494.9
67.5°	35.8	43.8	77.6	104.3	312.0	372.7	390.6	408.4	428.3	438.3	439.3
70°	32.8	41.7	71.5	92.4	272.3	325.0	339.9	358.7	374.6	379.6	382.7
72.5°	30.8	38.7	67.6	83.5	231.6	279.2	293.1	304.1	318.0	323.0	323.0
75°	27.9	34.8	63.6	74.5	189.8	228.5	240.5	251.4	262.3	264.4	261.3
77.5°	24.8	30.8	54.6	62.6	148.1	180.9	190.8	196.8	205.7	207.7	208.7
80°	20.8	26.9	42.8	48.7	107.3	133.2	140.1	145.1	153.0	153.0	155.0
82.5°	15.9	20.8	30.8	34.8	72.5	91.4	97.4	100.4	105.3	105.3	105.3
85°	10.0	12.9	19.9	22.8	43.8	55.6	59.7	60.7	64.6	65.6	65.6
87.5°	4.9	6.9	12.9	13.9	22.8	28.8	28.8	30.8	30.8	29.8	28.8
90°	1.5	2.7	3.9	4.1	6.5	9.7	11.3	10.0	7.5	5.6	5.6
92.5°	5.9	16.0	26.1	28.7	40.3	55.8	63.5	55.6	39.9	28.2	27.1
95°	14.2	32.7	51.2	55.8	99.1	156.8	185.6	165.7	125.7	95.7	92.4
97.5°	24.6	40.9	57.2	61.3	133.5	229.7	277.8	265.2	240.0	221.0	214.6
100°	32.7	47.4	62.2	65.9	146.0	252.8	306.2	307.1	308.9	310.3	302.6
102.5°	39.5	53.4	67.1	70.5	151.8	260.0	314.2	330.3	362.5	386.7	380.1
105°	51.1	62.7	74.4	77.4	156.0	260.8	313.3	349.4	421.6	475.7	472.2
107.5°	62.9	73.8	84.7	87.4	156.8	249.3	295.5	345.9	446.6	522.1	522.9
110°	70.9	80.8	90.6	93.1	155.6	239.0	280.7	337.0	449.5	533.9	537.6



TEST NUMBER: P936219

CATALOG NUMBER: SQ4-FB-025U-050D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	78.8	88.2	97.5	99.9	155.6	230.0	267.2	324.8	440.0	526.3	531.9
115°	90.7	99.4	108.0	110.2	157.1	219.6	251.0	306.5	417.4	500.6	508.5
117.5°	102.5	110.3	118.1	120.0	160.0	213.2	239.9	290.0	390.1	465.2	473.8
120°	109.3	116.7	124.0	125.9	162.4	211.1	235.4	281.2	372.7	441.3	449.8
122.5°	115.9	123.4	130.8	132.7	165.8	210.0	232.0	273.2	355.6	417.4	425.8
125°	126.2	133.0	139.8	141.5	170.4	209.1	228.3	263.3	333.4	385.8	393.5
127.5°	134.5	141.3	148.2	149.9	175.0	208.5	225.2	255.2	315.4	360.4	366.9
130°	138.9	146.3	153.6	155.5	178.3	208.8	224.0	250.8	304.2	344.3	350.3
132.5°	143.6	151.0	158.3	160.2	181.1	209.1	223.0	246.9	294.8	330.7	336.0
135°	150.4	157.1	163.8	165.5	184.1	208.9	221.2	241.3	281.4	311.4	316.1
137.5°	157.4	164.0	170.6	172.3	188.5	210.1	220.9	237.9	271.8	297.2	300.9
140°	163.1	169.2	175.4	177.0	191.3	210.3	219.8	234.5	263.8	285.7	289.3
142.5°	167.6	173.2	178.9	180.3	193.5	211.0	219.8	232.7	258.5	277.7	280.8
145°	174.4	179.3	184.3	185.5	196.5	211.0	218.3	228.8	249.9	265.7	267.9
147.5°	181.2	186.0	190.9	192.1	200.9	212.5	218.3	226.6	243.1	255.6	257.5
150°	185.6	190.0	194.4	195.5	203.1	213.3	218.3	225.4	239.3	249.8	251.3
152.5°	190.3	193.5	196.9	197.7	204.6	213.8	218.3	224.3	236.2	245.2	246.4
155°	197.1	199.6	202.0	202.6	207.9	214.9	218.3	223.1	232.6	239.7	240.5
157.5°	202.1	204.5	206.9	207.5	211.1	216.0	218.3	222.0	229.4	234.9	235.5
160°	205.6	207.5	209.3	209.8	212.6	216.5	218.3	221.5	227.8	232.6	232.9
162.5°	209.0	210.3	211.7	212.1	214.2	217.0	218.3	221.0	226.4	230.4	230.7
165°	212.7	213.9	215.2	215.5	216.5	217.8	218.3	220.2	224.1	226.9	227.2
167.5°	216.1	216.7	217.3	217.5	218.2	219.3	219.8	221.1	223.6	225.5	225.6
170°	218.3	218.9	219.5	219.6	219.7	219.8	219.8	221.1	223.6	225.5	225.5
172.5°	219.5	219.6	219.8	219.8	219.8	219.8	219.8	220.8	222.8	224.3	224.2
175°	221.2	221.2	221.2	221.2	220.7	220.1	219.8	220.4	221.7	222.7	222.7
177.5°	221.2	221.2	221.2	221.2	220.8	220.3	220.1	220.6	221.6	222.4	222.3
180°	221.2	221.2	221.2	221.2	221.2	221.2	221.2	221.2	221.2	221.2	221.2



TEST NUMBER: P936219

CATALOG NUMBER: SQ4-FB-025U-050D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	309.0	309.0
2.5°	329.9	327.9
5°	424.3	426.3
7.5°	571.5	570.5
10°	710.6	719.5
12.5°	811.9	813.9
15°	873.6	877.5
17.5°	897.4	898.4
20°	898.4	896.4
22.5°	887.4	885.4
25°	874.6	873.6
27.5°	862.6	863.6
30°	857.7	860.6
32.5°	857.7	862.6
35°	859.7	864.6
37.5°	858.7	864.6
40°	854.6	861.6
42.5°	843.8	848.7
45°	826.9	832.8
47.5°	804.9	809.0
50°	777.2	781.1
52.5°	742.4	743.4
55°	700.6	704.6
57.5°	655.9	656.9
60°	606.2	609.2
62.5°	553.6	553.6
65°	497.9	499.8
67.5°	440.3	445.2
70°	381.7	382.7
72.5°	324.0	324.0
75°	264.4	265.4
77.5°	207.7	207.7
80°	154.0	155.0
82.5°	106.3	108.3
85°	66.6	66.6
87.5°	30.8	27.9
90°	5.6	5.6
92.5°	22.5	18.1
95°	78.7	65.2
97.5°	188.7	162.8
100°	271.9	241.1
102.5°	353.7	327.3
105°	458.0	443.8
107.5°	526.3	529.8
110°	552.4	567.2



TEST NUMBER: P936219

CATALOG NUMBER: SQ4-FB-025U-050D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	554.7	577.4
115°	539.9	571.5
117.5°	508.8	543.7
120°	483.7	517.6
122.5°	459.2	492.6
125°	424.2	455.1
127.5°	392.9	418.9
130°	374.4	398.4
132.5°	357.6	379.1
135°	334.5	353.1
137.5°	316.2	331.3
140°	303.4	317.6
142.5°	292.9	305.2
145°	277.2	286.5
147.5°	265.2	272.8
150°	257.6	263.8
152.5°	251.1	255.8
155°	243.5	246.7
157.5°	237.7	239.9
160°	234.2	235.4
162.5°	231.9	233.1
165°	228.5	229.8
167.5°	226.2	226.6
170°	225.5	225.5
172.5°	223.7	223.3
175°	222.7	222.7
177.5°	221.7	221.2
180°	221.2	221.2



TEST NUMBER: P936219
 CATALOG NUMBER: SQ4-FB-025U-050D-840-1D-UNV-STD-W-6

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.32	5.35	5.15	6.22	7.29	17.48	18.52	18.31	19.38	20.46
	3H	5.04	5.97	5.88	6.84	7.94	19.33	20.26	20.18	21.14	22.24
	4H	5.34	6.23	6.20	7.10	8.22	19.98	20.86	20.84	21.74	22.86
	6H	5.60	6.42	6.48	7.30	8.43	20.42	21.23	21.29	22.12	23.25
	8H	5.67	6.45	6.56	7.36	8.49	20.54	21.32	21.42	22.22	23.35
	12H	5.70	6.44	6.59	7.34	8.49	20.61	21.35	21.50	22.25	23.41
4H	2H	11.55	12.43	12.41	13.31	14.42	17.78	18.66	18.64	19.54	20.65
	3H	13.13	13.87	14.01	14.78	15.91	19.84	20.58	20.71	21.49	22.62
	4H	13.23	13.91	14.12	14.82	15.97	20.61	21.28	21.50	22.19	23.35
	6H	13.25	13.84	14.16	14.77	15.93	21.15	21.74	22.06	22.67	23.83
	8H	13.24	13.79	14.14	14.71	15.88	21.32	21.87	22.22	22.79	23.96
	12H	13.20	13.70	14.13	14.64	15.82	21.42	21.91	22.34	22.85	24.03
8H	4H	14.69	15.24	15.60	16.16	17.33	20.68	21.23	21.59	22.16	23.33
	6H	14.94	15.40	15.88	16.36	17.53	21.32	21.77	22.25	22.74	23.91
	8H	14.96	15.36	15.91	16.32	17.51	21.54	21.94	22.48	22.90	24.08
	12H	14.94	15.29	15.89	16.24	17.48	21.69	22.04	22.64	22.99	24.23
12H	4H	14.84	15.34	15.77	16.28	17.46	20.64	21.14	21.57	22.08	23.26
	6H	15.20	15.60	16.14	16.56	17.75	21.30	21.71	22.25	22.66	23.85
	8H	15.28	15.63	16.23	16.58	17.82	21.54	21.89	22.49	22.84	24.08