

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936619

Luminaire Tested: SQ4-FB-050U-050D-840-1D-UNV-STD-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936619
REPORT IS A COMBINATION OF REPORTS P933477 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-050D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5343.1 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 42.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936619
CATALOG NUMBER: SQ4-FB-050U-050D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P936619

CATALOG NUMBER: SQ4-FB-050U-050D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45	45	45	45
1	96	92	88	84	88	84	81	77	70	67	65	57	55	53	45	43	42	37	37	37	37
2	87	79	73	68	79	73	67	63	60	56	53	49	46	44	39	37	35	30	30	30	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25	25	25	25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	24	21	21	21	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	26	23	21	18	18	18	18
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	21	18	15	15	15	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	21	18	16	13	13	13	13
8	51	39	31	26	47	36	29	24	30	25	21	25	20	17	20	16	14	12	12	12	12
9	48	35	28	23	44	33	26	21	27	22	18	23	18	15	18	15	12	10	10	10	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	13	11	9	9	9	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1912	1912	1912
5°	1867	2209	2570
10°	1693	3220	4261
15°	1438	4205	5145
20°	1171	4872	5243
25°	976	5097	5137
30°	823	5128	5127
35°	727	5041	5259
40°	633	4930	5396
45°	573	4847	5418
50°	525	4772	5328
55°	502	4664	5092
60°	515	4458	4719
65°	533	4144	4206
70°	567	3611	3554
75°	628	2942	2774
80°	677	2037	1868
85°	596	1081	957

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 5418 cd/sqm



TEST NUMBER: P936619

CATALOG NUMBER: SQ4-FB-050U-050D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.0	0.7
10°-20°	177.2	3.3
20°-30°	309.9	5.8
30°-40°	399.0	7.5
40°-50°	445.6	8.3
50°-60°	426.8	8.0
60°-70°	338.3	6.3
70°-80°	198.9	3.7
80°-90°	57.0	1.1
90°-100°	221.9	4.2
100°-110°	583.3	10.9
110°-120°	604.8	11.3
120°-130°	485.1	9.1
130°-140°	380.6	7.1
140°-150°	292.2	5.5
150°-160°	210.4	3.9
160°-170°	128.7	2.4
170°-180°	43.5	0.8
0°-30°	527.1	9.9
0°-40°	926.1	17.3
0°-60°	1798.5	33.7
0°-90°	2392.7	44.8
90°-120°	1409.9	26.4
90°-150°	2567.8	48.1
90°-180°	2950.0	55.2
0°-180°	5343.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	309	309	309	309	309	
5°	301	323	364	411	426	28
15°	226	416	702	851	878	63
25°	144	472	836	872	874	66
35°	97	451	787	832	865	61
45°	67	360	696	797	833	52
55°	48	228	590	686	705	43
65°	38	121	438	493	500	37
75°	28	74	240	264	265	29
85°	10	23	60	66	67	11
90°	3	9	23	12	12	3
95°	29	115	382	197	134	33
105°	105	159	645	979	913	111
115°	187	227	516	1030	1176	184
125°	260	291	470	794	936	231
135°	309	341	455	641	727	239
145°	359	382	449	547	590	225
155°	406	417	449	493	508	186
165°	438	444	449	467	473	124
175°	455	455	452	458	458	43
180°	455	455	455	455	455	



TEST NUMBER: P936619

CATALOG NUMBER: SQ4-FB-050U-050D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	309.0	309.0	309.0	309.0	309.0	309.0	309.0	309.0	309.0	309.0	309.0
2.5°	309.0	309.0	311.0	312.0	314.1	315.1	317.0	319.0	325.0	325.9	327.9
5°	301.1	305.1	318.0	323.0	336.9	355.8	363.7	376.6	403.5	411.4	416.4
7.5°	289.2	298.2	329.9	337.9	372.7	422.4	443.2	471.1	513.8	534.7	551.6
10°	270.3	289.2	345.8	364.8	421.4	496.9	535.7	574.4	639.0	667.8	678.8
12.5°	249.5	280.3	362.7	388.6	470.1	580.4	627.1	669.9	743.4	782.1	788.0
15°	225.6	267.4	378.6	416.4	521.8	649.9	701.6	754.3	822.9	850.7	857.7
17.5°	204.7	257.4	393.5	433.3	561.5	712.5	765.2	809.0	864.6	883.5	888.4
20°	178.9	241.5	403.5	455.2	603.3	758.3	809.0	842.8	880.5	892.5	894.4
22.5°	160.0	224.6	409.4	463.1	631.0	786.1	828.8	855.6	881.5	885.4	886.4
25°	144.1	205.7	408.4	472.1	654.9	802.9	835.7	855.6	870.5	872.5	872.5
27.5°	129.2	184.9	404.5	474.0	672.8	807.0	832.8	846.7	853.6	857.7	857.7
30°	116.3	165.0	394.5	470.1	680.7	802.9	823.9	830.8	837.7	843.8	846.7
32.5°	106.3	146.1	379.6	462.1	681.7	793.1	808.0	811.9	821.8	835.7	840.8
35°	97.4	127.3	362.7	451.2	675.8	777.2	787.0	791.1	811.0	831.8	838.7
37.5°	88.4	113.3	340.9	432.3	666.8	758.3	765.2	772.2	802.9	827.8	835.7
40°	79.5	101.4	315.1	411.4	653.0	735.4	741.4	752.3	793.1	821.8	829.8
42.5°	72.5	91.4	287.2	389.6	635.0	709.6	718.5	734.4	781.1	811.9	820.8
45°	66.6	81.5	257.4	359.7	612.2	682.7	695.7	717.5	767.2	797.0	804.9
47.5°	60.7	74.5	226.5	328.9	587.4	655.9	672.8	697.6	748.3	777.2	784.1
50°	55.6	67.6	195.8	296.1	560.5	627.1	646.9	672.8	724.5	751.3	760.3
52.5°	51.7	61.7	167.0	263.4	529.7	597.2	620.2	646.9	695.7	721.5	727.5
55°	47.7	56.6	142.1	228.5	497.9	565.4	590.3	616.1	663.8	685.7	689.7
57.5°	45.7	52.7	121.2	195.8	464.1	529.7	557.5	581.3	626.1	643.0	646.9
60°	42.8	49.7	105.3	168.0	427.3	495.9	519.8	543.6	581.3	595.3	598.2
62.5°	39.7	47.7	93.5	141.1	389.6	456.2	480.0	501.9	533.6	543.6	547.5
65°	37.7	45.7	84.5	121.2	350.8	414.4	438.3	457.1	482.9	492.9	494.9
67.5°	35.8	43.8	77.6	104.3	312.0	372.7	390.6	408.4	428.3	438.3	439.3
70°	32.8	41.7	71.5	92.4	272.3	325.0	339.9	358.7	374.6	379.6	382.7
72.5°	30.8	38.7	67.6	83.5	231.6	279.2	293.1	304.1	318.0	323.0	323.0
75°	27.9	34.8	63.6	74.5	189.8	228.5	240.5	251.4	262.3	264.4	261.3
77.5°	24.8	30.8	54.6	62.6	148.1	180.9	190.8	196.8	205.7	207.7	208.7
80°	20.8	26.9	42.8	48.7	107.3	133.2	140.1	145.1	153.0	153.0	155.0
82.5°	15.9	20.8	30.8	34.8	72.5	91.4	97.4	100.4	105.3	105.3	105.3
85°	10.0	12.9	19.9	22.8	43.8	55.6	59.7	60.7	64.6	65.6	65.6
87.5°	4.9	6.9	12.9	13.9	22.8	28.8	28.8	30.8	30.8	29.8	28.8
90°	3.1	5.5	8.0	8.6	13.4	20.0	23.2	20.6	15.4	11.6	11.6
92.5°	12.3	33.0	53.7	59.0	82.9	114.8	130.7	114.5	82.2	58.0	55.7
95°	29.3	67.3	105.3	114.8	203.9	322.8	382.2	341.1	258.8	197.0	190.0
97.5°	50.7	84.3	117.8	126.2	274.8	472.9	571.9	545.9	493.8	454.8	441.4
100°	67.2	97.6	128.0	135.7	300.5	520.3	630.1	632.0	635.9	638.7	622.9
102.5°	81.2	109.7	138.0	145.1	312.3	535.2	646.6	679.7	746.0	795.7	782.2
105°	105.1	129.1	153.1	159.2	321.0	536.9	644.8	719.1	867.6	979.0	971.7
107.5°	129.5	152.0	174.3	179.9	322.7	513.0	608.1	711.7	918.8	1074.3	1076.0
110°	146.0	166.2	186.4	191.5	320.2	491.8	577.6	693.4	925.1	1098.8	1106.4



TEST NUMBER: P936619

CATALOG NUMBER: SQ4-FB-050U-050D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	162.2	181.5	200.8	205.6	320.3	473.4	549.8	668.4	905.4	1083.1	1094.8
115°	186.6	204.4	222.2	226.6	323.3	452.1	516.5	630.7	859.1	1030.3	1046.5
117.5°	210.7	226.9	243.0	247.1	329.3	438.9	493.6	596.7	802.8	957.3	975.3
120°	224.8	240.0	255.2	259.1	334.1	434.3	484.4	578.6	766.9	908.1	925.6
122.5°	238.6	253.9	269.2	273.1	341.2	432.0	477.4	562.2	731.8	859.0	876.2
125°	259.6	273.6	287.6	291.1	350.6	430.1	469.8	541.8	685.9	793.9	809.7
127.5°	276.7	290.9	305.0	308.6	360.1	429.0	463.4	525.2	648.8	741.6	754.9
130°	285.9	301.1	316.4	320.1	367.0	429.6	460.9	515.9	626.1	708.7	721.0
132.5°	295.4	310.6	325.8	329.6	372.7	430.1	458.8	508.1	606.6	680.5	691.6
135°	309.4	323.3	337.1	340.6	378.8	429.7	455.2	496.5	579.0	640.8	650.4
137.5°	323.8	337.5	351.1	354.6	387.9	432.2	454.5	489.4	559.1	611.5	619.3
140°	335.7	348.4	360.9	364.1	393.5	432.7	452.4	482.5	542.8	588.0	595.3
142.5°	344.8	356.5	368.1	371.1	398.2	434.3	452.4	478.9	531.7	571.5	577.8
145°	358.9	369.1	379.3	381.9	404.4	434.3	449.3	471.0	514.3	546.8	551.5
147.5°	373.0	382.8	392.8	395.3	413.3	437.3	449.3	466.3	500.4	526.0	530.0
150°	382.2	391.1	400.0	402.3	418.0	438.9	449.3	463.8	492.5	514.1	517.2
152.5°	391.5	398.4	405.2	406.9	421.0	439.9	449.3	461.6	486.2	504.6	506.9
155°	405.7	410.7	415.7	416.9	427.7	442.1	449.3	459.1	478.7	493.3	494.9
157.5°	416.0	420.9	425.8	427.0	434.4	444.4	449.3	457.0	472.2	483.5	484.6
160°	423.1	426.8	430.6	431.6	437.5	445.4	449.3	455.9	468.9	478.7	479.3
162.5°	430.1	432.9	435.8	436.5	440.7	446.5	449.3	454.9	465.8	474.0	474.6
165°	437.7	440.3	442.8	443.5	445.5	448.1	449.3	453.3	461.1	467.0	467.7
167.5°	444.7	445.9	447.2	447.5	449.1	451.3	452.4	455.0	460.1	464.0	464.3
170°	449.3	450.5	451.8	452.1	452.2	452.3	452.4	455.0	460.1	464.0	464.0
172.5°	451.8	452.1	452.3	452.4	452.4	452.4	452.4	454.4	458.4	461.5	461.3
175°	455.2	455.2	455.2	455.2	454.3	453.0	452.4	453.7	456.3	458.1	458.1
177.5°	455.2	455.2	455.2	455.2	454.5	453.5	453.0	454.0	456.1	457.5	457.2
180°	455.2	455.2	455.2	455.2	455.2	455.2	455.2	455.2	455.2	455.2	455.2



TEST NUMBER: P936619

CATALOG NUMBER: SQ4-FB-050U-050D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	309.0	309.0
2.5°	329.9	327.9
5°	424.3	426.3
7.5°	571.5	570.5
10°	710.6	719.5
12.5°	811.9	813.9
15°	873.6	877.5
17.5°	897.4	898.4
20°	898.4	896.4
22.5°	887.4	885.4
25°	874.6	873.6
27.5°	862.6	863.6
30°	857.7	860.6
32.5°	857.7	862.6
35°	859.7	864.6
37.5°	858.7	864.6
40°	854.6	861.6
42.5°	843.8	848.7
45°	826.9	832.8
47.5°	804.9	809.0
50°	777.2	781.1
52.5°	742.4	743.4
55°	700.6	704.6
57.5°	655.9	656.9
60°	606.2	609.2
62.5°	553.6	553.6
65°	497.9	499.8
67.5°	440.3	445.2
70°	381.7	382.7
72.5°	324.0	324.0
75°	264.4	265.4
77.5°	207.7	207.7
80°	154.0	155.0
82.5°	106.3	108.3
85°	66.6	66.6
87.5°	30.8	27.9
90°	11.6	11.6
92.5°	46.4	37.2
95°	162.0	134.1
97.5°	388.3	335.1
100°	559.5	496.1
102.5°	727.9	673.5
105°	942.6	913.3
107.5°	1083.0	1090.2
110°	1136.7	1167.1



TEST NUMBER: P936619

CATALOG NUMBER: SQ4-FB-050U-050D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1141.5	1188.2
115°	1111.2	1176.0
117.5°	1047.1	1118.9
120°	995.3	1065.2
122.5°	945.0	1013.8
125°	873.1	936.5
127.5°	808.5	862.0
130°	770.4	819.8
132.5°	735.9	780.1
135°	688.5	726.7
137.5°	650.6	681.8
140°	624.4	653.7
142.5°	602.9	628.0
145°	570.6	589.5
147.5°	545.7	561.4
150°	530.1	542.8
152.5°	516.6	526.3
155°	501.3	507.6
157.5°	489.2	493.6
160°	481.8	484.4
162.5°	477.1	479.6
165°	470.3	472.9
167.5°	465.3	466.4
170°	464.0	464.0
172.5°	460.3	459.4
175°	458.1	458.1
177.5°	456.3	455.2
180°	455.2	455.2



TEST NUMBER: P936619
 CATALOG NUMBER: SQ4-FB-050U-050D-840-1D-UNV-STD-W-6

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.75	3.60	3.75	4.61	5.95	15.92	16.77	16.91	17.78	19.12
	3H	3.46	4.22	4.46	5.24	6.60	17.76	18.52	18.76	19.54	20.90
	4H	3.76	4.48	4.77	5.50	6.87	18.40	19.12	19.41	20.14	21.51
	6H	4.01	4.68	5.04	5.70	7.08	18.82	19.49	19.85	20.52	21.90
	8H	4.08	4.71	5.11	5.75	7.13	18.94	19.58	19.97	20.62	22.00
	12H	4.09	4.70	5.13	5.74	7.14	19.01	19.61	20.04	20.65	22.05
4H	2H	9.96	10.69	10.98	11.71	13.08	16.19	16.92	17.22	17.94	19.31
	3H	11.53	12.14	12.56	13.19	14.57	18.23	18.84	19.27	19.89	21.27
	4H	11.62	12.18	12.66	13.22	14.63	19.00	19.55	20.04	20.59	22.00
	6H	11.63	12.11	12.68	13.18	14.58	19.53	20.01	20.58	21.08	22.48
	8H	11.61	12.06	12.66	13.12	14.53	19.69	20.14	20.74	21.20	22.61
	12H	11.57	11.97	12.64	13.04	14.47	19.78	20.19	20.85	21.26	22.68
8H	4H	13.06	13.51	14.11	14.57	15.99	19.06	19.50	20.11	20.56	21.98
	6H	13.31	13.68	14.38	14.78	16.19	19.68	20.05	20.76	21.15	22.57
	8H	13.32	13.65	14.41	14.73	16.17	19.90	20.22	20.98	21.31	22.74
	12H	13.29	13.58	14.38	14.66	16.13	20.04	20.33	21.13	21.41	22.88
12H	4H	13.21	13.61	14.27	14.68	16.11	19.01	19.41	20.08	20.49	21.91
	6H	13.56	13.89	14.64	14.97	16.41	19.66	19.99	20.75	21.07	22.51
	8H	13.63	13.92	14.72	15.00	16.47	19.89	20.18	20.98	21.26	22.73