

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937319

Luminaire Tested: SQ4-FB-075U-125D-840-1D-UNV-STD-W-6

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P937319  
REPORT IS A COMBINATION OF REPORTS P933512 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-075U-125D-840-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10473.8 lumens  
Efficiency: N/A  
Efficacy: 112.6 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 93  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P937319  
CATALOG NUMBER: SQ4-FB-075U-125D-840-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P937319

CATALOG NUMBER: SQ4-FB-075U-125D-840-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58			58
1	99	94	90	86	92	88	84	81	76	73	71	65	63	61	55	53	52	47			47
2	89	82	75	69	83	76	70	65	66	61	57	56	53	50	47	45	43	38			38
3	81	71	63	57	75	66	59	54	57	52	47	49	45	41	41	38	36	32			32
4	74	62	54	48	68	58	51	45	50	45	40	43	39	35	36	33	30	27			27
5	68	55	47	40	63	52	44	38	45	39	34	38	34	30	33	29	26	23			23
6	62	49	41	35	57	46	38	33	40	34	29	34	29	26	29	25	22	19			19
7	57	44	36	30	53	41	34	28	36	30	25	31	26	22	26	22	19	17			17
8	53	40	32	26	49	37	30	25	33	27	22	28	23	20	24	20	17	15			15
9	49	36	28	23	46	34	27	22	30	24	20	26	21	17	22	18	15	13			13
10	46	33	26	21	43	31	24	20	27	22	18	24	19	16	20	16	14	12			12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4825	4825	4825
5°	4712	5575	6485
10°	4272	8125	10752
15°	3630	10613	12983
20°	2954	12295	13231
25°	2463	12863	12962
30°	2076	12941	12938
35°	1835	12723	13273
40°	1598	12440	13618
45°	1447	12232	13672
50°	1325	12044	13445
55°	1267	11770	12849
60°	1296	11249	11908
65°	1347	10457	10615
70°	1432	9113	8968
75°	1580	7424	6998
80°	1715	5142	4715
85°	1496	2724	2415

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 13672 cd/sqm



TEST NUMBER: P937319

CATALOG NUMBER: SQ4-FB-075U-125D-840-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.9	1.0
10°-20°	447.1	4.3
20°-30°	782.1	7.5
30°-40°	1006.8	9.6
40°-50°	1124.6	10.7
50°-60°	1077.1	10.3
60°-70°	853.6	8.1
70°-80°	501.9	4.8
80°-90°	142.1	1.4
90°-100°	333.7	3.2
100°-110°	877.2	8.4
110°-120°	909.6	8.7
120°-130°	729.6	7.0
130°-140°	572.5	5.5
140°-150°	439.4	4.2
150°-160°	316.4	3.0
160°-170°	193.6	1.8
170°-180°	65.4	0.6
0°-30°	1330.2	12.7
0°-40°	2337.0	22.3
0°-60°	4538.7	43.3
0°-90°	6036.3	57.6
90°-120°	2120.5	20.2
90°-150°	3862.0	36.9
90°-180°	4437.0	42.4
0°-180°	10473.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	780	780	780	780	780	
5°	760	815	918	1038	1076	70
15°	569	1051	1771	2147	2214	158
25°	364	1191	2109	2202	2204	168
35°	246	1139	1986	2099	2182	153
45°	168	908	1756	2011	2102	130
55°	120	577	1490	1730	1778	110
65°	95	306	1106	1244	1262	94
75°	70	188	607	667	670	74
85°	25	58	150	166	168	27
90°	4	13	35	18	18	5
95°	44	173	575	296	202	49
105°	158	239	970	1472	1374	168
115°	281	341	777	1550	1769	277
125°	390	438	707	1194	1409	347
135°	465	512	684	964	1093	360
145°	540	574	676	822	887	338
155°	610	627	676	742	764	280
165°	658	667	676	702	711	186
175°	684	684	680	689	689	65
180°	684	684	684	684	684	



TEST NUMBER: P937319

CATALOG NUMBER: SQ4-FB-075U-125D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	779.9	779.9	779.9	779.9	779.9	779.9	779.9	779.9	779.9	779.9	779.9
2.5°	779.9	779.9	785.0	787.4	792.5	795.0	800.0	805.0	820.0	822.6	827.6
5°	759.9	769.9	802.6	815.1	850.2	897.8	917.9	950.5	1018.2	1038.3	1050.8
7.5°	729.8	752.4	832.6	852.6	940.5	1065.9	1118.5	1188.8	1296.6	1349.2	1391.9
10°	682.1	729.8	872.7	920.4	1063.4	1254.0	1351.8	1449.6	1612.6	1685.3	1712.9
12.5°	629.5	707.2	915.4	980.6	1186.2	1464.6	1582.5	1690.3	1875.9	1973.7	1988.7
15°	569.3	674.6	955.5	1050.8	1316.6	1640.2	1770.6	1903.5	2076.6	2146.7	2164.3
17.5°	516.6	649.5	993.1	1093.4	1417.0	1798.2	1931.0	2041.4	2181.9	2229.5	2242.1
20°	451.4	609.4	1018.2	1148.6	1522.3	1913.6	2041.4	2126.7	2222.0	2252.0	2257.1
22.5°	403.8	566.8	1033.3	1168.7	1592.6	1983.7	2091.6	2159.3	2224.5	2234.6	2237.0
25°	363.7	519.1	1030.8	1191.2	1652.7	2026.4	2109.2	2159.3	2196.9	2202.0	2202.0
27.5°	326.0	466.4	1020.7	1196.3	1697.9	2036.4	2101.6	2136.7	2154.2	2164.3	2164.3
30°	293.4	416.3	995.6	1186.2	1717.9	2026.4	2079.0	2096.6	2114.1	2129.2	2136.7
32.5°	268.3	368.6	958.0	1166.1	1720.4	2001.3	2038.9	2048.9	2074.0	2109.2	2121.6
35°	245.8	321.0	915.4	1138.6	1705.4	1961.2	1986.3	1996.3	2046.4	2099.1	2116.7
37.5°	223.2	285.9	860.3	1090.9	1682.8	1913.6	1931.0	1948.6	2026.4	2089.0	2109.2
40°	200.7	255.8	795.0	1038.3	1647.7	1855.9	1870.9	1898.4	2001.3	2074.0	2094.1
42.5°	183.1	230.7	724.8	983.1	1602.5	1790.7	1813.2	1853.3	1971.2	2048.9	2071.5
45°	168.1	205.6	649.5	907.9	1544.8	1722.9	1755.5	1810.7	1936.1	2011.4	2031.4
47.5°	152.9	188.1	571.8	830.1	1482.2	1655.2	1697.9	1760.5	1888.5	1961.2	1978.8
50°	140.4	170.5	494.1	747.3	1414.4	1582.5	1632.7	1697.9	1828.3	1896.0	1918.5
52.5°	130.4	155.5	421.3	664.6	1336.7	1507.2	1564.9	1632.7	1755.5	1820.7	1835.8
55°	120.3	143.0	358.6	576.8	1256.4	1427.0	1489.7	1554.9	1675.3	1730.5	1740.5
57.5°	115.4	132.9	306.0	494.1	1171.2	1336.7	1406.9	1467.1	1580.0	1622.6	1632.7
60°	107.8	125.4	265.9	423.9	1078.4	1251.4	1311.7	1371.8	1467.1	1502.3	1509.8
62.5°	100.3	120.3	235.7	356.1	983.1	1151.1	1211.3	1266.5	1346.7	1371.8	1381.8
65°	95.3	115.4	213.2	306.0	885.2	1045.8	1106.0	1153.6	1218.8	1243.9	1248.9
67.5°	90.3	110.4	195.6	263.3	787.4	940.5	985.6	1030.8	1080.9	1106.0	1108.5
70°	82.8	105.3	180.6	233.3	687.2	820.0	857.7	905.3	945.5	958.0	965.6
72.5°	77.8	97.8	170.5	210.6	584.3	704.7	739.8	767.4	802.6	815.1	815.1
75°	70.2	87.7	160.6	188.1	479.0	576.8	606.9	634.5	662.1	667.1	659.6
77.5°	62.7	77.8	137.9	158.0	373.7	456.5	481.6	496.6	519.1	524.1	526.7
80°	52.7	67.7	107.8	122.9	270.8	336.0	353.6	366.2	386.2	386.2	391.2
82.5°	40.1	52.7	77.8	87.7	183.1	230.7	245.8	253.3	265.9	265.9	265.9
85°	25.1	32.6	50.2	57.7	110.4	140.4	150.5	152.9	163.0	165.5	165.5
87.5°	12.5	17.6	32.6	35.1	57.7	72.7	72.7	77.8	77.8	75.3	72.7
90°	4.5	8.2	12.0	12.8	20.2	29.9	34.9	31.0	23.3	17.5	17.5
92.5°	18.4	49.6	80.8	88.6	124.6	172.6	196.6	172.3	123.7	87.2	83.8
95°	44.1	101.3	158.4	172.7	306.7	485.4	574.7	512.9	389.1	296.3	285.8
97.5°	76.3	126.7	177.0	189.7	413.2	711.1	860.1	820.9	742.8	684.1	664.0
100°	101.1	146.8	192.6	204.0	451.9	782.5	947.8	950.7	956.4	960.6	936.8
102.5°	122.2	164.9	207.6	218.2	469.7	804.9	972.6	1022.4	1122.1	1196.8	1176.3
105°	158.1	194.2	230.4	239.4	482.8	807.5	969.8	1081.5	1304.9	1472.4	1461.4
107.5°	194.8	228.5	262.2	270.6	485.3	771.5	914.7	1070.5	1382.1	1615.8	1618.4
110°	219.6	250.1	280.4	288.0	481.6	739.7	868.7	1042.9	1391.3	1652.5	1664.0



TEST NUMBER: P937319

CATALOG NUMBER: SQ4-FB-075U-125D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	243.9	272.9	301.9	309.1	481.7	711.9	827.0	1005.2	1361.7	1629.0	1646.6
115°	280.7	307.5	334.1	340.9	486.2	679.9	776.9	948.6	1292.0	1549.6	1573.9
117.5°	317.0	341.3	365.6	371.7	495.3	660.0	742.4	897.4	1207.3	1439.8	1466.8
120°	338.1	361.0	383.8	389.6	502.6	653.3	728.6	870.2	1153.4	1365.8	1392.1
122.5°	358.8	381.9	405.0	410.7	513.2	649.8	718.1	845.5	1100.5	1291.8	1317.7
125°	390.5	411.5	432.5	437.8	527.4	646.8	706.6	814.9	1031.6	1194.0	1217.8
127.5°	416.2	437.5	458.6	464.0	541.6	645.2	696.9	789.9	975.9	1115.5	1135.6
130°	430.0	452.9	475.7	481.5	552.1	646.3	693.3	776.1	941.7	1065.9	1084.4
132.5°	444.2	467.1	489.9	495.7	560.5	646.8	690.0	764.1	912.4	1023.6	1040.2
135°	465.3	486.2	507.0	512.3	569.7	646.3	684.5	746.5	870.7	963.8	978.1
137.5°	487.0	507.5	528.2	533.3	583.4	650.2	683.6	736.1	841.0	919.7	931.5
140°	504.9	523.8	542.9	547.6	591.9	650.9	680.3	725.7	816.4	884.4	895.3
142.5°	518.7	536.3	553.9	558.2	598.9	653.2	680.3	720.2	799.8	859.6	869.0
145°	539.8	555.2	570.4	574.2	608.1	653.3	675.8	708.4	773.5	822.3	829.4
147.5°	560.9	575.8	590.7	594.5	621.6	657.7	675.8	701.4	752.7	791.1	797.0
150°	574.7	588.2	601.7	605.1	628.7	660.1	675.8	697.4	740.7	773.2	778.0
152.5°	588.9	599.2	609.4	612.0	633.2	661.6	675.8	694.3	731.2	759.0	762.6
155°	610.1	617.6	625.2	627.1	643.3	664.9	675.8	690.5	720.0	742.0	744.4
157.5°	625.7	633.1	640.4	642.3	653.5	668.4	675.8	687.3	710.1	727.3	728.9
160°	636.3	642.0	647.7	649.1	658.0	669.9	675.8	685.6	705.1	719.9	720.8
162.5°	646.8	651.2	655.4	656.5	662.9	671.5	675.8	684.1	700.6	713.0	713.9
165°	658.3	662.3	666.1	667.1	670.0	673.8	675.8	681.7	693.6	702.5	703.5
167.5°	668.9	670.8	672.5	673.0	675.5	678.8	680.3	684.2	692.0	697.8	698.2
170°	675.8	677.7	679.4	679.9	680.0	680.2	680.3	684.2	692.0	697.8	697.8
172.5°	679.4	679.8	680.2	680.3	680.3	680.3	680.3	683.4	689.5	694.2	693.8
175°	684.5	684.5	684.5	684.5	683.1	681.2	680.3	682.3	686.2	689.1	689.1
177.5°	684.5	684.5	684.5	684.5	683.4	682.0	681.3	682.9	686.0	688.2	687.8
180°	684.5	684.5	684.5	684.5	684.5	684.5	684.5	684.5	684.5	684.5	684.5



TEST NUMBER: P937319

CATALOG NUMBER: SQ4-FB-075U-125D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	779.9	779.9
2.5°	832.6	827.6
5°	1070.9	1075.9
7.5°	1442.1	1439.5
10°	1793.1	1815.7
12.5°	2048.9	2054.0
15°	2204.4	2214.5
17.5°	2264.6	2267.2
20°	2267.2	2262.1
22.5°	2239.5	2234.6
25°	2206.9	2204.4
27.5°	2176.9	2179.3
30°	2164.3	2171.8
32.5°	2164.3	2176.9
35°	2169.4	2181.9
37.5°	2166.8	2181.9
40°	2156.8	2174.3
42.5°	2129.2	2141.8
45°	2086.6	2101.6
47.5°	2031.4	2041.4
50°	1961.2	1971.2
52.5°	1873.3	1875.9
55°	1768.0	1778.1
57.5°	1655.2	1657.7
60°	1529.8	1537.3
62.5°	1396.9	1396.9
65°	1256.4	1261.5
67.5°	1111.0	1123.6
70°	963.0	965.6
72.5°	817.6	817.6
75°	667.1	669.6
77.5°	524.1	524.1
80°	388.7	391.2
82.5°	268.3	273.4
85°	168.1	168.1
87.5°	77.8	70.2
90°	17.5	17.5
92.5°	69.9	56.0
95°	243.7	201.7
97.5°	584.0	504.0
100°	841.4	746.0
102.5°	1094.7	1013.0
105°	1417.5	1373.6
107.5°	1629.0	1639.6
110°	1709.6	1755.4





TEST NUMBER: P937319

CATALOG NUMBER: SQ4-FB-075U-125D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	1716.8	1787.1
115°	1671.3	1768.7
117.5°	1574.8	1682.8
120°	1497.0	1601.9
122.5°	1421.2	1524.8
125°	1313.2	1408.6
127.5°	1216.0	1296.5
130°	1158.7	1233.0
132.5°	1106.8	1173.3
135°	1035.5	1092.9
137.5°	978.4	1025.4
140°	939.3	983.2
142.5°	906.8	944.5
145°	858.1	886.6
147.5°	820.6	844.3
150°	797.2	816.4
152.5°	777.1	791.6
155°	753.9	763.5
157.5°	735.7	742.4
160°	724.7	728.6
162.5°	717.6	721.2
165°	707.3	711.2
167.5°	699.9	701.5
170°	697.8	697.8
172.5°	692.4	690.9
175°	689.1	689.1
177.5°	686.2	684.5
180°	684.5	684.5



TEST NUMBER: P937319  
 CATALOG NUMBER: SQ4-FB-075U-125D-840-1D-UNV-STD-W-6

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.14	8.12	8.02	9.02	10.18	20.30	21.28	21.18	22.19	23.34
	3H	7.85	8.73	8.74	9.65	10.83	22.14	23.03	23.04	23.94	25.12
	4H	8.15	8.99	9.06	9.91	11.10	22.79	23.63	23.70	24.55	25.74
	6H	8.41	9.18	9.33	10.11	11.31	23.22	24.00	24.14	24.92	26.13
	8H	8.48	9.22	9.41	10.16	11.37	23.35	24.08	24.27	25.03	26.23
	12H	8.50	9.21	9.44	10.15	11.37	23.42	24.12	24.35	25.06	26.28
4H	2H	14.36	15.19	15.27	16.11	17.30	20.59	21.43	21.50	22.35	23.54
	3H	15.94	16.64	16.86	17.59	18.79	22.64	23.34	23.57	24.29	25.50
	4H	16.04	16.68	16.97	17.62	18.85	23.41	24.05	24.34	25.00	26.23
	6H	16.05	16.61	17.00	17.58	18.81	23.95	24.51	24.90	25.48	26.71
	8H	16.03	16.55	16.99	17.52	18.76	24.11	24.63	25.07	25.60	26.84
	12H	16.00	16.47	16.97	17.45	18.70	24.21	24.68	25.18	25.66	26.91
8H	4H	17.49	18.01	18.44	18.97	20.21	23.48	24.00	24.43	24.96	26.21
	6H	17.74	18.17	18.71	19.17	20.41	24.11	24.54	25.09	25.55	26.79
	8H	17.76	18.14	18.74	19.13	20.39	24.33	24.71	25.32	25.71	26.97
	12H	17.73	18.06	18.72	19.05	20.36	24.48	24.81	25.47	25.80	27.11
12H	4H	17.64	18.10	18.61	19.09	20.34	23.44	23.91	24.41	24.89	26.14
	6H	17.99	18.38	18.98	19.37	20.63	24.10	24.48	25.08	25.47	26.73
	8H	18.07	18.41	19.06	19.39	20.70	24.33	24.66	25.32	25.65	26.96