

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562713

Luminaire Tested: **SQ4-PC3-075U-050D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562713
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-050D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12936.7 lumens
Efficiency: N/A
Efficacy: 120.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 107.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562713

CATALOG NUMBER: SQ4-PC3-075U-050D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P562713

CATALOG NUMBER: SQ4-PC3-075U-050D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40				
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	40	39	34				
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	36	35	33	28				
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24				
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20				
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18				
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19	15				
7	56	44	37	31	51	41	34	29	34	29	25	27	23	21	21	19	16	14				
8	52	40	33	27	47	37	30	25	31	26	22	25	21	18	20	17	15	12				
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11				
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5781	5781	5781
5°	5824	5787	5765
10°	5810	5783	5767
15°	5779	5779	5774
20°	5741	5758	5758
25°	5687	5729	5711
30°	5618	5686	5661
35°	5534	5619	5580
40°	5443	5520	5464
45°	5344	5382	5299
50°	5204	5204	5121
55°	5039	4974	4899
60°	4796	4699	4624
65°	4432	4344	4306
70°	3881	3912	3897
75°	3123	3453	3474
80°	2219	2928	2959
85°	1351	2456	2456



TEST NUMBER: P562713

CATALOG NUMBER: SQ4-PC3-075U-050D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.9	1.4
10°-20°	510.5	3.9
20°-30°	773.1	6.0
30°-40°	926.8	7.2
40°-50°	945.0	7.3
50°-60°	824.9	6.4
60°-70°	590.6	4.6
70°-80°	304.2	2.4
80°-90°	80.0	0.6
90°-100°	565.0	4.4
100°-110°	1554.4	12.0
110°-120°	1604.4	12.4
120°-130°	1285.5	9.9
130°-140°	1009.6	7.8
140°-150°	773.7	6.0
150°-160°	556.3	4.3
160°-170°	340.2	2.6
170°-180°	114.7	0.9
0°-30°	1461.4	11.3
0°-40°	2388.2	18.5
0°-60°	4158.2	32.1
0°-90°	5132.9	39.7
90°-120°	3723.8	28.8
90°-150°	6792.7	52.5
90°-180°	7804.0	60.3
0°-180°	12936.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1880	1880	1880	1880	1880	
5°	1887	1868	1874	1869	1867	179
15°	1815	1800	1815	1815	1814	512
25°	1676	1664	1688	1683	1683	771
35°	1474	1471	1497	1486	1486	922
45°	1229	1225	1237	1222	1218	946
55°	940	928	928	914	914	838
65°	609	596	597	592	592	602
75°	263	275	291	292	292	284
85°	38	59	70	71	70	52
90°	2	10	18	23	23	7
95°	84	308	999	427	273	89
105°	278	427	1713	2608	2434	293
115°	492	599	1374	2736	3104	485
125°	678	773	1246	2108	2470	605
135°	818	908	1211	1705	1929	631
145°	946	1010	1193	1453	1565	593
155°	1070	1105	1185	1306	1343	492
165°	1157	1172	1190	1239	1246	326
175°	1198	1200	1193	1208	1206	114
180°	1198	1198	1198	1198	1198	

TEST NUMBER: P562713

CATALOG NUMBER: SQ4-PC3-075U-050D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1879.6	1879.6	1879.6	1879.6	1879.6
2.5°	1890.8	1874.4	1879.6	1875.3	1868.5
5°	1886.6	1867.9	1874.4	1869.1	1867.4
7.5°	1873.0	1854.3	1862.9	1859.4	1857.7
10°	1860.5	1841.8	1851.8	1848.3	1846.6
12.5°	1843.8	1826.4	1837.9	1834.4	1834.0
15°	1815.2	1799.9	1815.2	1815.2	1813.5
17.5°	1779.4	1765.4	1781.8	1782.8	1781.8
20°	1754.3	1739.0	1759.5	1757.8	1759.5
22.5°	1723.7	1711.1	1733.1	1728.6	1730.3
25°	1676.0	1664.1	1688.2	1683.0	1683.0
27.5°	1619.6	1611.1	1637.4	1631.8	1631.8
30°	1582.0	1573.5	1601.2	1594.2	1594.2
32.5°	1540.2	1534.5	1560.8	1552.4	1552.4
35°	1474.1	1470.7	1496.7	1486.3	1486.3
37.5°	1405.9	1402.8	1426.4	1413.8	1409.7
40°	1355.8	1354.1	1374.9	1361.0	1361.0
42.5°	1305.6	1303.9	1322.0	1305.3	1305.3
45°	1228.7	1225.3	1237.4	1221.7	1218.3
47.5°	1144.8	1141.4	1149.0	1131.9	1130.2
50°	1087.7	1084.3	1087.7	1072.0	1070.3
52.5°	1029.3	1023.1	1023.7	1008.0	1007.7
55°	939.8	927.9	927.6	913.7	913.7
57.5°	845.1	829.5	830.9	819.0	817.3
60°	779.7	762.7	764.0	753.6	751.8
62.5°	715.6	695.9	700.0	688.1	687.8
65°	609.1	595.5	597.0	591.7	591.7
67.5°	506.8	494.2	503.3	499.1	498.8
70°	431.6	423.1	435.1	435.1	433.4
72.5°	362.0	361.7	376.6	376.6	377.7
75°	262.8	274.7	290.6	292.4	292.4
77.5°	175.4	196.5	214.1	214.8	214.4
80°	125.3	149.1	165.3	168.8	167.1
82.5°	84.9	110.1	123.6	127.0	125.3
85°	38.3	58.7	69.6	71.3	69.6
87.5°	11.6	25.4	31.4	32.4	29.6
90°	2.5	10.0	17.8	22.9	22.9
92.5°	35.2	150.3	260.5	100.0	82.1
95°	84.1	308.4	999.1	427.2	272.7
97.5°	137.1	342.0	1524.6	1174.7	828.8
100°	175.9	362.8	1689.8	1705.6	1391.6
102.5°	212.6	387.5	1732.6	2116.0	1827.9
105°	277.8	427.3	1712.7	2608.5	2434.0
107.5°	340.0	476.6	1615.4	2849.6	2901.5
110°	384.9	509.5	1542.0	2909.6	3089.0



TEST NUMBER: P562713

CATALOG NUMBER: SQ4-PC3-075U-050D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	425.6	546.3	1468.6	2871.0	3144.1
115°	491.9	599.1	1373.8	2735.5	3104.3
117.5°	555.1	653.8	1313.6	2545.5	2962.6
120°	593.9	688.6	1287.1	2403.0	2834.2
122.5°	628.5	723.2	1268.8	2278.2	2687.4
125°	678.0	772.7	1246.3	2108.4	2469.7
127.5°	724.9	815.1	1231.5	1966.7	2283.7
130°	749.3	841.5	1223.4	1882.4	2171.5
132.5°	777.9	870.1	1217.3	1808.4	2069.6
135°	818.1	907.9	1210.6	1705.1	1929.4
137.5°	855.9	939.1	1205.0	1621.6	1806.5
140°	884.4	961.7	1203.0	1566.2	1733.1
142.5°	908.9	980.1	1198.9	1516.7	1659.7
145°	945.6	1010.4	1192.8	1452.8	1564.9
147.5°	984.8	1040.6	1189.7	1396.2	1485.9
150°	1009.3	1059.1	1187.7	1365.2	1434.9
152.5°	1031.7	1077.6	1185.7	1338.4	1396.2
155°	1070.5	1105.4	1185.2	1305.8	1343.2
157.5°	1098.5	1126.9	1185.2	1279.0	1304.9
160°	1118.9	1141.3	1185.2	1264.6	1284.6
162.5°	1135.2	1153.6	1187.2	1252.3	1268.2
165°	1157.1	1172.1	1190.3	1238.8	1246.3
167.5°	1172.4	1183.9	1192.8	1227.5	1229.5
170°	1182.6	1190.1	1192.8	1223.4	1223.4
172.5°	1190.8	1194.3	1192.8	1217.2	1215.2
175°	1197.9	1200.4	1192.8	1208.0	1205.5
177.5°	1199.9	1199.9	1191.8	1203.9	1199.9
180°	1197.9	1197.9	1197.9	1197.9	1197.9

(END OF REPORT)