

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562929

Luminaire Tested: **SQ4-PC3-100U-075D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562929
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18033.4 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 153.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562929

CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P562929

CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	87	84	81	78	69	67	65	56	54	53	43	42	41	35
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	31	30	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	22
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22	19
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	22	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	13
9	49	37	29	24	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8520	8520	8520
5°	8584	8529	8497
10°	8563	8523	8499
15°	8518	8518	8510
20°	8462	8487	8487
25°	8382	8443	8417
30°	8280	8380	8344
35°	8157	8282	8224
40°	8022	8136	8053
45°	7877	7932	7810
50°	7670	7670	7548
55°	7427	7331	7221
60°	7069	6926	6816
65°	6533	6402	6346
70°	5721	5766	5743
75°	4602	5090	5120
80°	3271	4316	4362
85°	1990	3620	3620



TEST NUMBER: P562929

CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	262.2	1.5
10°-20°	752.4	4.2
20°-30°	1139.4	6.3
30°-40°	1366.0	7.6
40°-50°	1392.8	7.7
50°-60°	1215.9	6.7
60°-70°	870.4	4.8
70°-80°	448.3	2.5
80°-90°	116.7	0.6
90°-100°	754.6	4.2
100°-110°	2083.1	11.6
110°-120°	2148.4	11.9
120°-130°	1726.4	9.6
130°-140°	1356.8	7.5
140°-150°	1040.6	5.8
150°-160°	747.9	4.1
160°-170°	457.3	2.5
170°-180°	154.2	0.9
0°-30°	2154.0	11.9
0°-40°	3520.0	19.5
0°-60°	6128.7	34.0
0°-90°	7564.1	41.9
90°-120°	4986.1	27.6
90°-150°	9109.9	50.5
90°-180°	10469.0	58.1
0°-180°	18033.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2770	2770	2770	2770	2770	
5°	2781	2753	2763	2755	2752	264
15°	2675	2653	2675	2675	2673	754
25°	2470	2453	2488	2480	2480	1137
35°	2173	2168	2206	2191	2191	1359
45°	1811	1806	1824	1801	1796	1394
55°	1385	1368	1367	1347	1347	1235
65°	898	878	880	872	872	888
75°	387	405	428	431	431	419
85°	56	86	103	105	103	77
90°	5	10	21	23	26	10
95°	111	408	1369	563	366	119
105°	371	573	2292	3499	3295	395
115°	665	804	1846	3654	4156	654
125°	913	1039	1673	2832	3323	812
135°	1098	1217	1627	2293	2586	850
145°	1274	1362	1606	1952	2101	797
155°	1436	1484	1593	1752	1807	662
165°	1555	1575	1601	1663	1676	438
175°	1611	1614	1604	1627	1622	153
180°	1611	1611	1611	1611	1611	

TEST NUMBER: P562929

CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2770.3	2770.3	2770.3	2770.3	2770.3
2.5°	2786.8	2762.7	2770.3	2764.0	2753.9
5°	2780.6	2753.0	2762.6	2754.9	2752.4
7.5°	2760.6	2733.0	2745.7	2740.5	2738.0
10°	2742.1	2714.5	2729.3	2724.1	2721.6
12.5°	2717.5	2691.9	2708.8	2703.6	2703.1
15°	2675.4	2652.9	2675.4	2675.4	2672.9
17.5°	2622.6	2602.0	2626.2	2627.7	2626.2
20°	2585.7	2563.1	2593.3	2590.8	2593.3
22.5°	2540.5	2521.9	2554.4	2547.7	2550.3
25°	2470.2	2452.7	2488.2	2480.5	2480.5
27.5°	2387.1	2374.6	2413.3	2405.1	2405.1
30°	2331.7	2319.2	2359.9	2349.7	2349.7
32.5°	2270.1	2261.6	2300.4	2288.1	2288.1
35°	2172.7	2167.7	2206.0	2190.6	2190.6
37.5°	2072.1	2067.6	2102.4	2083.8	2077.8
40°	1998.2	1995.7	2026.5	2005.9	2005.9
42.5°	1924.4	1921.9	1948.5	1923.8	1923.8
45°	1811.0	1806.0	1823.8	1800.6	1795.6
47.5°	1687.3	1682.3	1693.5	1668.3	1665.8
50°	1603.2	1598.2	1603.2	1580.1	1577.6
52.5°	1517.0	1508.0	1508.8	1485.7	1485.2
55°	1385.2	1367.6	1367.2	1346.7	1346.7
57.5°	1245.6	1222.6	1224.6	1207.1	1204.6
60°	1149.2	1124.1	1126.1	1110.6	1108.1
62.5°	1054.8	1025.7	1031.7	1014.2	1013.7
65°	897.8	877.7	879.8	872.1	872.1
67.5°	747.0	728.4	741.8	735.7	735.2
70°	636.2	623.6	641.3	641.2	638.7
72.5°	533.5	533.0	555.1	555.1	556.6
75°	387.3	404.9	428.4	430.9	430.9
77.5°	258.6	289.7	315.5	316.5	316.0
80°	184.7	219.8	243.7	248.8	246.3
82.5°	125.2	162.3	182.1	187.2	184.7
85°	56.4	86.5	102.6	105.1	102.6
87.5°	17.4	36.5	45.2	45.6	42.1
90°	5.2	10.2	20.6	23.3	25.8
92.5°	46.4	192.6	344.4	125.7	98.0
95°	110.9	408.3	1368.9	562.7	366.1
97.5°	183.6	457.3	2027.9	1561.3	1130.7
100°	237.2	486.7	2271.3	2287.3	1858.8
102.5°	288.7	520.1	2318.7	2826.1	2419.8
105°	371.2	572.9	2291.9	3498.9	3294.7
107.5°	458.9	638.4	2164.0	3823.4	3898.0
110°	520.8	682.1	2065.0	3893.2	4135.2



TEST NUMBER: P562929

CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	576.5	731.7	1972.2	3838.1	4195.0
115°	665.1	803.8	1845.9	3654.2	4155.8
117.5°	742.5	880.6	1762.9	3395.4	3966.1
120°	794.0	930.2	1729.9	3220.2	3794.9
122.5°	843.5	973.6	1703.1	3056.5	3601.0
125°	912.6	1038.7	1673.2	2831.6	3323.1
127.5°	971.4	1097.4	1655.6	2641.3	3065.3
130°	1010.6	1136.6	1647.4	2524.9	2910.6
132.5°	1047.7	1167.7	1639.1	2427.2	2776.6
135°	1098.2	1216.7	1626.7	2293.4	2585.8
137.5°	1155.0	1262.9	1620.6	2181.0	2430.6
140°	1185.9	1291.8	1616.4	2106.1	2325.4
142.5°	1221.0	1318.8	1612.3	2039.5	2232.6
145°	1273.6	1361.8	1606.1	1952.4	2101.1
147.5°	1324.1	1401.2	1600.5	1878.9	1994.4
150°	1361.2	1424.2	1598.4	1835.1	1928.4
152.5°	1390.1	1449.1	1596.3	1797.6	1874.8
155°	1436.0	1483.9	1593.2	1751.8	1807.2
157.5°	1478.3	1515.1	1593.7	1718.4	1756.2
160°	1503.0	1535.8	1595.8	1699.6	1727.3
162.5°	1523.6	1552.4	1597.9	1682.9	1704.6
165°	1554.6	1574.7	1601.0	1663.1	1675.7
167.5°	1578.3	1590.4	1603.5	1651.1	1655.1
170°	1590.7	1600.7	1603.5	1644.8	1644.8
172.5°	1601.0	1607.0	1603.5	1636.5	1634.5
175°	1611.3	1613.8	1603.5	1626.6	1621.6
177.5°	1615.4	1613.4	1603.0	1617.4	1613.3
180°	1611.3	1611.3	1611.3	1611.3	1611.3

(END OF REPORT)