

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562977

Luminaire Tested: **SQ4-PC3-100U-125D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562977
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-125D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23292.8 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 214.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562977
CATALOG NUMBER: SQ4-PC3-100U-125D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P562977

CATALOG NUMBER: SQ4-PC3-100U-125D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55		
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	51	47		
2	90	83	76	71	83	77	72	67	66	62	59	56	54	51	47	45	43	39		
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33		
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	37	34	32	28		
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24		
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21		
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19		
8	55	42	34	29	51	39	32	27	35	29	25	30	25	22	26	22	19	17		
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15		
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14446	14446	14446
5°	14555	14461	14408
10°	14520	14452	14411
15°	14444	14444	14430
20°	14348	14391	14391
25°	14213	14316	14272
30°	14040	14210	14148
35°	13831	14043	13945
40°	13602	13795	13655
45°	13355	13450	13242
50°	13006	13006	12798
55°	12593	12430	12244
60°	11985	11744	11557
65°	11078	10857	10761
70°	9700	9778	9738
75°	7804	8631	8682
80°	5547	7318	7394
85°	3377	6140	6140



TEST NUMBER: P562977

CATALOG NUMBER: SQ4-PC3-100U-125D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	444.6	1.9
10°-20°	1275.8	5.5
20°-30°	1932.0	8.3
30°-40°	2316.2	9.9
40°-50°	2361.7	10.1
50°-60°	2061.6	8.9
60°-70°	1475.9	6.3
70°-80°	760.2	3.3
80°-90°	195.6	0.8
90°-100°	754.6	3.2
100°-110°	2083.1	8.9
110°-120°	2148.4	9.2
120°-130°	1726.4	7.4
130°-140°	1356.8	5.8
140°-150°	1040.6	4.5
150°-160°	747.9	3.2
160°-170°	457.3	2.0
170°-180°	154.2	0.7
0°-30°	3652.3	15.7
0°-40°	5968.5	25.6
0°-60°	10391.8	44.6
0°-90°	12823.5	55.1
90°-120°	4986.1	21.4
90°-150°	9109.9	39.1
90°-180°	10469.0	44.9
0°-180°	23292.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4697	4697	4697	4697	4697	
5°	4715	4668	4684	4671	4667	448
15°	4536	4498	4536	4536	4532	1279
25°	4188	4159	4219	4206	4206	1928
35°	3684	3676	3740	3714	3714	2304
45°	3071	3062	3092	3053	3045	2364
55°	2349	2319	2318	2284	2284	2094
65°	1522	1488	1492	1479	1479	1506
75°	657	686	726	731	731	710
85°	96	147	174	178	174	130
90°	5	10	21	23	26	12
95°	111	408	1369	563	366	119
105°	371	573	2292	3499	3295	395
115°	665	804	1846	3654	4156	654
125°	913	1039	1673	2832	3323	812
135°	1098	1217	1627	2293	2586	850
145°	1274	1362	1606	1952	2101	797
155°	1436	1484	1593	1752	1807	662
165°	1555	1575	1601	1663	1676	438
175°	1611	1614	1604	1627	1622	153
180°	1611	1611	1611	1611	1611	

TEST NUMBER: P562977

CATALOG NUMBER: SQ4-PC3-100U-125D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4697.4	4697.4	4697.4	4697.4	4697.4
2.5°	4725.2	4684.4	4697.4	4686.6	4669.6
5°	4714.8	4668.0	4684.4	4671.2	4667.0
7.5°	4680.9	4634.1	4655.6	4646.9	4642.6
10°	4649.6	4602.8	4627.8	4619.0	4614.8
12.5°	4607.8	4564.4	4593.0	4584.3	4583.4
15°	4536.5	4498.2	4536.5	4536.4	4532.1
17.5°	4446.9	4412.0	4453.0	4455.5	4453.0
20°	4384.2	4346.0	4397.3	4393.0	4397.3
22.5°	4307.7	4276.2	4331.2	4320.0	4324.2
25°	4188.5	4158.7	4219.0	4205.9	4205.9
27.5°	4047.6	4026.3	4092.0	4078.0	4078.0
30°	3953.6	3932.4	4001.5	3984.1	3984.1
32.5°	3849.3	3834.8	3900.6	3879.7	3879.7
35°	3684.0	3675.5	3740.5	3714.4	3714.4
37.5°	3513.5	3505.8	3564.8	3533.3	3523.1
40°	3388.2	3384.0	3436.1	3401.3	3401.3
42.5°	3263.0	3258.7	3303.8	3262.1	3262.1
45°	3070.7	3062.2	3092.5	3053.1	3044.6
47.5°	2861.1	2852.6	2871.5	2828.8	2824.5
50°	2718.4	2709.9	2718.4	2679.2	2674.9
52.5°	2572.3	2557.0	2558.3	2519.2	2518.3
55°	2348.7	2318.9	2318.3	2283.5	2283.5
57.5°	2112.1	2073.0	2076.4	2046.8	2042.5
60°	1948.6	1906.0	1909.4	1883.2	1879.0
62.5°	1788.5	1739.2	1749.3	1719.8	1718.9
65°	1522.3	1488.3	1491.9	1478.8	1478.8
67.5°	1266.6	1235.1	1257.9	1247.4	1246.6
70°	1078.7	1057.4	1087.4	1087.3	1083.0
72.5°	904.7	903.8	941.2	941.3	943.8
75°	656.8	686.5	726.4	730.7	730.7
77.5°	438.4	491.2	535.0	536.7	535.9
80°	313.2	372.7	413.2	421.8	417.5
82.5°	212.3	275.2	308.8	317.4	313.2
85°	95.7	146.7	174.0	178.2	174.0
87.5°	28.9	60.5	73.7	74.1	67.8
90°	5.2	10.2	20.6	23.3	25.8
92.5°	46.4	192.6	344.4	125.7	98.0
95°	110.9	408.3	1368.9	562.7	366.1
97.5°	183.6	457.3	2027.9	1561.3	1130.7
100°	237.2	486.7	2271.3	2287.3	1858.8
102.5°	288.7	520.1	2318.7	2826.1	2419.8
105°	371.2	572.9	2291.9	3498.9	3294.7
107.5°	458.9	638.4	2164.0	3823.4	3898.0
110°	520.8	682.1	2065.0	3893.2	4135.2



TEST NUMBER: P562977

CATALOG NUMBER: SQ4-PC3-100U-125D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	576.5	731.7	1972.2	3838.1	4195.0
115°	665.1	803.8	1845.9	3654.2	4155.8
117.5°	742.5	880.6	1762.9	3395.4	3966.1
120°	794.0	930.2	1729.9	3220.2	3794.9
122.5°	843.5	973.6	1703.1	3056.5	3601.0
125°	912.6	1038.7	1673.2	2831.6	3323.1
127.5°	971.4	1097.4	1655.6	2641.3	3065.3
130°	1010.6	1136.6	1647.4	2524.9	2910.6
132.5°	1047.7	1167.7	1639.1	2427.2	2776.6
135°	1098.2	1216.7	1626.7	2293.4	2585.8
137.5°	1155.0	1262.9	1620.6	2181.0	2430.6
140°	1185.9	1291.8	1616.4	2106.1	2325.4
142.5°	1221.0	1318.8	1612.3	2039.5	2232.6
145°	1273.6	1361.8	1606.1	1952.4	2101.1
147.5°	1324.1	1401.2	1600.5	1878.9	1994.4
150°	1361.2	1424.2	1598.4	1835.1	1928.4
152.5°	1390.1	1449.1	1596.3	1797.6	1874.8
155°	1436.0	1483.9	1593.2	1751.8	1807.2
157.5°	1478.3	1515.1	1593.7	1718.4	1756.2
160°	1503.0	1535.8	1595.8	1699.6	1727.3
162.5°	1523.6	1552.4	1597.9	1682.9	1704.6
165°	1554.6	1574.7	1601.0	1663.1	1675.7
167.5°	1578.3	1590.4	1603.5	1651.1	1655.1
170°	1590.7	1600.7	1603.5	1644.8	1644.8
172.5°	1601.0	1607.0	1603.5	1636.5	1634.5
175°	1611.3	1613.8	1603.5	1626.6	1621.6
177.5°	1615.4	1613.4	1603.0	1617.4	1613.3
180°	1611.3	1611.3	1611.3	1611.3	1611.3

(END OF REPORT)