

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562683

Luminaire Tested: **SQ4-PC3-050U-125D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562683
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-125D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10471.2 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 87.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562683
CATALOG NUMBER: SQ4-PC3-050U-125D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562683

CATALOG NUMBER: SQ4-PC3-050U-125D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	98	94	91	97	93	90	86	84	81	79	75	73	71	67	65	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	50
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46	43
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34	32
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	34	30	28
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	35	30	27	25
8	57	44	36	30	54	42	35	30	39	32	28	35	30	26	32	27	24	22
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	22	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16794	16794	16794
5°	16920	16811	16748
10°	16879	16800	16753
15°	16791	16791	16774
20°	16680	16730	16730
25°	16522	16642	16591
30°	16321	16519	16447
35°	16078	16325	16211
40°	15813	16036	15873
45°	15525	15635	15393
50°	15119	15119	14878
55°	14639	14450	14232
60°	13933	13652	13435
65°	12877	12620	12509
70°	11276	11366	11321
75°	9071	10034	10093
80°	6447	8508	8597
85°	3924	7135	7135



TEST NUMBER: P562683

CATALOG NUMBER: SQ4-PC3-050U-125D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.4	2.5
10°-20°	741.5	7.1
20°-30°	1122.9	10.7
30°-40°	1346.2	12.9
40°-50°	1372.7	13.1
50°-60°	1198.3	11.4
60°-70°	857.9	8.2
70°-80°	441.9	4.2
80°-90°	113.5	1.1
90°-100°	221.9	2.1
100°-110°	602.8	5.8
110°-120°	619.7	5.9
120°-130°	495.5	4.7
130°-140°	389.3	3.7
140°-150°	298.5	2.9
150°-160°	214.7	2.1
160°-170°	131.3	1.3
170°-180°	44.2	0.4
0°-30°	2122.8	20.3
0°-40°	3469.1	33.1
0°-60°	6040.0	57.7
0°-90°	7453.3	71.2
90°-120°	1444.4	13.8
90°-150°	2627.7	25.1
90°-180°	3018.0	28.8
0°-180°	10471.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2730	2730	2730	2730	2730	
5°	2740	2713	2723	2715	2713	260
15°	2637	2614	2637	2637	2634	743
25°	2434	2417	2452	2445	2445	1120
35°	2141	2136	2174	2159	2159	1339
45°	1785	1780	1797	1775	1770	1374
55°	1365	1348	1348	1327	1327	1217
65°	885	865	867	860	860	875
75°	382	399	422	425	425	413
85°	56	85	101	104	101	76
90°	2	6	10	13	13	5
95°	33	121	386	168	113	35
105°	107	167	663	1009	950	114
115°	190	231	531	1056	1202	188
125°	262	298	480	809	954	233
135°	315	350	467	659	743	244
145°	364	390	461	560	602	229
155°	412	426	458	503	517	190
165°	446	452	459	479	480	126
175°	462	464	461	467	465	44
180°	462	462	462	462	462	

TEST NUMBER: P562683

CATALOG NUMBER: SQ4-PC3-050U-125D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2730.3	2730.3	2730.3	2730.3	2730.3
2.5°	2746.5	2722.7	2730.3	2724.0	2714.1
5°	2740.4	2713.2	2722.7	2715.1	2712.6
7.5°	2720.7	2693.5	2706.0	2700.9	2698.4
10°	2702.5	2675.3	2689.8	2684.7	2682.3
12.5°	2678.2	2653.0	2669.6	2664.6	2664.1
15°	2636.8	2614.5	2636.8	2636.7	2634.2
17.5°	2584.7	2564.4	2588.2	2589.7	2588.2
20°	2548.3	2526.0	2555.9	2553.4	2555.9
22.5°	2503.8	2485.5	2517.4	2510.9	2513.4
25°	2434.5	2417.2	2452.2	2444.6	2444.6
27.5°	2352.6	2340.2	2378.4	2370.3	2370.3
30°	2298.0	2285.6	2325.8	2315.7	2315.7
32.5°	2237.3	2228.9	2267.2	2255.0	2255.0
35°	2141.3	2136.3	2174.1	2159.0	2159.0
37.5°	2042.2	2037.7	2072.0	2053.7	2047.7
40°	1969.4	1966.9	1997.2	1976.9	1976.9
42.5°	1896.5	1894.1	1920.3	1896.0	1896.0
45°	1784.8	1779.9	1797.4	1774.6	1769.6
47.5°	1663.0	1658.0	1669.0	1644.2	1641.7
50°	1580.0	1575.1	1580.0	1557.2	1554.8
52.5°	1495.1	1486.2	1487.0	1464.2	1463.7
55°	1365.1	1347.8	1347.5	1327.2	1327.2
57.5°	1227.6	1204.9	1206.9	1189.6	1187.2
60°	1132.6	1107.8	1109.8	1094.6	1092.1
62.5°	1039.5	1010.9	1016.8	999.6	999.1
65°	884.8	865.0	867.1	859.5	859.5
67.5°	736.2	717.9	731.1	725.0	724.5
70°	627.0	614.6	632.0	632.0	629.5
72.5°	525.8	525.3	547.1	547.1	548.6
75°	381.7	399.0	422.2	424.7	424.7
77.5°	254.8	285.5	311.0	312.0	311.5
80°	182.0	216.6	240.2	245.2	242.7
82.5°	123.4	160.0	179.5	184.5	182.0
85°	55.6	85.3	101.1	103.6	101.1
87.5°	16.5	35.1	42.5	43.0	39.1
90°	1.5	5.8	10.4	13.4	13.4
92.5°	13.4	60.8	105.5	45.3	38.3
95°	32.7	121.3	386.4	168.2	113.0
97.5°	54.1	134.0	592.4	460.9	323.7
100°	68.4	142.5	655.4	664.4	536.5
102.5°	82.6	150.9	672.1	821.7	708.9
105°	107.0	166.6	662.9	1009.3	949.7
107.5°	132.3	184.9	624.5	1106.1	1122.7
110°	150.1	198.1	596.0	1125.2	1196.4



TEST NUMBER: P562683

CATALOG NUMBER: SQ4-PC3-050U-125D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	165.6	211.2	567.4	1109.4	1216.6
115°	190.2	230.9	530.6	1055.6	1202.4
117.5°	213.4	252.4	507.1	979.3	1144.7
120°	228.9	266.7	496.4	928.2	1092.4
122.5°	242.0	279.7	489.3	876.9	1035.3
125°	261.6	297.9	480.1	808.8	954.2
127.5°	279.1	315.2	475.0	757.2	881.9
130°	289.8	324.7	472.6	724.8	836.7
132.5°	300.5	335.4	470.2	697.2	796.3
135°	315.1	350.0	466.7	658.8	743.1
137.5°	330.8	362.5	464.9	624.9	695.9
140°	340.3	370.9	463.7	603.4	667.3
142.5°	349.9	378.0	462.5	586.5	640.0
145°	364.1	390.3	460.7	559.8	601.9
147.5°	380.2	402.6	459.2	538.8	571.9
150°	390.9	409.8	459.2	526.7	552.9
152.5°	399.2	415.8	458.1	515.9	537.4
155°	411.7	426.2	457.8	502.7	517.2
157.5°	423.9	435.2	457.8	493.7	504.7
160°	431.0	441.2	457.8	487.7	496.4
162.5°	438.1	446.0	458.9	482.9	489.3
165°	445.9	451.7	459.2	478.6	480.1
167.5°	453.9	456.8	460.7	473.5	474.7
170°	456.3	459.2	460.7	471.1	471.1
172.5°	458.6	460.4	460.7	468.8	468.8
175°	462.2	463.7	460.7	466.6	465.2
177.5°	463.4	463.4	459.8	464.5	462.2
180°	462.2	462.2	462.2	462.2	462.2

(END OF REPORT)