

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563121

Luminaire Tested: **SQ4-PC3-150U-075D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563121
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-075D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23268.4 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 194.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563121
CATALOG NUMBER: SQ4-PC3-150U-075D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563121

CATALOG NUMBER: SQ4-PC3-150U-075D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	35	34	27
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	28	26	24	19
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	13	10
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8520	8520	8520
5°	8584	8529	8497
10°	8563	8523	8499
15°	8518	8518	8510
20°	8462	8487	8487
25°	8382	8443	8417
30°	8280	8380	8344
35°	8157	8282	8224
40°	8022	8136	8053
45°	7877	7932	7810
50°	7670	7670	7548
55°	7427	7331	7221
60°	7069	6926	6816
65°	6533	6402	6346
70°	5721	5766	5743
75°	4602	5090	5120
80°	3271	4316	4362
85°	1990	3620	3620



TEST NUMBER: P563121

CATALOG NUMBER: SQ4-PC3-150U-075D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	262.2	1.1
10°-20°	752.4	3.2
20°-30°	1139.4	4.9
30°-40°	1366.0	5.9
40°-50°	1392.8	6.0
50°-60°	1215.9	5.2
60°-70°	870.4	3.7
70°-80°	448.3	1.9
80°-90°	118.5	0.5
90°-100°	1131.9	4.9
100°-110°	3060.3	13.2
110°-120°	3217.5	13.8
120°-130°	2613.5	11.2
130°-140°	2050.0	8.8
140°-150°	1573.4	6.8
150°-160°	1131.6	4.9
160°-170°	691.3	3.0
170°-180°	233.1	1.0
0°-30°	2154.0	9.3
0°-40°	3520.0	15.1
0°-60°	6128.7	26.3
0°-90°	7565.9	32.5
90°-120°	7409.7	31.8
90°-150°	13646.6	58.6
90°-180°	15703.0	67.5
0°-180°	23268.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2770	2770	2770	2770	2770	
5°	2781	2753	2763	2755	2752	264
15°	2675	2653	2675	2675	2673	754
25°	2470	2453	2488	2480	2480	1137
35°	2173	2168	2206	2191	2191	1359
45°	1811	1806	1824	1801	1796	1394
55°	1385	1368	1367	1347	1347	1235
65°	898	878	880	872	872	888
75°	387	405	428	431	431	419
85°	56	86	103	105	103	77
90°	5	16	34	37	34	14
95°	176	616	1882	974	579	184
105°	569	879	3395	5008	4803	599
115°	1002	1224	2816	5451	6153	989
125°	1371	1571	2538	4282	5031	1222
135°	1644	1839	2470	3458	3914	1270
145°	1911	2055	2436	2960	3185	1196
155°	2158	2242	2414	2655	2742	995
165°	2349	2372	2425	2520	2532	662
175°	2438	2436	2428	2459	2454	231
180°	2436	2436	2436	2436	2436	

TEST NUMBER: P563121

CATALOG NUMBER: SQ4-PC3-150U-075D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2770.3	2770.3	2770.3	2770.3	2770.3
2.5°	2786.8	2762.7	2770.3	2764.0	2753.9
5°	2780.6	2753.0	2762.6	2754.9	2752.4
7.5°	2760.6	2733.0	2745.7	2740.5	2738.0
10°	2742.1	2714.5	2729.3	2724.1	2721.6
12.5°	2717.5	2691.9	2708.8	2703.6	2703.1
15°	2675.4	2652.9	2675.4	2675.4	2672.9
17.5°	2622.6	2602.0	2626.2	2627.7	2626.2
20°	2585.7	2563.1	2593.3	2590.8	2593.3
22.5°	2540.5	2521.9	2554.4	2547.7	2550.3
25°	2470.2	2452.7	2488.2	2480.5	2480.5
27.5°	2387.1	2374.6	2413.3	2405.1	2405.1
30°	2331.7	2319.2	2359.9	2349.7	2349.7
32.5°	2270.1	2261.6	2300.4	2288.1	2288.1
35°	2172.7	2167.7	2206.0	2190.6	2190.6
37.5°	2072.1	2067.6	2102.4	2083.8	2077.8
40°	1998.2	1995.7	2026.5	2005.9	2005.9
42.5°	1924.4	1921.9	1948.5	1923.8	1923.8
45°	1811.0	1806.0	1823.8	1800.6	1795.6
47.5°	1687.3	1682.3	1693.5	1668.3	1665.8
50°	1603.2	1598.2	1603.2	1580.1	1577.6
52.5°	1517.0	1508.0	1508.8	1485.7	1485.2
55°	1385.2	1367.6	1367.2	1346.7	1346.7
57.5°	1245.6	1222.6	1224.6	1207.1	1204.6
60°	1149.2	1124.1	1126.1	1110.6	1108.1
62.5°	1054.8	1025.7	1031.7	1014.2	1013.7
65°	897.8	877.7	879.8	872.1	872.1
67.5°	747.0	728.4	741.8	735.7	735.2
70°	636.2	623.6	641.3	641.2	638.7
72.5°	533.5	533.0	555.1	555.1	556.6
75°	387.3	404.9	428.4	430.9	430.9
77.5°	258.6	289.7	315.5	316.5	316.0
80°	184.7	219.8	243.7	248.8	246.3
82.5°	125.2	162.3	182.1	187.2	184.7
85°	56.4	86.5	102.6	105.1	102.6
87.5°	17.5	37.6	47.9	48.3	43.8
90°	5.2	15.5	34.1	36.6	34.1
92.5°	74.5	271.3	535.3	232.4	168.3
95°	175.6	616.5	1882.3	974.1	579.4
97.5°	282.1	707.1	2934.1	2428.2	1783.2
100°	361.8	743.7	3261.3	3401.2	2750.1
102.5°	435.2	794.6	3376.7	4139.0	3651.9
105°	568.9	879.1	3395.0	5007.9	4802.8
107.5°	692.6	975.6	3246.6	5550.0	5618.1
110°	789.1	1045.4	3114.5	5695.5	5985.2



TEST NUMBER: P563121

CATALOG NUMBER: SQ4-PC3-150U-075D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	875.1	1115.0	2992.8	5666.4	6153.0
115°	1001.5	1224.5	2815.6	5450.6	6153.0
117.5°	1125.2	1334.4	2698.7	5120.8	5917.0
120°	1200.7	1405.8	2629.5	4884.2	5696.8
122.5°	1272.0	1473.0	2587.5	4630.6	5449.3
125°	1371.1	1571.1	2537.7	4282.4	5030.9
127.5°	1462.3	1658.7	2508.4	3998.3	4656.5
130°	1512.7	1715.2	2495.8	3822.7	4417.4
132.5°	1565.1	1765.6	2483.2	3664.4	4211.9
135°	1643.8	1838.6	2469.6	3457.8	3914.1
137.5°	1722.9	1907.0	2458.0	3290.2	3661.9
140°	1777.5	1949.2	2453.8	3182.3	3513.0
142.5°	1829.9	1991.4	2445.5	3084.9	3374.6
145°	1911.2	2054.7	2435.5	2959.7	3185.3
147.5°	1985.1	2112.2	2424.0	2846.3	3019.6
150°	2039.6	2152.4	2419.8	2784.7	2923.1
152.5°	2090.0	2188.4	2417.7	2727.5	2841.3
155°	2157.6	2242.2	2414.5	2655.1	2742.2
157.5°	2227.9	2286.8	2415.0	2604.6	2662.0
160°	2267.7	2316.4	2417.1	2572.7	2613.8
162.5°	2299.2	2339.7	2419.2	2547.3	2578.1
165°	2349.0	2372.0	2425.0	2519.7	2532.5
167.5°	2383.1	2399.0	2425.5	2495.9	2502.1
170°	2404.0	2411.7	2427.6	2485.3	2485.3
172.5°	2420.8	2422.3	2427.6	2472.7	2470.6
175°	2438.1	2435.5	2427.6	2459.0	2453.8
177.5°	2443.9	2437.7	2427.1	2447.9	2441.8
180°	2435.5	2435.5	2435.5	2435.5	2435.5

(END OF REPORT)