

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562803

Luminaire Tested: **SQ4-PC3-0U-050D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562803  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-0U-050D-840-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2981.6 lumens  
Efficiency: N/A  
Efficacy: 111.7 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562803  
CATALOG NUMBER: SQ4-PC3-0U-050D-840-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P562803

CATALOG NUMBER: SQ4-PC3-0U-050D-840-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6720	6720	6720
5°	6770	6727	6702
10°	6754	6722	6703
15°	6719	6719	6712
20°	6674	6694	6694
25°	6611	6659	6639
30°	6531	6610	6581
35°	6433	6533	6487
40°	6327	6416	6352
45°	6213	6256	6159
50°	6049	6049	5953
55°	5858	5782	5695
60°	5575	5463	5376
65°	5154	5050	5005
70°	4512	4548	4530
75°	3629	4014	4038
80°	2579	3404	3439
85°	1574	2858	2858



TEST NUMBER: P562803

CATALOG NUMBER: SQ4-PC3-0U-050D-840-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.4	3.5
10°-20°	296.7	10.0
20°-30°	449.3	15.1
30°-40°	538.7	18.1
40°-50°	549.3	18.4
50°-60°	479.5	16.1
60°-70°	343.3	11.5
70°-80°	176.8	5.9
80°-90°	44.7	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	849.4	28.5
0°-40°	1388.1	46.6
0°-60°	2416.9	81.1
0°-90°	2981.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2981.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1092	1092	1092	1092	1092	
5°	1096	1086	1090	1086	1085	104
15°	1055	1046	1055	1055	1054	297
25°	974	967	981	978	978	448
35°	857	855	870	864	864	536
45°	714	712	719	710	708	550
55°	546	539	539	531	531	487
65°	354	346	347	344	344	350
75°	153	160	169	170	170	165
85°	22	34	40	42	40	31
90°	0	0	0	0	0	



TEST NUMBER: P562803

CATALOG NUMBER: SQ4-PC3-0U-050D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1092.5	1092.5	1092.5	1092.5	1092.5
2.5°	1099.0	1089.5	1092.5	1090.0	1086.0
5°	1096.5	1085.7	1089.5	1086.4	1085.4
7.5°	1088.7	1077.8	1082.8	1080.7	1079.8
10°	1081.4	1070.5	1076.3	1074.3	1073.3
12.5°	1071.7	1061.6	1068.2	1066.2	1066.0
15°	1055.1	1046.2	1055.1	1055.1	1054.1
17.5°	1034.2	1026.1	1035.7	1036.2	1035.7
20°	1019.7	1010.8	1022.7	1021.7	1022.7
22.5°	1001.9	994.5	1007.3	1004.7	1005.7
25°	974.1	967.2	981.2	978.2	978.2
27.5°	941.4	936.4	951.7	948.5	948.5
30°	919.5	914.6	930.7	926.6	926.6
32.5°	895.2	891.9	907.2	902.3	902.3
35°	856.8	854.8	870.0	863.9	863.9
37.5°	817.2	815.4	829.1	821.8	819.4
40°	788.0	787.0	799.1	791.1	791.1
42.5°	758.9	757.9	768.4	758.7	758.7
45°	714.2	712.2	719.2	710.1	708.1
47.5°	665.4	663.4	667.8	657.9	656.9
50°	632.2	630.3	632.2	623.1	622.1
52.5°	598.2	594.7	595.0	585.9	585.7
55°	546.3	539.3	539.2	531.1	531.1
57.5°	491.2	482.1	482.9	476.0	475.0
60°	453.2	443.3	444.1	438.0	437.0
62.5°	416.0	404.5	406.9	400.0	399.8
65°	354.1	346.1	347.0	343.9	343.9
67.5°	294.6	287.3	292.5	290.1	289.9
70°	250.9	245.9	252.9	252.9	251.9
72.5°	210.4	210.2	218.9	218.9	219.5
75°	152.7	159.7	168.9	169.9	169.9
77.5°	102.0	114.2	124.4	124.8	124.6
80°	72.8	86.7	96.1	98.1	97.1
82.5°	49.4	64.0	71.8	73.8	72.8
85°	22.3	34.1	40.5	41.5	40.5
87.5°	6.5	13.6	16.2	16.1	14.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)