

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563505

Luminaire Tested: **SQ4-PP3-0U-075D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563505
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-075D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7489.3 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Direct

Input Watts (W): 79.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563505
CATALOG NUMBER: SQ4-PP3-0U-075D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563505

CATALOG NUMBER: SQ4-PP3-0U-075D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85				85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72				72
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61				61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53				53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46				46
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40				40
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36				36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32				32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29				29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26				26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8999	8999	8999
5°	9065	9010	8978
10°	9050	8986	8946
15°	8990	8941	8892
20°	8930	8880	8813
25°	8824	8763	8676
30°	8661	8615	8506
35°	8434	8376	8271
40°	8165	8113	8020
45°	7941	7886	7808
50°	7657	7607	7534
55°	7260	7164	7109
60°	6609	6420	6388
65°	5822	5580	5561
70°	5027	4820	4820
75°	4328	4266	4205
80°	3815	3861	3771
85°	2985	3257	3257



TEST NUMBER: P563505

CATALOG NUMBER: SQ4-PP3-0U-075D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.7	3.7
10°-20°	790.1	10.5
20°-30°	1183.4	15.8
30°-40°	1388.0	18.5
40°-50°	1392.4	18.6
50°-60°	1187.8	15.9
60°-70°	774.7	10.3
70°-80°	388.6	5.2
80°-90°	107.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2250.1	30.0
0°-40°	3638.2	48.6
0°-60°	6218.4	83.0
0°-90°	7489.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7489.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2926	2926	2926	2926	2926	
5°	2936	2909	2918	2908	2908	279
15°	2824	2796	2808	2798	2793	797
25°	2600	2570	2582	2559	2557	1196
35°	2246	2224	2231	2205	2203	1403
45°	1826	1813	1813	1795	1795	1406
55°	1354	1349	1336	1328	1326	1203
65°	800	785	767	762	764	799
75°	364	364	359	356	354	395
85°	85	92	92	92	92	103
90°	0	0	0	0	0	



TEST NUMBER: P563505

CATALOG NUMBER: SQ4-PP3-OU-075D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2926.1	2926.1	2926.1	2926.1	2926.1
2.5°	2944.6	2920.5	2926.1	2921.7	2909.7
5°	2936.4	2908.8	2918.4	2908.2	2908.2
7.5°	2916.4	2886.3	2895.9	2885.6	2885.1
10°	2897.9	2867.8	2877.4	2867.1	2864.6
12.5°	2871.2	2841.2	2852.8	2840.5	2840.0
15°	2823.5	2796.0	2808.2	2797.8	2792.8
17.5°	2769.7	2739.6	2754.3	2739.9	2737.9
20°	2728.7	2698.6	2713.3	2692.8	2692.8
22.5°	2679.4	2649.3	2666.1	2639.4	2639.4
25°	2600.4	2570.3	2582.5	2559.3	2556.8
27.5°	2506.6	2477.0	2489.6	2463.5	2463.0
30°	2438.9	2411.3	2426.0	2397.8	2395.3
32.5°	2365.0	2339.4	2350.1	2321.9	2319.4
35°	2246.5	2224.0	2231.1	2205.4	2202.9
37.5°	2121.9	2098.8	2107.0	2084.9	2083.9
40°	2033.7	2018.6	2020.8	2002.8	1997.8
42.5°	1951.6	1934.6	1936.7	1918.8	1917.8
45°	1825.9	1813.4	1813.1	1795.2	1795.2
47.5°	1692.6	1683.1	1680.3	1665.4	1664.9
50°	1600.3	1592.7	1590.0	1577.1	1574.6
52.5°	1503.8	1500.3	1491.5	1480.7	1480.2
55°	1354.1	1349.1	1336.1	1328.4	1325.9
57.5°	1191.5	1181.4	1166.9	1155.6	1157.6
60°	1074.5	1064.5	1043.8	1038.6	1038.6
62.5°	961.7	949.7	928.9	921.8	925.8
65°	800.1	785.1	766.8	761.7	764.2
67.5°	653.4	639.9	620.1	620.1	618.1
70°	559.1	551.5	536.0	536.0	536.0
72.5°	475.0	471.4	460.1	460.0	458.0
75°	364.2	364.2	359.0	356.4	353.9
77.5°	272.9	273.9	271.3	268.7	264.1
80°	215.4	220.4	218.0	215.4	212.9
82.5°	162.1	167.1	166.7	162.1	161.6
85°	84.6	92.2	92.3	92.3	92.3
87.5°	22.6	30.6	32.8	32.9	34.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)