

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563553

Luminaire Tested: **SQ4-PP3-0U-125D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563553
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-125D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12698.8 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Direct

Input Watts (W): 140.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563553
CATALOG NUMBER: SQ4-PP3-0U-125D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563553

CATALOG NUMBER: SQ4-PP3-OU-125D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	105	101	97	107	103	99	96	98	95	93		95	92	90		91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77		84	79	76		81	77	74	72
3	92	81	74	67	89	80	73	67	77	71	66		74	69	64		72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56		66	60	56		64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49		60	53	48		58	52	48	46
6	72	59	50	44	70	58	49	43	56	49	43		54	48	43		53	47	42	40
7	66	53	45	39	65	52	44	39	51	44	38		49	43	38		48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34		45	39	34		44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31		42	35	31		41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28		39	33	28		38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15259	15259	15259
5°	15371	15277	15223
10°	15345	15236	15168
15°	15243	15160	15077
20°	15142	15057	14943
25°	14962	14859	14711
30°	14685	14608	14423
35°	14301	14203	14024
40°	13844	13757	13599
45°	13466	13371	13239
50°	12982	12899	12774
55°	12311	12147	12054
60°	11207	10886	10832
65°	9873	9462	9430
70°	8524	8172	8172
75°	7337	7234	7131
80°	6470	6546	6392
85°	5064	5522	5522



TEST NUMBER: P563553

CATALOG NUMBER: SQ4-PP3-0U-125D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	469.2	3.7
10°-20°	1339.6	10.5
20°-30°	2006.6	15.8
30°-40°	2353.6	18.5
40°-50°	2360.9	18.6
50°-60°	2014.1	15.9
60°-70°	1313.5	10.3
70°-80°	659.0	5.2
80°-90°	182.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3815.3	30.0
0°-40°	6168.9	48.6
0°-60°	10543.9	83.0
0°-90°	12698.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12698.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4962	4962	4962	4962	4962	
5°	4979	4932	4948	4931	4931	473
15°	4788	4741	4762	4744	4735	1351
25°	4409	4358	4379	4340	4335	2028
35°	3809	3771	3783	3740	3735	2379
45°	3096	3075	3074	3044	3044	2384
55°	2296	2288	2266	2252	2248	2040
65°	1357	1331	1300	1292	1296	1354
75°	618	618	609	604	600	670
85°	144	156	156	156	156	174
90°	0	0	0	0	0	



TEST NUMBER: P563553

CATALOG NUMBER: SQ4-PP3-0U-125D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4961.5	4961.5	4961.5	4961.5	4961.5
2.5°	4992.9	4952.0	4961.5	4954.1	4933.7
5°	4978.9	4932.2	4948.5	4931.1	4931.1
7.5°	4945.0	4894.0	4910.2	4892.8	4892.0
10°	4913.7	4862.7	4878.9	4861.4	4857.2
12.5°	4868.5	4817.5	4837.2	4816.3	4815.4
15°	4787.6	4740.8	4761.5	4743.9	4735.4
17.5°	4696.3	4645.3	4670.2	4645.8	4642.4
20°	4626.7	4575.7	4600.6	4565.8	4565.8
22.5°	4543.2	4492.2	4520.6	4475.4	4475.4
25°	4409.3	4358.3	4378.9	4339.6	4335.4
27.5°	4250.1	4200.0	4221.4	4177.1	4176.2
30°	4135.3	4088.6	4113.6	4065.7	4061.4
32.5°	4010.1	3966.7	3984.9	3937.0	3932.7
35°	3809.2	3770.9	3783.1	3739.5	3735.3
37.5°	3597.9	3558.8	3572.7	3535.2	3533.5
40°	3448.3	3422.8	3426.6	3395.9	3387.4
42.5°	3309.1	3280.2	3283.9	3253.4	3251.7
45°	3096.1	3074.8	3074.3	3043.9	3043.9
47.5°	2870.0	2853.8	2849.1	2823.8	2823.0
50°	2713.4	2700.7	2696.0	2674.2	2669.9
52.5°	2549.9	2544.0	2529.0	2510.8	2509.9
55°	2296.0	2287.5	2265.5	2252.4	2248.1
57.5°	2020.3	2003.3	1978.5	1959.5	1962.9
60°	1822.0	1805.0	1769.8	1761.1	1761.1
62.5°	1630.7	1610.2	1575.0	1563.0	1569.8
65°	1356.7	1331.2	1300.2	1291.6	1295.8
67.5°	1108.0	1085.0	1051.4	1051.4	1048.0
70°	948.0	935.2	908.8	908.8	908.8
72.5°	805.3	799.4	780.1	780.0	776.6
75°	617.5	617.5	608.8	604.3	600.1
77.5°	462.7	464.4	460.1	455.5	447.9
80°	365.3	373.8	369.6	365.2	360.9
82.5°	274.8	283.3	282.6	274.8	274.0
85°	143.5	156.3	156.5	156.5	156.5
87.5°	38.3	51.9	55.7	55.7	59.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)