

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563019

Luminaire Tested: **SQ4-PC3-125U-075D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563019
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-075D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11971.8 lumens
Efficiency: N/A
Efficacy: 136.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 87.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563019
CATALOG NUMBER: SQ4-PC3-125U-075D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563019

CATALOG NUMBER: SQ4-PC3-125U-075D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	83	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	52	46	43	41	34	33	31	26
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	59	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17	14
7	56	44	36	31	51	40	33	28	33	28	24	26	23	20	20	17	15	13
8	52	40	32	27	47	36	30	25	30	25	21	24	20	18	18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9904	9904	9904
5°	9979	9914	9878
10°	9954	9908	9880
15°	9903	9903	9893
20°	9837	9866	9866
25°	9744	9815	9784
30°	9626	9742	9700
35°	9482	9628	9561
40°	9325	9457	9361
45°	9156	9221	9079
50°	8916	8916	8774
55°	8634	8522	8393
60°	8216	8051	7923
65°	7594	7443	7377
70°	6650	6703	6676
75°	5349	5917	5953
80°	3801	5016	5069
85°	2315	4206	4206



TEST NUMBER: P563019

CATALOG NUMBER: SQ4-PC3-125U-075D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.4	1.3
10°-20°	437.3	3.7
20°-30°	662.3	5.5
30°-40°	794.0	6.6
40°-50°	809.6	6.8
50°-60°	706.7	5.9
60°-70°	505.9	4.2
70°-80°	260.6	2.2
80°-90°	68.6	0.6
90°-100°	548.9	4.6
100°-110°	1478.5	12.4
110°-120°	1551.7	13.0
120°-130°	1259.2	10.5
130°-140°	987.5	8.2
140°-150°	758.2	6.3
150°-160°	545.1	4.6
160°-170°	333.0	2.8
170°-180°	112.3	0.9
0°-30°	1252.0	10.5
0°-40°	2045.9	17.1
0°-60°	3562.2	29.8
0°-90°	4397.3	36.7
90°-120°	3579.1	29.9
90°-150°	6584.0	55.0
90°-180°	7574.0	63.3
0°-180°	11971.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1616	1600	1606	1601	1600	153
15°	1555	1542	1555	1555	1554	438
25°	1436	1426	1446	1442	1442	661
35°	1263	1260	1282	1273	1273	790
45°	1053	1050	1060	1047	1044	810
55°	805	795	795	783	783	718
65°	522	510	511	507	507	516
75°	225	235	249	250	250	243
85°	33	50	60	61	60	45
90°	3	9	18	19	19	7
95°	84	298	900	460	318	87
105°	274	426	1635	2446	2296	288
115°	483	591	1362	2631	2976	475
125°	659	757	1223	2066	2432	589
135°	794	886	1188	1667	1888	613
145°	918	989	1173	1425	1530	576
155°	1042	1080	1163	1279	1320	480
165°	1130	1143	1167	1214	1220	319
175°	1175	1173	1169	1185	1182	112
180°	1173	1173	1173	1173	1173	

TEST NUMBER: P563019

CATALOG NUMBER: SQ4-PC3-125U-075D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1619.8	1605.8	1610.2	1606.5	1600.7
5°	1616.2	1600.2	1605.7	1601.2	1599.8
7.5°	1604.6	1588.5	1595.9	1592.9	1591.4
10°	1593.8	1577.8	1586.4	1583.4	1581.9
12.5°	1579.5	1564.6	1574.4	1571.5	1571.2
15°	1555.1	1541.9	1555.1	1555.0	1553.6
17.5°	1524.3	1512.4	1526.4	1527.3	1526.4
20°	1502.9	1489.8	1507.3	1505.9	1507.3
22.5°	1476.6	1465.8	1484.7	1480.8	1482.3
25°	1435.8	1425.6	1446.2	1441.7	1441.7
27.5°	1387.5	1380.2	1402.7	1397.9	1397.9
30°	1355.3	1348.0	1371.7	1365.7	1365.7
32.5°	1319.5	1314.5	1337.1	1329.9	1329.9
35°	1262.8	1259.9	1282.2	1273.3	1273.3
37.5°	1204.4	1201.8	1222.0	1211.2	1207.7
40°	1161.4	1160.0	1177.8	1165.9	1165.9
42.5°	1118.5	1117.1	1132.5	1118.2	1118.2
45°	1052.6	1049.7	1060.1	1046.6	1043.7
47.5°	980.7	977.8	984.3	969.7	968.2
50°	931.8	928.9	931.8	918.4	916.9
52.5°	881.7	876.5	877.0	863.5	863.3
55°	805.1	794.9	794.7	782.7	782.7
57.5°	724.0	710.6	711.8	701.6	700.1
60°	667.9	653.4	654.5	645.5	644.1
62.5°	613.1	596.2	599.7	589.5	589.2
65°	521.8	510.2	511.4	506.9	506.9
67.5°	434.2	423.4	431.2	427.6	427.3
70°	369.8	362.5	372.7	372.7	371.2
72.5°	310.1	309.8	322.6	322.7	323.5
75°	225.1	235.3	249.0	250.5	250.5
77.5°	150.3	168.4	183.4	184.0	183.7
80°	107.3	127.8	141.6	144.6	143.1
82.5°	72.8	94.3	105.9	108.8	107.3
85°	32.8	50.3	59.6	61.1	59.6
87.5°	10.1	21.8	27.4	27.7	25.4
90°	3.0	8.8	17.9	19.4	19.4
92.5°	36.5	128.8	254.7	122.6	85.2
95°	83.7	298.5	899.8	460.1	318.4
97.5°	133.6	341.7	1411.3	1179.0	889.0
100°	171.9	359.0	1573.9	1646.7	1366.1
102.5°	209.0	383.2	1627.7	1997.0	1766.7
105°	273.5	425.5	1635.2	2446.3	2295.8
107.5°	334.5	470.1	1565.5	2677.2	2716.1
110°	375.2	503.8	1502.1	2748.9	2890.7



TEST NUMBER: P563019

CATALOG NUMBER: SQ4-PC3-125U-075D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	418.2	537.5	1441.2	2733.1	2966.0
115°	482.8	590.9	1361.6	2631.0	2975.9
117.5°	541.7	643.1	1300.1	2468.1	2852.1
120°	579.9	677.8	1269.0	2351.1	2745.7
122.5°	613.4	710.2	1246.3	2231.5	2624.9
125°	659.1	757.1	1222.6	2066.5	2431.8
127.5°	703.1	799.5	1207.7	1920.9	2247.1
130°	729.4	825.9	1201.7	1837.5	2123.9
132.5°	755.7	851.0	1195.7	1764.0	2027.1
135°	793.7	885.7	1188.3	1667.1	1887.8
137.5°	829.8	918.1	1184.4	1584.9	1766.1
140°	855.0	939.7	1180.8	1534.3	1697.9
142.5°	881.3	960.2	1178.4	1487.0	1625.0
145°	917.7	989.3	1173.3	1425.3	1530.5
147.5°	957.2	1019.4	1168.2	1373.4	1456.1
150°	983.5	1037.6	1165.8	1340.8	1409.5
152.5°	1007.4	1054.5	1164.6	1314.2	1370.0
155°	1041.8	1079.8	1162.9	1278.9	1319.8
157.5°	1072.0	1101.5	1163.2	1254.1	1281.5
160°	1091.1	1116.0	1164.3	1239.5	1260.0
162.5°	1107.8	1128.0	1165.5	1227.5	1242.1
165°	1130.0	1143.1	1167.3	1213.8	1219.7
167.5°	1147.9	1155.5	1168.8	1203.3	1205.6
170°	1159.9	1162.8	1168.8	1197.2	1197.2
172.5°	1167.0	1167.6	1170.0	1191.3	1191.3
175°	1174.8	1173.3	1168.8	1185.2	1182.3
177.5°	1178.1	1175.8	1169.7	1179.2	1176.9
180°	1173.3	1173.3	1173.3	1173.3	1173.3

(END OF REPORT)