

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563187

Luminaire Tested: **SQ4-PP3-025U-050D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563187
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-050D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4418.1 lumens
Efficiency: N/A
Efficacy: 126.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 34.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563187
CATALOG NUMBER: SQ4-PP3-025U-050D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563187

CATALOG NUMBER: SQ4-PP3-025U-050D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	90	96	92	89	86	82	79	77	72	71	69	64	62	61	57
2	93	85	79	74	87	81	75	71	72	68	64	64	61	58	56	54	52	48
3	85	75	68	62	80	71	65	59	64	58	54	57	53	49	50	47	44	41
4	78	67	59	53	73	63	56	51	57	51	46	51	46	42	45	41	38	35
5	72	60	51	45	67	57	49	44	51	45	40	46	41	37	41	37	33	31
6	66	54	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30	27
7	61	49	40	35	57	46	39	34	42	36	31	38	32	29	34	29	26	24
8	57	44	36	31	53	42	35	30	38	32	28	34	29	26	31	27	24	21
9	53	40	33	28	50	39	32	27	35	29	25	32	27	23	29	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7097	7097	7097
5°	7150	7106	7081
10°	7138	7087	7056
15°	7091	7052	7013
20°	7044	7004	6951
25°	6960	6912	6843
30°	6831	6795	6709
35°	6652	6607	6523
40°	6439	6399	6325
45°	6264	6219	6158
50°	6039	6000	5942
55°	5726	5650	5607
60°	5213	5063	5039
65°	4592	4401	4387
70°	3965	3802	3802
75°	3413	3365	3318
80°	3011	3046	2972
85°	2357	2569	2569



TEST NUMBER: P563187

CATALOG NUMBER: SQ4-PP3-025U-050D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.1	2.5
10°-20°	311.6	7.1
20°-30°	466.7	10.6
30°-40°	547.4	12.4
40°-50°	549.1	12.4
50°-60°	468.4	10.6
60°-70°	305.5	6.9
70°-80°	153.3	3.5
80°-90°	43.6	1.0
90°-100°	110.0	2.5
100°-110°	289.3	6.5
110°-120°	300.0	6.8
120°-130°	240.6	5.4
130°-140°	188.8	4.3
140°-150°	144.9	3.3
150°-160°	104.4	2.4
160°-170°	63.9	1.4
170°-180°	21.6	0.5
0°-30°	887.4	20.1
0°-40°	1434.7	32.5
0°-60°	2452.3	55.5
0°-90°	2954.6	66.9
90°-120°	699.3	15.8
90°-150°	1273.6	28.8
90°-180°	1463.0	33.1
0°-180°	4418.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1154	1154	1154	1154	1154	
5°	1158	1147	1151	1147	1147	110
15°	1114	1103	1107	1103	1101	314
25°	1026	1014	1018	1009	1008	472
35°	886	877	880	870	869	553
45°	720	715	715	708	708	554
55°	534	532	527	524	523	475
65°	316	310	302	300	301	315
75°	144	144	142	141	140	156
85°	33	36	36	36	36	39
90°	1	4	12	6	6	2
95°	14	57	190	98	67	16
105°	52	79	320	486	453	55
115°	93	112	256	511	583	91
125°	129	144	233	394	465	114
135°	153	169	226	318	360	119
145°	178	189	223	271	292	112
155°	201	207	223	245	252	92
165°	217	220	223	232	234	61
175°	226	226	224	227	227	21
180°	226	226	226	226	226	

TEST NUMBER: P563187

CATALOG NUMBER: SQ4-PP3-025U-050D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1153.9	1153.9	1153.9	1153.9	1153.9
2.5°	1161.2	1151.7	1153.9	1152.2	1147.5
5°	1158.0	1147.1	1150.9	1146.9	1146.9
7.5°	1150.1	1138.2	1142.0	1138.0	1137.8
10°	1142.8	1130.9	1134.7	1130.7	1129.7
12.5°	1132.3	1120.4	1125.0	1120.2	1120.0
15°	1113.5	1102.6	1107.4	1103.3	1101.3
17.5°	1092.2	1080.4	1086.2	1080.5	1079.7
20°	1076.1	1064.2	1070.0	1061.9	1061.9
22.5°	1056.6	1044.8	1051.4	1040.9	1040.9
25°	1025.5	1013.6	1018.4	1009.3	1008.3
27.5°	988.5	976.8	981.8	971.5	971.3
30°	961.8	950.9	956.7	945.6	944.6
32.5°	932.7	922.6	926.8	915.6	914.7
35°	885.9	877.0	879.9	869.7	868.7
37.5°	836.8	827.7	830.9	822.2	821.8
40°	802.0	796.1	796.9	789.8	787.8
42.5°	769.6	762.9	763.8	756.7	756.3
45°	720.1	715.1	715.0	707.9	707.9
47.5°	667.5	663.7	662.6	656.8	656.6
50°	631.1	628.1	627.0	621.9	621.0
52.5°	593.0	591.7	588.2	583.9	583.7
55°	534.0	532.0	526.9	523.9	522.9
57.5°	469.9	465.9	460.2	455.7	456.5
60°	423.8	419.8	411.6	409.6	409.6
62.5°	379.3	374.5	366.3	363.5	365.1
65°	315.5	309.6	302.4	300.4	301.4
67.5°	257.7	252.3	244.5	244.5	243.7
70°	220.5	217.5	211.4	211.4	211.4
72.5°	187.3	185.9	181.4	181.4	180.6
75°	143.6	143.6	141.6	140.6	139.6
77.5°	107.6	108.0	107.0	105.9	104.2
80°	85.0	86.9	86.0	84.9	83.9
82.5°	63.9	65.9	65.7	63.9	63.7
85°	33.4	36.3	36.4	36.4	36.4
87.5°	9.2	12.9	15.3	14.1	14.9
90°	1.4	4.3	11.6	5.8	5.8
92.5°	6.1	29.3	64.8	28.7	18.5
95°	14.5	56.9	189.6	97.7	66.6
97.5°	25.2	62.5	283.7	225.6	166.2
100°	33.3	67.3	312.6	316.8	246.0
102.5°	40.2	71.9	320.7	394.6	334.0
105°	52.1	79.0	319.9	485.6	453.0
107.5°	64.3	89.2	301.6	532.8	540.7
110°	72.4	95.0	286.6	545.0	578.9



TEST NUMBER: P563187

CATALOG NUMBER: SQ4-PP3-025U-050D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	80.5	102.0	272.7	537.3	589.4
115°	92.6	112.4	256.2	511.1	583.3
117.5°	104.5	122.6	244.9	474.8	554.9
120°	111.4	128.4	240.3	450.4	528.3
122.5°	118.4	135.4	236.8	426.1	502.8
125°	128.8	144.4	233.0	393.8	464.6
127.5°	137.2	153.1	229.8	367.8	427.5
130°	141.8	158.8	228.7	351.5	406.7
132.5°	146.5	163.5	227.5	337.5	387.0
135°	153.4	169.0	225.8	317.9	360.4
137.5°	160.7	175.9	225.5	303.3	338.1
140°	166.4	180.6	224.3	291.7	324.2
142.5°	171.1	184.1	224.3	283.4	311.5
145°	178.0	189.3	222.9	271.1	292.4
147.5°	185.0	196.0	222.9	260.9	278.5
150°	189.6	199.5	222.9	255.1	269.2
152.5°	194.2	201.9	222.9	250.3	261.1
155°	201.2	206.8	222.9	244.8	251.8
157.5°	206.4	211.8	222.9	239.8	244.9
160°	209.9	214.1	222.9	237.4	240.3
162.5°	213.3	216.5	222.9	235.1	237.9
165°	217.1	219.9	222.9	231.6	234.5
167.5°	220.6	222.0	224.3	230.2	231.3
170°	222.9	224.3	224.3	230.1	230.1
172.5°	224.0	224.3	224.3	228.9	227.8
175°	225.8	225.8	224.3	227.2	227.2
177.5°	225.8	225.8	224.6	226.9	225.8
180°	225.8	225.8	225.8	225.8	225.8

(END OF REPORT)