

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563211

Luminaire Tested: **SQ4-PP3-025U-075D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563211
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-075D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5817.7 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563211
CATALOG NUMBER: SQ4-PP3-025U-075D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563211

CATALOG NUMBER: SQ4-PP3-025U-075D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75
1	104	99	95	92	98	95	91	88	86	83	81	78	76	74	70	69	67	64
2	95	87	81	76	90	83	77	73	76	71	67	69	65	62	62	60	57	54
3	87	77	69	63	82	73	67	61	67	61	57	61	57	53	55	52	49	46
4	79	68	60	54	75	65	58	52	60	54	49	54	49	45	50	46	42	39
5	73	61	53	46	69	58	51	45	54	47	42	49	44	40	45	40	37	34
6	67	55	46	40	64	53	45	39	48	42	37	44	39	35	41	36	33	30
7	62	50	41	36	59	48	40	35	44	37	33	40	35	31	37	33	29	27
8	58	45	37	32	55	44	36	31	40	34	29	37	32	28	34	29	26	24
9	54	41	34	28	51	40	33	28	37	31	26	34	29	25	32	27	24	22
10	51	38	31	26	48	37	30	25	34	28	24	32	26	23	29	25	21	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10461	10461	10461
5°	10538	10473	10436
10°	10520	10445	10399
15°	10450	10393	10337
20°	10381	10322	10244
25°	10258	10187	10086
30°	10068	10015	9888
35°	9805	9737	9614
40°	9491	9431	9324
45°	9232	9167	9076
50°	8900	8844	8758
55°	8439	8328	8264
60°	7684	7463	7426
65°	6769	6487	6465
70°	5843	5602	5602
75°	5031	4960	4888
80°	4435	4488	4382
85°	3472	3790	3790



TEST NUMBER: P563211

CATALOG NUMBER: SQ4-PP3-025U-075D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	2.8
10°-20°	459.2	7.9
20°-30°	687.8	11.8
30°-40°	806.8	13.9
40°-50°	809.3	13.9
50°-60°	690.4	11.9
60°-70°	450.3	7.7
70°-80°	225.9	3.9
80°-90°	63.7	1.1
90°-100°	110.0	1.9
100°-110°	289.3	5.0
110°-120°	300.0	5.2
120°-130°	240.6	4.1
130°-140°	188.8	3.2
140°-150°	144.9	2.5
150°-160°	104.4	1.8
160°-170°	63.9	1.1
170°-180°	21.6	0.4
0°-30°	1307.9	22.5
0°-40°	2114.6	36.3
0°-60°	3614.4	62.1
0°-90°	4354.2	74.8
90°-120°	699.3	12.0
90°-150°	1273.6	21.9
90°-180°	1463.0	25.1
0°-180°	5817.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1701	1701	1701	1701	1701	
5°	1707	1691	1696	1690	1690	162
15°	1641	1625	1632	1626	1623	463
25°	1512	1494	1501	1488	1486	695
35°	1306	1293	1297	1282	1280	816
45°	1061	1054	1054	1043	1043	817
55°	787	784	777	772	771	699
65°	465	456	446	443	444	464
75°	212	212	209	207	206	230
85°	49	54	54	54	54	58
90°	1	4	12	6	6	3
95°	14	57	190	98	67	16
105°	52	79	320	486	453	55
115°	93	112	256	511	583	91
125°	129	144	233	394	465	114
135°	153	169	226	318	360	119
145°	178	189	223	271	292	112
155°	201	207	223	245	252	92
165°	217	220	223	232	234	61
175°	226	226	224	227	227	21
180°	226	226	226	226	226	

TEST NUMBER: P563211

CATALOG NUMBER: SQ4-PP3-025U-075D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1700.8	1700.8	1700.8	1700.8	1700.8
2.5°	1711.5	1697.5	1700.8	1698.2	1691.2
5°	1706.7	1690.7	1696.3	1690.3	1690.3
7.5°	1695.1	1677.6	1683.2	1677.2	1676.9
10°	1684.4	1666.9	1672.4	1666.5	1665.0
12.5°	1668.9	1651.4	1658.1	1651.0	1650.7
15°	1641.1	1625.1	1632.2	1626.2	1623.3
17.5°	1609.8	1592.4	1600.9	1592.5	1591.4
20°	1586.0	1568.5	1577.0	1565.1	1565.1
22.5°	1557.4	1539.9	1549.6	1534.1	1534.1
25°	1511.5	1494.0	1501.0	1487.6	1486.1
27.5°	1456.9	1439.7	1447.1	1431.9	1431.6
30°	1417.6	1401.5	1410.1	1393.7	1392.2
32.5°	1374.6	1359.8	1366.0	1349.6	1348.1
35°	1305.8	1292.6	1296.8	1281.9	1280.4
37.5°	1233.3	1219.9	1224.7	1211.8	1211.3
40°	1182.0	1173.3	1174.6	1164.1	1161.2
42.5°	1134.3	1124.4	1125.7	1115.2	1114.7
45°	1061.3	1054.0	1053.8	1043.4	1043.4
47.5°	983.8	978.3	976.6	968.0	967.7
50°	930.1	925.8	924.2	916.7	915.2
52.5°	874.1	872.0	866.9	860.7	860.4
55°	787.0	784.1	776.6	772.1	770.6
57.5°	692.5	686.7	678.2	671.7	672.9
60°	624.6	618.7	606.7	603.7	603.7
62.5°	559.0	552.0	539.9	535.8	538.1
65°	465.1	456.3	445.7	442.7	444.2
67.5°	379.8	371.9	360.4	360.4	359.2
70°	324.9	320.6	311.5	311.5	311.5
72.5°	276.1	274.0	267.4	267.4	266.2
75°	211.7	211.7	208.7	207.2	205.7
77.5°	158.6	159.2	157.7	156.2	153.5
80°	125.2	128.1	126.7	125.2	123.7
82.5°	94.2	97.1	96.9	94.2	93.9
85°	49.2	53.6	53.7	53.7	53.7
87.5°	13.4	18.6	21.4	20.3	21.4
90°	1.4	4.3	11.6	5.8	5.8
92.5°	6.1	29.3	64.8	28.7	18.5
95°	14.5	56.9	189.6	97.7	66.6
97.5°	25.2	62.5	283.7	225.6	166.2
100°	33.3	67.3	312.6	316.8	246.0
102.5°	40.2	71.9	320.7	394.6	334.0
105°	52.1	79.0	319.9	485.6	453.0
107.5°	64.3	89.2	301.6	532.8	540.7
110°	72.4	95.0	286.6	545.0	578.9



TEST NUMBER: P563211

CATALOG NUMBER: SQ4-PP3-025U-075D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	80.5	102.0	272.7	537.3	589.4
115°	92.6	112.4	256.2	511.1	583.3
117.5°	104.5	122.6	244.9	474.8	554.9
120°	111.4	128.4	240.3	450.4	528.3
122.5°	118.4	135.4	236.8	426.1	502.8
125°	128.8	144.4	233.0	393.8	464.6
127.5°	137.2	153.1	229.8	367.8	427.5
130°	141.8	158.8	228.7	351.5	406.7
132.5°	146.5	163.5	227.5	337.5	387.0
135°	153.4	169.0	225.8	317.9	360.4
137.5°	160.7	175.9	225.5	303.3	338.1
140°	166.4	180.6	224.3	291.7	324.2
142.5°	171.1	184.1	224.3	283.4	311.5
145°	178.0	189.3	222.9	271.1	292.4
147.5°	185.0	196.0	222.9	260.9	278.5
150°	189.6	199.5	222.9	255.1	269.2
152.5°	194.2	201.9	222.9	250.3	261.1
155°	201.2	206.8	222.9	244.8	251.8
157.5°	206.4	211.8	222.9	239.8	244.9
160°	209.9	214.1	222.9	237.4	240.3
162.5°	213.3	216.5	222.9	235.1	237.9
165°	217.1	219.9	222.9	231.6	234.5
167.5°	220.6	222.0	224.3	230.2	231.3
170°	222.9	224.3	224.3	230.1	230.1
172.5°	224.0	224.3	224.3	228.9	227.8
175°	225.8	225.8	224.3	227.2	227.2
177.5°	225.8	225.8	224.6	226.9	225.8
180°	225.8	225.8	225.8	225.8	225.8

(END OF REPORT)