

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563649

Luminaire Tested: **SQ4-PP3-100U-125D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563649
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-125D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 23171.4 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 214.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563649

CATALOG NUMBER: SQ4-PP3-100U-125D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563649

CATALOG NUMBER: SQ4-PP3-100U-125D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	34
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22	20
8	55	43	35	29	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	23	20	24	21	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15259	15259	15259
5°	15371	15277	15223
10°	15345	15236	15168
15°	15243	15160	15077
20°	15142	15057	14943
25°	14962	14859	14711
30°	14685	14608	14423
35°	14301	14203	14024
40°	13844	13757	13599
45°	13466	13371	13239
50°	12982	12899	12774
55°	12311	12147	12054
60°	11207	10886	10832
65°	9873	9462	9430
70°	8524	8172	8172
75°	7337	7234	7131
80°	6470	6546	6392
85°	5064	5522	5522



TEST NUMBER: P563649

CATALOG NUMBER: SQ4-PP3-100U-125D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	469.2	2.0
10°-20°	1339.6	5.8
20°-30°	2006.6	8.7
30°-40°	2353.6	10.2
40°-50°	2360.9	10.2
50°-60°	2014.1	8.7
60°-70°	1313.5	5.7
70°-80°	659.0	2.8
80°-90°	185.7	0.8
90°-100°	754.6	3.3
100°-110°	2083.1	9.0
110°-120°	2148.4	9.3
120°-130°	1726.4	7.5
130°-140°	1356.8	5.9
140°-150°	1040.6	4.5
150°-160°	747.9	3.2
160°-170°	457.3	2.0
170°-180°	154.2	0.7
0°-30°	3815.3	16.5
0°-40°	6168.9	26.6
0°-60°	10543.9	45.5
0°-90°	12702.2	54.8
90°-120°	4986.1	21.5
90°-150°	9109.9	39.3
90°-180°	10469.0	45.2
0°-180°	23171.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4962	4962	4962	4962	4962	
5°	4979	4932	4948	4931	4931	473
15°	4788	4741	4762	4744	4735	1351
25°	4409	4358	4379	4340	4335	2028
35°	3809	3771	3783	3740	3735	2379
45°	3096	3075	3074	3044	3044	2384
55°	2296	2288	2266	2252	2248	2040
65°	1357	1331	1300	1292	1296	1354
75°	618	618	609	604	600	670
85°	144	156	156	156	156	169
90°	5	10	21	23	26	13
95°	111	408	1369	563	366	119
105°	371	573	2292	3499	3295	395
115°	665	804	1846	3654	4156	654
125°	913	1039	1673	2832	3323	812
135°	1098	1217	1627	2293	2586	850
145°	1274	1362	1606	1952	2101	797
155°	1436	1484	1593	1752	1807	662
165°	1555	1575	1601	1663	1676	438
175°	1611	1614	1604	1627	1622	153
180°	1611	1611	1611	1611	1611	

TEST NUMBER: P563649

CATALOG NUMBER: SQ4-PP3-100U-125D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4961.5	4961.5	4961.5	4961.5	4961.5
2.5°	4992.9	4952.0	4961.5	4954.1	4933.7
5°	4978.9	4932.2	4948.5	4931.1	4931.1
7.5°	4945.0	4894.0	4910.2	4892.8	4892.0
10°	4913.7	4862.7	4878.9	4861.4	4857.2
12.5°	4868.5	4817.5	4837.2	4816.3	4815.4
15°	4787.6	4740.8	4761.5	4743.9	4735.4
17.5°	4696.3	4645.3	4670.2	4645.8	4642.4
20°	4626.7	4575.7	4600.6	4565.8	4565.8
22.5°	4543.2	4492.2	4520.6	4475.4	4475.4
25°	4409.3	4358.3	4378.9	4339.6	4335.4
27.5°	4250.1	4200.0	4221.4	4177.1	4176.2
30°	4135.3	4088.6	4113.6	4065.7	4061.4
32.5°	4010.1	3966.7	3984.9	3937.0	3932.7
35°	3809.2	3770.9	3783.1	3739.5	3735.3
37.5°	3597.9	3558.8	3572.7	3535.2	3533.5
40°	3448.3	3422.8	3426.6	3395.9	3387.4
42.5°	3309.1	3280.2	3283.9	3253.4	3251.7
45°	3096.1	3074.8	3074.3	3043.9	3043.9
47.5°	2870.0	2853.8	2849.1	2823.8	2823.0
50°	2713.4	2700.7	2696.0	2674.2	2669.9
52.5°	2549.9	2544.0	2529.0	2510.8	2509.9
55°	2296.0	2287.5	2265.5	2252.4	2248.1
57.5°	2020.3	2003.3	1978.5	1959.5	1962.9
60°	1822.0	1805.0	1769.8	1761.1	1761.1
62.5°	1630.7	1610.2	1575.0	1563.0	1569.8
65°	1356.7	1331.2	1300.2	1291.6	1295.8
67.5°	1108.0	1085.0	1051.4	1051.4	1048.0
70°	948.0	935.2	908.8	908.8	908.8
72.5°	805.3	799.4	780.1	780.0	776.6
75°	617.5	617.5	608.8	604.3	600.1
77.5°	462.7	464.4	460.1	455.5	447.9
80°	365.3	373.8	369.6	365.2	360.9
82.5°	274.8	283.3	282.6	274.8	274.0
85°	143.5	156.3	156.5	156.5	156.5
87.5°	39.3	53.9	59.8	60.4	64.3
90°	5.2	10.2	20.6	23.3	25.8
92.5°	46.4	192.6	344.4	125.7	98.0
95°	110.9	408.3	1368.9	562.7	366.1
97.5°	183.6	457.3	2027.9	1561.3	1130.7
100°	237.2	486.7	2271.3	2287.3	1858.8
102.5°	288.7	520.1	2318.7	2826.1	2419.8
105°	371.2	572.9	2291.9	3498.9	3294.7
107.5°	458.9	638.4	2164.0	3823.4	3898.0
110°	520.8	682.1	2065.0	3893.2	4135.2



TEST NUMBER: P563649

CATALOG NUMBER: SQ4-PP3-100U-125D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	576.5	731.7	1972.2	3838.1	4195.0
115°	665.1	803.8	1845.9	3654.2	4155.8
117.5°	742.5	880.6	1762.9	3395.4	3966.1
120°	794.0	930.2	1729.9	3220.2	3794.9
122.5°	843.5	973.6	1703.1	3056.5	3601.0
125°	912.6	1038.7	1673.2	2831.6	3323.1
127.5°	971.4	1097.4	1655.6	2641.3	3065.3
130°	1010.6	1136.6	1647.4	2524.9	2910.6
132.5°	1047.7	1167.7	1639.1	2427.2	2776.6
135°	1098.2	1216.7	1626.7	2293.4	2585.8
137.5°	1155.0	1262.9	1620.6	2181.0	2430.6
140°	1185.9	1291.8	1616.4	2106.1	2325.4
142.5°	1221.0	1318.8	1612.3	2039.5	2232.6
145°	1273.6	1361.8	1606.1	1952.4	2101.1
147.5°	1324.1	1401.2	1600.5	1878.9	1994.4
150°	1361.2	1424.2	1598.4	1835.1	1928.4
152.5°	1390.1	1449.1	1596.3	1797.6	1874.8
155°	1436.0	1483.9	1593.2	1751.8	1807.2
157.5°	1478.3	1515.1	1593.7	1718.4	1756.2
160°	1503.0	1535.8	1595.8	1699.6	1727.3
162.5°	1523.6	1552.4	1597.9	1682.9	1704.6
165°	1554.6	1574.7	1601.0	1663.1	1675.7
167.5°	1578.3	1590.4	1603.5	1651.1	1655.1
170°	1590.7	1600.7	1603.5	1644.8	1644.8
172.5°	1601.0	1607.0	1603.5	1636.5	1634.5
175°	1611.3	1613.8	1603.5	1626.6	1621.6
177.5°	1615.4	1613.4	1603.0	1617.4	1613.3
180°	1611.3	1611.3	1611.3	1611.3	1611.3

(END OF REPORT)