

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563283

Luminaire Tested: **SQ4-PP3-050U-050D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563283  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-050U-050D-840-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5973.1 lumens  
Efficiency: N/A  
Efficacy: 133.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 44.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563283  
CATALOG NUMBER: SQ4-PP3-050U-050D-840-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563283

CATALOG NUMBER: SQ4-PP3-050U-050D-840-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49				
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42				
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	36				
3	82	72	65	59	75	67	61	55	57	52	48	48	44	41	39	36	34	30				
4	75	64	56	50	69	59	52	47	51	45	41	42	38	35	35	32	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23				
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7097	7097	7097
5°	7150	7106	7081
10°	7138	7087	7056
15°	7091	7052	7013
20°	7044	7004	6951
25°	6960	6912	6843
30°	6831	6795	6709
35°	6652	6607	6523
40°	6439	6399	6325
45°	6264	6219	6158
50°	6039	6000	5942
55°	5726	5650	5607
60°	5213	5063	5039
65°	4592	4401	4387
70°	3965	3802	3802
75°	3413	3365	3318
80°	3011	3046	2972
85°	2357	2569	2569



TEST NUMBER: P563283

CATALOG NUMBER: SQ4-PP3-050U-050D-840-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	109.1	1.8
10°-20°	311.6	5.2
20°-30°	466.7	7.8
30°-40°	547.4	9.2
40°-50°	549.1	9.2
50°-60°	468.4	7.8
60°-70°	305.5	5.1
70°-80°	153.3	2.6
80°-90°	44.2	0.7
90°-100°	221.9	3.7
100°-110°	602.8	10.1
110°-120°	619.7	10.4
120°-130°	495.5	8.3
130°-140°	389.3	6.5
140°-150°	298.5	5.0
150°-160°	214.7	3.6
160°-170°	131.3	2.2
170°-180°	44.2	0.7
0°-30°	887.4	14.9
0°-40°	1434.7	24.0
0°-60°	2452.3	41.1
0°-90°	2955.2	49.5
90°-120°	1444.4	24.2
90°-150°	2627.7	44.0
90°-180°	3018.0	50.5
0°-180°	5973.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1154	1154	1154	1154	1154	
5°	1158	1147	1151	1147	1147	110
15°	1114	1103	1107	1103	1101	314
25°	1026	1014	1018	1009	1008	472
35°	886	877	880	870	869	553
45°	720	715	715	708	708	554
55°	534	532	527	524	523	475
65°	316	310	302	300	301	315
75°	144	144	142	141	140	156
85°	33	36	36	36	36	39
90°	2	6	10	13	13	4
95°	33	121	386	168	113	35
105°	107	167	663	1009	950	114
115°	190	231	531	1056	1202	188
125°	262	298	480	809	954	233
135°	315	350	467	659	743	244
145°	364	390	461	560	602	229
155°	412	426	458	503	517	190
165°	446	452	459	479	480	126
175°	462	464	461	467	465	44
180°	462	462	462	462	462	

TEST NUMBER: P563283

CATALOG NUMBER: SQ4-PP3-050U-050D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1153.9	1153.9	1153.9	1153.9	1153.9
2.5°	1161.2	1151.7	1153.9	1152.2	1147.5
5°	1158.0	1147.1	1150.9	1146.9	1146.9
7.5°	1150.1	1138.2	1142.0	1138.0	1137.8
10°	1142.8	1130.9	1134.7	1130.7	1129.7
12.5°	1132.3	1120.4	1125.0	1120.2	1120.0
15°	1113.5	1102.6	1107.4	1103.3	1101.3
17.5°	1092.2	1080.4	1086.2	1080.5	1079.7
20°	1076.1	1064.2	1070.0	1061.9	1061.9
22.5°	1056.6	1044.8	1051.4	1040.9	1040.9
25°	1025.5	1013.6	1018.4	1009.3	1008.3
27.5°	988.5	976.8	981.8	971.5	971.3
30°	961.8	950.9	956.7	945.6	944.6
32.5°	932.7	922.6	926.8	915.6	914.7
35°	885.9	877.0	879.9	869.7	868.7
37.5°	836.8	827.7	830.9	822.2	821.8
40°	802.0	796.1	796.9	789.8	787.8
42.5°	769.6	762.9	763.8	756.7	756.3
45°	720.1	715.1	715.0	707.9	707.9
47.5°	667.5	663.7	662.6	656.8	656.6
50°	631.1	628.1	627.0	621.9	621.0
52.5°	593.0	591.7	588.2	583.9	583.7
55°	534.0	532.0	526.9	523.9	522.9
57.5°	469.9	465.9	460.2	455.7	456.5
60°	423.8	419.8	411.6	409.6	409.6
62.5°	379.3	374.5	366.3	363.5	365.1
65°	315.5	309.6	302.4	300.4	301.4
67.5°	257.7	252.3	244.5	244.5	243.7
70°	220.5	217.5	211.4	211.4	211.4
72.5°	187.3	185.9	181.4	181.4	180.6
75°	143.6	143.6	141.6	140.6	139.6
77.5°	107.6	108.0	107.0	105.9	104.2
80°	85.0	86.9	86.0	84.9	83.9
82.5°	63.9	65.9	65.7	63.9	63.7
85°	33.4	36.3	36.4	36.4	36.4
87.5°	9.2	13.2	15.0	15.6	16.4
90°	1.5	5.8	10.4	13.4	13.4
92.5°	13.4	60.8	105.5	45.3	38.3
95°	32.7	121.3	386.4	168.2	113.0
97.5°	54.1	134.0	592.4	460.9	323.7
100°	68.4	142.5	655.4	664.4	536.5
102.5°	82.6	150.9	672.1	821.7	708.9
105°	107.0	166.6	662.9	1009.3	949.7
107.5°	132.3	184.9	624.5	1106.1	1122.7
110°	150.1	198.1	596.0	1125.2	1196.4



TEST NUMBER: P563283

CATALOG NUMBER: SQ4-PP3-050U-050D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	165.6	211.2	567.4	1109.4	1216.6
115°	190.2	230.9	530.6	1055.6	1202.4
117.5°	213.4	252.4	507.1	979.3	1144.7
120°	228.9	266.7	496.4	928.2	1092.4
122.5°	242.0	279.7	489.3	876.9	1035.3
125°	261.6	297.9	480.1	808.8	954.2
127.5°	279.1	315.2	475.0	757.2	881.9
130°	289.8	324.7	472.6	724.8	836.7
132.5°	300.5	335.4	470.2	697.2	796.3
135°	315.1	350.0	466.7	658.8	743.1
137.5°	330.8	362.5	464.9	624.9	695.9
140°	340.3	370.9	463.7	603.4	667.3
142.5°	349.9	378.0	462.5	586.5	640.0
145°	364.1	390.3	460.7	559.8	601.9
147.5°	380.2	402.6	459.2	538.8	571.9
150°	390.9	409.8	459.2	526.7	552.9
152.5°	399.2	415.8	458.1	515.9	537.4
155°	411.7	426.2	457.8	502.7	517.2
157.5°	423.9	435.2	457.8	493.7	504.7
160°	431.0	441.2	457.8	487.7	496.4
162.5°	438.1	446.0	458.9	482.9	489.3
165°	445.9	451.7	459.2	478.6	480.1
167.5°	453.9	456.8	460.7	473.5	474.7
170°	456.3	459.2	460.7	471.1	471.1
172.5°	458.6	460.4	460.7	468.8	468.8
175°	462.2	463.7	460.7	466.6	465.2
177.5°	463.4	463.4	459.8	464.5	462.2
180°	462.2	462.2	462.2	462.2	462.2

(END OF REPORT)