

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563721

Luminaire Tested: **SQ4-PP3-125U-100D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563721  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-125U-100D-935-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 22987.3 lumens  
Efficiency: N/A  
Efficacy: 114.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 201.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563721  
CATALOG NUMBER: SQ4-PP3-125U-100D-935-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P563721

CATALOG NUMBER: SQ4-PP3-125U-100D-935-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	44	43	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27	23
5	67	56	48	42	61	52	45	39	43	38	34	35	32	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	21	18	16	14
9	49	37	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11957	11957	11957
5°	12045	11971	11929
10°	12025	11939	11886
15°	11945	11880	11815
20°	11866	11799	11710
25°	11725	11644	11528
30°	11508	11447	11302
35°	11207	11130	10989
40°	10848	10780	10656
45°	10552	10478	10374
50°	10173	10108	10010
55°	9647	9519	9446
60°	8781	8530	8488
65°	7736	7414	7389
70°	6679	6404	6404
75°	5750	5668	5587
80°	5069	5129	5009
85°	3966	4330	4330



TEST NUMBER: P563721

CATALOG NUMBER: SQ4-PP3-125U-100D-935-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	367.6	1.6
10°-20°	1049.7	4.6
20°-30°	1572.4	6.8
30°-40°	1844.3	8.0
40°-50°	1850.1	8.0
50°-60°	1578.3	6.9
60°-70°	1029.3	4.5
70°-80°	516.4	2.2
80°-90°	147.7	0.6
90°-100°	944.3	4.1
100°-110°	2543.8	11.1
110°-120°	2669.6	11.6
120°-130°	2166.3	9.4
130°-140°	1699.0	7.4
140°-150°	1304.4	5.7
150°-160°	937.9	4.1
160°-170°	573.0	2.5
170°-180°	193.2	0.8
0°-30°	2989.8	13.0
0°-40°	4834.1	21.0
0°-60°	8262.4	35.9
0°-90°	9955.7	43.3
90°-120°	6157.8	26.8
90°-150°	11327.5	49.3
90°-180°	13032.0	56.7
0°-180°	22987.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3888	3888	3888	3888	3888	
5°	3902	3865	3878	3864	3864	371
15°	3752	3715	3731	3717	3711	1058
25°	3455	3415	3431	3401	3397	1589
35°	2985	2955	2964	2930	2927	1865
45°	2426	2410	2409	2385	2385	1868
55°	1799	1792	1775	1765	1762	1599
65°	1063	1043	1019	1012	1015	1061
75°	484	484	477	474	470	525
85°	112	122	123	123	123	132
90°	5	15	31	33	33	14
95°	144	514	1548	792	548	150
105°	471	732	2813	4209	3950	495
115°	831	1017	2343	4526	5120	817
125°	1134	1302	2104	3555	4184	1013
135°	1366	1524	2044	2868	3248	1054
145°	1579	1702	2019	2452	2633	990
155°	1792	1858	2001	2200	2271	825
165°	1944	1967	2008	2088	2098	548
175°	2021	2019	2011	2039	2034	192
180°	2019	2019	2019	2019	2019	

TEST NUMBER: P563721

CATALOG NUMBER: SQ4-PP3-125U-100D-935-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3887.9	3887.9	3887.9	3887.9	3887.9
2.5°	3912.5	3880.5	3887.9	3882.1	3866.1
5°	3901.6	3864.9	3877.7	3864.1	3864.1
7.5°	3875.0	3835.0	3847.7	3834.1	3833.4
10°	3850.5	3810.5	3823.2	3809.5	3806.2
12.5°	3815.0	3775.0	3790.5	3774.1	3773.5
15°	3751.6	3715.0	3731.2	3717.4	3710.8
17.5°	3680.1	3640.1	3659.6	3640.5	3637.8
20°	3625.6	3585.6	3605.1	3577.9	3577.9
22.5°	3560.1	3520.2	3542.4	3507.0	3507.0
25°	3455.2	3415.2	3431.3	3400.6	3397.3
27.5°	3330.5	3291.2	3308.0	3273.2	3272.6
30°	3240.5	3203.9	3223.5	3185.9	3182.6
32.5°	3142.4	3108.4	3122.6	3085.1	3081.7
35°	2985.0	2955.0	2964.5	2930.4	2927.0
37.5°	2819.4	2788.7	2799.6	2770.3	2768.9
40°	2702.1	2682.2	2685.1	2661.1	2654.4
42.5°	2593.1	2570.4	2573.3	2549.5	2548.1
45°	2426.1	2409.5	2409.1	2385.2	2385.2
47.5°	2248.9	2236.3	2232.6	2212.8	2212.1
50°	2126.3	2116.3	2112.6	2095.5	2092.2
52.5°	1998.2	1993.5	1981.8	1967.5	1966.8
55°	1799.2	1792.5	1775.3	1765.0	1761.7
57.5°	1583.1	1569.8	1550.4	1535.5	1538.1
60°	1427.7	1414.4	1386.8	1380.0	1380.0
62.5°	1277.8	1261.8	1234.2	1224.8	1230.1
65°	1063.1	1043.1	1018.8	1012.1	1015.4
67.5°	868.2	850.2	823.9	823.9	821.2
70°	742.8	732.8	712.2	712.2	712.2
72.5°	631.1	626.4	611.3	611.2	608.6
75°	483.9	483.9	477.0	473.6	470.2
77.5°	362.6	363.9	360.5	357.0	351.0
80°	286.2	292.9	289.6	286.2	282.8
82.5°	215.4	222.0	221.5	215.3	214.7
85°	112.4	122.4	122.7	122.7	122.7
87.5°	31.0	43.7	49.8	50.4	53.0
90°	5.1	15.2	30.9	33.4	33.4
92.5°	62.7	221.7	438.2	210.9	146.6
95°	144.0	513.6	1548.1	791.6	547.7
97.5°	229.9	587.9	2428.0	2028.4	1529.6
100°	295.7	617.6	2707.8	2833.2	2350.4
102.5°	359.5	659.2	2800.4	3435.8	3039.6
105°	470.6	732.1	2813.3	4208.9	3949.9
107.5°	575.5	808.8	2693.4	4606.1	4673.0
110°	645.5	866.7	2584.4	4729.5	4973.4

TEST NUMBER: P563721

CATALOG NUMBER: SQ4-PP3-125U-100D-935-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	719.5	924.7	2479.5	4702.2	5103.0
115°	830.6	1016.7	2342.7	4526.5	5119.9
117.5°	931.9	1106.4	2236.7	4246.2	4907.0
120°	997.8	1166.2	2183.2	4045.0	4723.9
122.5°	1055.4	1221.8	2144.2	3839.3	4516.1
125°	1134.0	1302.5	2103.5	3555.3	4183.9
127.5°	1209.7	1375.6	2077.8	3304.8	3866.1
130°	1254.9	1420.9	2067.5	3161.3	3654.2
132.5°	1300.2	1464.1	2057.2	3034.9	3487.5
135°	1365.5	1523.9	2044.4	2868.2	3247.9
137.5°	1427.7	1579.6	2037.7	2726.7	3038.5
140°	1470.9	1616.8	2031.5	2639.7	2921.3
142.5°	1516.2	1652.0	2027.4	2558.4	2795.8
145°	1578.9	1702.1	2018.7	2452.2	2633.3
147.5°	1646.8	1753.9	2009.9	2362.9	2505.2
150°	1692.1	1785.1	2005.8	2306.8	2425.0
152.5°	1733.2	1814.2	2003.7	2261.0	2357.1
155°	1792.4	1857.7	2000.7	2200.3	2270.7
157.5°	1844.3	1895.1	2001.2	2157.6	2204.8
160°	1877.2	1920.0	2003.2	2132.6	2167.8
162.5°	1906.0	1940.7	2005.3	2111.8	2137.0
165°	1944.1	1966.7	2008.4	2088.3	2098.4
167.5°	1974.9	1988.0	2010.9	2070.2	2074.2
170°	1995.5	2000.5	2010.9	2059.8	2059.8
172.5°	2007.9	2008.9	2013.0	2049.5	2049.5
175°	2021.2	2018.7	2010.9	2039.1	2034.1
177.5°	2026.9	2022.9	2012.5	2028.9	2024.8
180°	2018.7	2018.7	2018.7	2018.7	2018.7

(END OF REPORT)