

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563817

Luminaire Tested: **SQ4-PP3-150U-100D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563817
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-100D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 25658.6 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 223.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563817
CATALOG NUMBER: SQ4-PP3-150U-100D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563817

CATALOG NUMBER: SQ4-PP3-150U-100D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	63	60	56	53	47	45	43	36	34	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	73	62	54	49	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	67	55	47	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	61	50	42	36	56	45	38	33	38	32	28	30	26	24	23	21	19	16
7	57	45	37	31	51	41	34	29	34	29	25	27	24	21	21	19	17	14
8	52	40	33	28	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11957	11957	11957
5°	12045	11971	11929
10°	12025	11939	11886
15°	11945	11880	11815
20°	11866	11799	11710
25°	11725	11644	11528
30°	11508	11447	11302
35°	11207	11130	10989
40°	10848	10780	10656
45°	10552	10478	10374
50°	10173	10108	10010
55°	9647	9519	9446
60°	8781	8530	8488
65°	7736	7414	7389
70°	6679	6404	6404
75°	5750	5668	5587
80°	5069	5129	5009
85°	3966	4330	4330



TEST NUMBER: P563817

CATALOG NUMBER: SQ4-PP3-150U-100D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	367.6	1.4
10°-20°	1049.7	4.1
20°-30°	1572.4	6.1
30°-40°	1844.3	7.2
40°-50°	1850.1	7.2
50°-60°	1578.3	6.2
60°-70°	1029.3	4.0
70°-80°	516.4	2.0
80°-90°	148.0	0.6
90°-100°	1131.9	4.4
100°-110°	3060.3	11.9
110°-120°	3217.5	12.5
120°-130°	2613.5	10.2
130°-140°	2050.0	8.0
140°-150°	1573.4	6.1
150°-160°	1131.6	4.4
160°-170°	691.3	2.7
170°-180°	233.1	0.9
0°-30°	2989.8	11.7
0°-40°	4834.1	18.8
0°-60°	8262.4	32.2
0°-90°	9956.1	38.8
90°-120°	7409.7	28.9
90°-150°	13646.6	53.2
90°-180°	15703.0	61.2
0°-180°	25658.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3888	3888	3888	3888	3888	
5°	3902	3865	3878	3864	3864	371
15°	3752	3715	3731	3717	3711	1058
25°	3455	3415	3431	3401	3397	1589
35°	2985	2955	2964	2930	2927	1865
45°	2426	2410	2409	2385	2385	1868
55°	1799	1792	1775	1765	1762	1599
65°	1063	1043	1019	1012	1015	1061
75°	484	484	477	474	470	525
85°	112	122	123	123	123	132
90°	5	16	34	37	34	16
95°	176	616	1882	974	579	184
105°	569	879	3395	5008	4803	599
115°	1002	1224	2816	5451	6153	989
125°	1371	1571	2538	4282	5031	1222
135°	1644	1839	2470	3458	3914	1270
145°	1911	2055	2436	2960	3185	1196
155°	2158	2242	2414	2655	2742	995
165°	2349	2372	2425	2520	2532	662
175°	2438	2436	2428	2459	2454	231
180°	2436	2436	2436	2436	2436	

TEST NUMBER: P563817

CATALOG NUMBER: SQ4-PP3-150U-100D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3887.9	3887.9	3887.9	3887.9	3887.9
2.5°	3912.5	3880.5	3887.9	3882.1	3866.1
5°	3901.6	3864.9	3877.7	3864.1	3864.1
7.5°	3875.0	3835.0	3847.7	3834.1	3833.4
10°	3850.5	3810.5	3823.2	3809.5	3806.2
12.5°	3815.0	3775.0	3790.5	3774.1	3773.5
15°	3751.6	3715.0	3731.2	3717.4	3710.8
17.5°	3680.1	3640.1	3659.6	3640.5	3637.8
20°	3625.6	3585.6	3605.1	3577.9	3577.9
22.5°	3560.1	3520.2	3542.4	3507.0	3507.0
25°	3455.2	3415.2	3431.3	3400.6	3397.3
27.5°	3330.5	3291.2	3308.0	3273.2	3272.6
30°	3240.5	3203.9	3223.5	3185.9	3182.6
32.5°	3142.4	3108.4	3122.6	3085.1	3081.7
35°	2985.0	2955.0	2964.5	2930.4	2927.0
37.5°	2819.4	2788.7	2799.6	2770.3	2768.9
40°	2702.1	2682.2	2685.1	2661.1	2654.4
42.5°	2593.1	2570.4	2573.3	2549.5	2548.1
45°	2426.1	2409.5	2409.1	2385.2	2385.2
47.5°	2248.9	2236.3	2232.6	2212.8	2212.1
50°	2126.3	2116.3	2112.6	2095.5	2092.2
52.5°	1998.2	1993.5	1981.8	1967.5	1966.8
55°	1799.2	1792.5	1775.3	1765.0	1761.7
57.5°	1583.1	1569.8	1550.4	1535.5	1538.1
60°	1427.7	1414.4	1386.8	1380.0	1380.0
62.5°	1277.8	1261.8	1234.2	1224.8	1230.1
65°	1063.1	1043.1	1018.8	1012.1	1015.4
67.5°	868.2	850.2	823.9	823.9	821.2
70°	742.8	732.8	712.2	712.2	712.2
72.5°	631.1	626.4	611.3	611.2	608.6
75°	483.9	483.9	477.0	473.6	470.2
77.5°	362.6	363.9	360.5	357.0	351.0
80°	286.2	292.9	289.6	286.2	282.8
82.5°	215.4	222.0	221.5	215.3	214.7
85°	112.4	122.4	122.7	122.7	122.7
87.5°	31.0	43.7	50.4	51.0	53.2
90°	5.2	15.5	34.1	36.6	34.1
92.5°	74.5	271.3	535.3	232.4	168.3
95°	175.6	616.5	1882.3	974.1	579.4
97.5°	282.1	707.1	2934.1	2428.2	1783.2
100°	361.8	743.7	3261.3	3401.2	2750.1
102.5°	435.2	794.6	3376.7	4139.0	3651.9
105°	568.9	879.1	3395.0	5007.9	4802.8
107.5°	692.6	975.6	3246.6	5550.0	5618.1
110°	789.1	1045.4	3114.5	5695.5	5985.2



TEST NUMBER: P563817

CATALOG NUMBER: SQ4-PP3-150U-100D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	875.1	1115.0	2992.8	5666.4	6153.0
115°	1001.5	1224.5	2815.6	5450.6	6153.0
117.5°	1125.2	1334.4	2698.7	5120.8	5917.0
120°	1200.7	1405.8	2629.5	4884.2	5696.8
122.5°	1272.0	1473.0	2587.5	4630.6	5449.3
125°	1371.1	1571.1	2537.7	4282.4	5030.9
127.5°	1462.3	1658.7	2508.4	3998.3	4656.5
130°	1512.7	1715.2	2495.8	3822.7	4417.4
132.5°	1565.1	1765.6	2483.2	3664.4	4211.9
135°	1643.8	1838.6	2469.6	3457.8	3914.1
137.5°	1722.9	1907.0	2458.0	3290.2	3661.9
140°	1777.5	1949.2	2453.8	3182.3	3513.0
142.5°	1829.9	1991.4	2445.5	3084.9	3374.6
145°	1911.2	2054.7	2435.5	2959.7	3185.3
147.5°	1985.1	2112.2	2424.0	2846.3	3019.6
150°	2039.6	2152.4	2419.8	2784.7	2923.1
152.5°	2090.0	2188.4	2417.7	2727.5	2841.3
155°	2157.6	2242.2	2414.5	2655.1	2742.2
157.5°	2227.9	2286.8	2415.0	2604.6	2662.0
160°	2267.7	2316.4	2417.1	2572.7	2613.8
162.5°	2299.2	2339.7	2419.2	2547.3	2578.1
165°	2349.0	2372.0	2425.0	2519.7	2532.5
167.5°	2383.1	2399.0	2425.5	2495.9	2502.1
170°	2404.0	2411.7	2427.6	2485.3	2485.3
172.5°	2420.8	2422.3	2427.6	2472.7	2470.6
175°	2438.1	2435.5	2427.6	2459.0	2453.8
177.5°	2443.9	2437.7	2427.1	2447.9	2441.8
180°	2435.5	2435.5	2435.5	2435.5	2435.5

(END OF REPORT)