

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P564417

Luminaire Tested: **SQ4-PR1-125U-125D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564417
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-125D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 25660.0 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 233.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564417

CATALOG NUMBER: SQ4-PR1-125U-125D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P564417

CATALOG NUMBER: SQ4-PR1-125U-125D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35	31
4	75	64	56	51	69	60	53	47	51	46	41	43	39	36	35	32	30	26
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26	23
6	63	51	43	38	58	48	41	36	41	36	31	35	30	27	29	26	23	20
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15
10	47	35	28	23	44	33	27	22	29	23	20	25	20	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15530	15530	15530
5°	15670	15549	15468
10°	15620	15511	15430
15°	15551	15455	15371
20°	15473	15374	15260
25°	15364	15261	15084
30°	15198	15090	14874
35°	14974	14843	14631
40°	14633	14476	14213
45°	14036	13790	13507
50°	12985	12673	12423
55°	11334	11077	10844
60°	9550	9470	9283
65°	8261	8293	8230
70°	7587	7626	7626
75°	7287	7287	7339
80°	6856	6932	6856
85°	5526	6140	6140



TEST NUMBER: P564417

CATALOG NUMBER: SQ4-PR1-125U-125D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	477.5	1.9
10°-20°	1366.2	5.3
20°-30°	2060.7	8.0
30°-40°	2455.4	9.6
40°-50°	2420.8	9.4
50°-60°	1850.1	7.2
60°-70°	1144.9	4.5
70°-80°	650.3	2.5
80°-90°	202.6	0.8
90°-100°	944.3	3.7
100°-110°	2543.8	9.9
110°-120°	2669.6	10.4
120°-130°	2166.3	8.4
130°-140°	1699.0	6.6
140°-150°	1304.4	5.1
150°-160°	937.9	3.7
160°-170°	573.0	2.2
170°-180°	193.2	0.8
0°-30°	3904.5	15.2
0°-40°	6359.9	24.8
0°-60°	10630.7	41.4
0°-90°	12628.4	49.2
90°-120°	6157.8	24.0
90°-150°	11327.5	44.1
90°-180°	13032.0	50.8
0°-180°	25660.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5050	5050	5050	5050	5050	
5°	5076	5020	5037	5019	5011	482
15°	4884	4833	4854	4836	4828	1378
25°	4528	4472	4497	4449	4445	2084
35°	3988	3942	3954	3901	3897	2489
45°	3227	3185	3171	3114	3106	2472
55°	2114	2080	2066	2031	2022	1894
65°	1135	1127	1140	1131	1131	1150
75°	613	613	613	618	618	648
85°	157	165	174	174	174	182
90°	5	15	31	33	33	16
95°	144	514	1548	792	548	150
105°	471	732	2813	4209	3950	495
115°	831	1017	2343	4526	5120	817
125°	1134	1302	2104	3555	4184	1013
135°	1366	1524	2044	2868	3248	1054
145°	1579	1702	2019	2452	2633	990
155°	1792	1858	2001	2200	2271	825
165°	1944	1967	2008	2088	2098	548
175°	2021	2019	2011	2039	2034	192
180°	2019	2019	2019	2019	2019	

TEST NUMBER: P564417

CATALOG NUMBER: SQ4-PR1-125U-125D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5049.7	5049.7	5049.7	5049.7	5049.7
2.5°	5081.0	5036.8	5049.7	5038.7	5014.9
5°	5075.8	5020.5	5036.6	5019.1	5010.6
7.5°	5036.6	4982.2	4998.4	4980.9	4975.8
10°	5001.9	4950.8	4967.1	4949.5	4941.0
12.5°	4963.6	4909.1	4928.8	4907.7	4899.2
15°	4884.4	4833.4	4854.0	4836.4	4827.9
17.5°	4797.4	4743.0	4763.5	4743.2	4732.2
20°	4727.8	4676.8	4697.4	4666.8	4662.6
22.5°	4651.3	4600.3	4620.8	4579.9	4579.1
25°	4527.8	4472.5	4497.3	4449.4	4445.1
27.5°	4380.8	4329.7	4350.3	4301.5	4296.4
30°	4279.8	4228.8	4249.4	4197.0	4188.5
32.5°	4165.0	4117.4	4134.6	4082.3	4077.2
35°	3988.4	3941.7	3953.6	3901.3	3897.1
37.5°	3787.5	3745.0	3751.8	3694.3	3690.1
40°	3644.8	3602.3	3605.7	3544.7	3540.4
42.5°	3488.2	3445.7	3442.1	3381.2	3376.9
45°	3227.3	3184.8	3170.7	3114.0	3105.5
47.5°	2929.8	2887.3	2861.1	2814.8	2808.9
50°	2714.0	2671.5	2648.8	2609.4	2596.6
52.5°	2480.9	2438.4	2419.2	2383.2	2370.4
55°	2113.8	2079.8	2066.0	2031.0	2022.5
57.5°	1765.0	1742.0	1738.0	1704.0	1700.6
60°	1552.7	1540.0	1539.7	1509.3	1509.3
62.5°	1371.8	1362.5	1369.2	1349.1	1345.7
65°	1135.2	1126.7	1139.6	1130.9	1130.9
67.5°	948.2	948.2	956.0	952.5	952.5
70°	843.8	843.8	848.1	848.1	848.1
72.5°	749.8	746.4	757.7	757.6	754.2
75°	613.3	613.3	613.3	617.6	617.6
77.5°	477.6	478.4	481.9	481.0	477.6
80°	387.1	391.4	391.4	387.1	387.1
82.5°	296.6	300.9	301.0	300.0	296.6
85°	156.6	165.1	174.0	174.0	174.0
87.5°	46.3	61.9	75.8	76.2	72.8
90°	5.1	15.2	30.9	33.4	33.4
92.5°	62.7	221.7	438.2	210.9	146.6
95°	144.0	513.6	1548.1	791.6	547.7
97.5°	229.9	587.9	2428.0	2028.4	1529.6
100°	295.7	617.6	2707.8	2833.2	2350.4
102.5°	359.5	659.2	2800.4	3435.8	3039.6
105°	470.6	732.1	2813.3	4208.9	3949.9
107.5°	575.5	808.8	2693.4	4606.1	4673.0
110°	645.5	866.7	2584.4	4729.5	4973.4



TEST NUMBER: P564417

CATALOG NUMBER: SQ4-PR1-125U-125D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	719.5	924.7	2479.5	4702.2	5103.0
115°	830.6	1016.7	2342.7	4526.5	5119.9
117.5°	931.9	1106.4	2236.7	4246.2	4907.0
120°	997.8	1166.2	2183.2	4045.0	4723.9
122.5°	1055.4	1221.8	2144.2	3839.3	4516.1
125°	1134.0	1302.5	2103.5	3555.3	4183.9
127.5°	1209.7	1375.6	2077.8	3304.8	3866.1
130°	1254.9	1420.9	2067.5	3161.3	3654.2
132.5°	1300.2	1464.1	2057.2	3034.9	3487.5
135°	1365.5	1523.9	2044.4	2868.2	3247.9
137.5°	1427.7	1579.6	2037.7	2726.7	3038.5
140°	1470.9	1616.8	2031.5	2639.7	2921.3
142.5°	1516.2	1652.0	2027.4	2558.4	2795.8
145°	1578.9	1702.1	2018.7	2452.2	2633.3
147.5°	1646.8	1753.9	2009.9	2362.9	2505.2
150°	1692.1	1785.1	2005.8	2306.8	2425.0
152.5°	1733.2	1814.2	2003.7	2261.0	2357.1
155°	1792.4	1857.7	2000.7	2200.3	2270.7
157.5°	1844.3	1895.1	2001.2	2157.6	2204.8
160°	1877.2	1920.0	2003.2	2132.6	2167.8
162.5°	1906.0	1940.7	2005.3	2111.8	2137.0
165°	1944.1	1966.7	2008.4	2088.3	2098.4
167.5°	1974.9	1988.0	2010.9	2070.2	2074.2
170°	1995.5	2000.5	2010.9	2059.8	2059.8
172.5°	2007.9	2008.9	2013.0	2049.5	2049.5
175°	2021.2	2018.7	2010.9	2039.1	2034.1
177.5°	2026.9	2022.9	2012.5	2028.9	2024.8
180°	2018.7	2018.7	2018.7	2018.7	2018.7

(END OF REPORT)