

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563883

Luminaire Tested: **SQ4-PR1-025U-075D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563883  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-025U-075D-840-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5791.9 lumens  
Efficiency: N/A  
Efficacy: 119.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 48.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563883  
CATALOG NUMBER: SQ4-PR1-025U-075D-840-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563883

CATALOG NUMBER: SQ4-PR1-025U-075D-840-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79	75				
1	104	99	96	92	99	95	91	88	86	83	81	78	76	74	70	69	67	64				
2	95	87	81	76	90	83	78	73	76	71	68	69	65	62	62	60	58	54				
3	87	77	70	64	82	74	67	62	67	62	57	61	57	53	56	52	49	46				
4	80	69	61	54	76	66	58	53	60	54	49	55	50	46	50	46	43	40				
5	73	62	53	47	70	59	51	46	54	48	43	50	44	40	45	41	38	35				
6	68	55	47	41	64	53	46	40	49	43	38	45	40	35	41	37	33	31				
7	63	50	42	36	60	48	41	35	45	38	33	41	36	32	38	33	30	27				
8	58	46	38	32	56	44	37	32	41	34	30	38	32	28	35	30	27	25				
9	55	42	34	29	52	40	33	28	37	31	27	35	29	26	32	27	24	22				
10	51	39	31	26	49	37	30	26	35	29	24	32	27	23	30	25	22	20				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10647	10647	10647
5°	10743	10660	10605
10°	10709	10635	10578
15°	10662	10595	10538
20°	10608	10540	10462
25°	10534	10462	10341
30°	10420	10346	10198
35°	10266	10177	10031
40°	10032	9924	9744
45°	9623	9454	9260
50°	8902	8689	8517
55°	7770	7594	7435
60°	6548	6493	6365
65°	5663	5685	5641
70°	5201	5228	5228
75°	4995	4995	5031
80°	4700	4754	4700
85°	3790	4206	4206



TEST NUMBER: P563883

CATALOG NUMBER: SQ4-PR1-025U-075D-840-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.7	2.8
10°-20°	468.3	8.1
20°-30°	706.4	12.2
30°-40°	841.7	14.5
40°-50°	829.8	14.3
50°-60°	634.2	10.9
60°-70°	392.4	6.8
70°-80°	222.9	3.8
80°-90°	69.0	1.2
90°-100°	110.0	1.9
100°-110°	289.3	5.0
110°-120°	300.0	5.2
120°-130°	240.6	4.2
130°-140°	188.8	3.3
140°-150°	144.9	2.5
150°-160°	104.4	1.8
160°-170°	63.9	1.1
170°-180°	21.6	0.4
0°-30°	1338.4	23.1
0°-40°	2180.1	37.6
0°-60°	3644.1	62.9
0°-90°	4328.5	74.7
90°-120°	699.3	12.1
90°-150°	1273.6	22.0
90°-180°	1463.0	25.3
0°-180°	5791.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1731	1731	1731	1731	1731	
5°	1740	1721	1726	1720	1718	165
15°	1674	1657	1664	1658	1655	472
25°	1552	1533	1542	1525	1524	714
35°	1367	1351	1355	1337	1336	853
45°	1106	1092	1087	1067	1064	848
55°	725	713	708	696	693	649
65°	389	386	391	388	388	394
75°	210	210	210	212	212	222
85°	54	57	60	60	60	62
90°	1	4	12	6	6	3
95°	14	57	190	98	67	16
105°	52	79	320	486	453	55
115°	93	112	256	511	583	91
125°	129	144	233	394	465	114
135°	153	169	226	318	360	119
145°	178	189	223	271	292	112
155°	201	207	223	245	252	92
165°	217	220	223	232	234	61
175°	226	226	224	227	227	21
180°	226	226	226	226	226	



TEST NUMBER: P563883

CATALOG NUMBER: SQ4-PR1-025U-075D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1731.0	1731.0	1731.0	1731.0	1731.0
2.5°	1741.7	1726.6	1731.0	1727.2	1719.1
5°	1739.9	1721.0	1726.5	1720.5	1717.6
7.5°	1726.5	1707.9	1713.4	1707.4	1705.6
10°	1714.6	1697.1	1702.7	1696.6	1693.7
12.5°	1701.5	1682.8	1689.5	1682.3	1679.4
15°	1674.3	1656.8	1663.9	1657.9	1654.9
17.5°	1644.5	1625.9	1632.9	1625.9	1622.1
20°	1620.7	1603.2	1610.2	1599.7	1598.3
22.5°	1594.4	1576.9	1584.0	1570.0	1569.7
25°	1552.1	1533.1	1541.6	1525.2	1523.7
27.5°	1501.7	1484.2	1491.2	1474.5	1472.8
30°	1467.1	1449.6	1456.7	1438.7	1435.8
32.5°	1427.7	1411.4	1417.3	1399.4	1397.6
35°	1367.2	1351.2	1355.3	1337.3	1335.9
37.5°	1298.3	1283.7	1286.1	1266.4	1264.9
40°	1249.4	1234.8	1236.0	1215.1	1213.6
42.5°	1195.7	1181.2	1179.9	1159.0	1157.6
45°	1106.3	1091.7	1086.9	1067.4	1064.5
47.5°	1004.3	989.7	980.7	964.9	962.9
50°	930.3	915.8	908.0	894.5	890.1
52.5°	850.4	835.9	829.3	816.9	812.6
55°	724.6	712.9	708.2	696.2	693.3
57.5°	605.0	597.2	595.8	584.1	583.0
60°	532.3	527.9	527.8	517.4	517.4
62.5°	470.2	467.0	469.3	462.5	461.3
65°	389.1	386.2	390.6	387.6	387.6
67.5°	325.0	325.0	327.7	326.5	326.5
70°	289.2	289.2	290.7	290.7	290.7
72.5°	257.0	255.9	259.7	259.7	258.5
75°	210.2	210.2	210.2	211.7	211.7
77.5°	163.7	164.0	165.2	164.9	163.7
80°	132.7	134.2	134.2	132.7	132.7
82.5°	101.7	103.1	103.2	102.8	101.7
85°	53.7	56.6	59.6	59.6	59.6
87.5°	15.8	21.0	26.2	25.0	23.8
90°	1.4	4.3	11.6	5.8	5.8
92.5°	6.1	29.3	64.8	28.7	18.5
95°	14.5	56.9	189.6	97.7	66.6
97.5°	25.2	62.5	283.7	225.6	166.2
100°	33.3	67.3	312.6	316.8	246.0
102.5°	40.2	71.9	320.7	394.6	334.0
105°	52.1	79.0	319.9	485.6	453.0
107.5°	64.3	89.2	301.6	532.8	540.7
110°	72.4	95.0	286.6	545.0	578.9



TEST NUMBER: P563883

CATALOG NUMBER: SQ4-PR1-025U-075D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	80.5	102.0	272.7	537.3	589.4
115°	92.6	112.4	256.2	511.1	583.3
117.5°	104.5	122.6	244.9	474.8	554.9
120°	111.4	128.4	240.3	450.4	528.3
122.5°	118.4	135.4	236.8	426.1	502.8
125°	128.8	144.4	233.0	393.8	464.6
127.5°	137.2	153.1	229.8	367.8	427.5
130°	141.8	158.8	228.7	351.5	406.7
132.5°	146.5	163.5	227.5	337.5	387.0
135°	153.4	169.0	225.8	317.9	360.4
137.5°	160.7	175.9	225.5	303.3	338.1
140°	166.4	180.6	224.3	291.7	324.2
142.5°	171.1	184.1	224.3	283.4	311.5
145°	178.0	189.3	222.9	271.1	292.4
147.5°	185.0	196.0	222.9	260.9	278.5
150°	189.6	199.5	222.9	255.1	269.2
152.5°	194.2	201.9	222.9	250.3	261.1
155°	201.2	206.8	222.9	244.8	251.8
157.5°	206.4	211.8	222.9	239.8	244.9
160°	209.9	214.1	222.9	237.4	240.3
162.5°	213.3	216.5	222.9	235.1	237.9
165°	217.1	219.9	222.9	231.6	234.5
167.5°	220.6	222.0	224.3	230.2	231.3
170°	222.9	224.3	224.3	230.1	230.1
172.5°	224.0	224.3	224.3	228.9	227.8
175°	225.8	225.8	224.3	227.2	227.2
177.5°	225.8	225.8	224.6	226.9	225.8
180°	225.8	225.8	225.8	225.8	225.8

(END OF REPORT)