

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563907

Luminaire Tested: **SQ4-PR1-025U-100D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563907
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-025U-100D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7214.3 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 63.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563907
CATALOG NUMBER: SQ4-PR1-025U-100D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563907

CATALOG NUMBER: SQ4-PR1-025U-100D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80
1	105	101	97	93	100	96	93	90	88	86	83	81	79	77	74	73	71	68
2	96	88	82	77	92	85	79	74	78	74	70	72	68	65	66	63	61	58
3	88	78	71	65	84	75	68	63	69	64	59	64	59	56	59	55	52	49
4	81	70	61	55	77	67	60	54	62	56	51	57	52	48	53	49	45	43
5	74	62	54	48	71	60	52	47	56	49	44	52	46	42	48	43	40	37
6	69	56	48	42	66	54	47	41	50	44	39	47	41	37	44	39	35	33
7	64	51	43	37	61	49	42	36	46	39	35	43	37	33	40	35	31	29
8	59	47	39	33	57	45	38	32	42	36	31	39	34	30	37	32	28	26
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	26	24
10	52	39	32	27	50	38	31	26	36	30	25	34	28	24	31	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14147	14147	14147
5°	14274	14164	14090
10°	14229	14130	14055
15°	14166	14078	14002
20°	14095	14004	13901
25°	13995	13902	13740
30°	13845	13747	13549
35°	13640	13521	13328
40°	13329	13187	12948
45°	12786	12562	12303
50°	11829	11544	11317
55°	10325	10091	9879
60°	8700	8627	8456
65°	7524	7554	7497
70°	6911	6947	6947
75°	6638	6638	6685
80°	6245	6316	6245
85°	5032	5589	5589



TEST NUMBER: P563907

CATALOG NUMBER: SQ4-PR1-025U-100D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	217.5	3.0
10°-20°	622.3	8.6
20°-30°	938.6	13.0
30°-40°	1118.3	15.5
40°-50°	1102.6	15.3
50°-60°	842.6	11.7
60°-70°	521.5	7.2
70°-80°	296.2	4.1
80°-90°	91.3	1.3
90°-100°	110.0	1.5
100°-110°	289.3	4.0
110°-120°	300.0	4.2
120°-130°	240.6	3.3
130°-140°	188.8	2.6
140°-150°	144.9	2.0
150°-160°	104.4	1.4
160°-170°	63.9	0.9
170°-180°	21.6	0.3
0°-30°	1778.4	24.7
0°-40°	2896.7	40.2
0°-60°	4841.9	67.1
0°-90°	5750.9	79.7
90°-120°	699.3	9.7
90°-150°	1273.6	17.7
90°-180°	1463.0	20.3
0°-180°	7214.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2300	2300	2300	2300	2300	
5°	2312	2287	2294	2286	2282	219
15°	2225	2201	2211	2203	2199	628
25°	2062	2037	2048	2026	2025	949
35°	1817	1795	1801	1777	1775	1134
45°	1470	1450	1444	1418	1414	1126
55°	963	947	941	925	921	863
65°	517	513	519	515	515	524
75°	279	279	279	281	281	295
85°	71	75	79	79	79	83
90°	1	4	12	6	6	4
95°	14	57	190	98	67	16
105°	52	79	320	486	453	55
115°	93	112	256	511	583	91
125°	129	144	233	394	465	114
135°	153	169	226	318	360	119
145°	178	189	223	271	292	112
155°	201	207	223	245	252	92
165°	217	220	223	232	234	61
175°	226	226	224	227	227	21
180°	226	226	226	226	226	



TEST NUMBER: P563907

CATALOG NUMBER: SQ4-PR1-025U-100D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2300.0	2300.0	2300.0	2300.0	2300.0
2.5°	2314.2	2294.1	2300.0	2295.0	2284.1
5°	2311.9	2286.7	2294.0	2286.0	2282.1
7.5°	2294.0	2269.2	2276.6	2268.6	2266.3
10°	2278.2	2254.9	2262.3	2254.3	2250.4
12.5°	2260.7	2235.9	2244.9	2235.3	2231.4
15°	2224.7	2201.4	2210.8	2202.8	2198.9
17.5°	2185.1	2160.3	2169.6	2160.4	2155.4
20°	2153.4	2130.1	2139.5	2125.6	2123.7
22.5°	2118.5	2095.3	2104.6	2086.0	2085.6
25°	2062.2	2037.1	2048.4	2026.5	2024.6
27.5°	1995.3	1972.0	1981.4	1959.2	1956.9
30°	1949.3	1926.1	1935.5	1911.6	1907.7
32.5°	1897.0	1875.3	1883.2	1859.3	1857.0
35°	1816.6	1795.3	1800.7	1776.9	1775.0
37.5°	1725.1	1705.7	1708.8	1682.6	1680.7
40°	1660.1	1640.7	1642.3	1614.5	1612.6
42.5°	1588.8	1569.4	1567.8	1540.0	1538.1
45°	1469.9	1450.5	1444.2	1418.3	1414.4
47.5°	1334.4	1315.0	1303.1	1282.1	1279.3
50°	1236.2	1216.8	1206.4	1188.5	1182.7
52.5°	1130.0	1110.6	1101.8	1085.5	1079.7
55°	962.8	947.3	941.0	925.0	921.2
57.5°	803.9	793.4	791.6	776.1	774.6
60°	707.2	701.4	701.3	687.4	687.4
62.5°	624.8	620.6	623.6	614.5	612.9
65°	517.0	513.2	519.0	515.1	515.1
67.5°	431.9	431.9	435.4	433.8	433.8
70°	384.3	384.3	386.3	386.3	386.3
72.5°	341.5	340.0	345.1	345.1	343.5
75°	279.3	279.3	279.3	281.3	281.3
77.5°	217.5	217.9	219.5	219.1	217.5
80°	176.3	178.2	178.3	176.3	176.3
82.5°	135.1	137.0	137.1	136.7	135.1
85°	71.3	75.2	79.2	79.2	79.2
87.5°	20.9	27.7	34.0	32.8	31.3
90°	1.4	4.3	11.6	5.8	5.8
92.5°	6.1	29.3	64.8	28.7	18.5
95°	14.5	56.9	189.6	97.7	66.6
97.5°	25.2	62.5	283.7	225.6	166.2
100°	33.3	67.3	312.6	316.8	246.0
102.5°	40.2	71.9	320.7	394.6	334.0
105°	52.1	79.0	319.9	485.6	453.0
107.5°	64.3	89.2	301.6	532.8	540.7
110°	72.4	95.0	286.6	545.0	578.9



TEST NUMBER: P563907

CATALOG NUMBER: SQ4-PR1-025U-100D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	80.5	102.0	272.7	537.3	589.4
115°	92.6	112.4	256.2	511.1	583.3
117.5°	104.5	122.6	244.9	474.8	554.9
120°	111.4	128.4	240.3	450.4	528.3
122.5°	118.4	135.4	236.8	426.1	502.8
125°	128.8	144.4	233.0	393.8	464.6
127.5°	137.2	153.1	229.8	367.8	427.5
130°	141.8	158.8	228.7	351.5	406.7
132.5°	146.5	163.5	227.5	337.5	387.0
135°	153.4	169.0	225.8	317.9	360.4
137.5°	160.7	175.9	225.5	303.3	338.1
140°	166.4	180.6	224.3	291.7	324.2
142.5°	171.1	184.1	224.3	283.4	311.5
145°	178.0	189.3	222.9	271.1	292.4
147.5°	185.0	196.0	222.9	260.9	278.5
150°	189.6	199.5	222.9	255.1	269.2
152.5°	194.2	201.9	222.9	250.3	261.1
155°	201.2	206.8	222.9	244.8	251.8
157.5°	206.4	211.8	222.9	239.8	244.9
160°	209.9	214.1	222.9	237.4	240.3
162.5°	213.3	216.5	222.9	235.1	237.9
165°	217.1	219.9	222.9	231.6	234.5
167.5°	220.6	222.0	224.3	230.2	231.3
170°	222.9	224.3	224.3	230.1	230.1
172.5°	224.0	224.3	224.3	228.9	227.8
175°	225.8	225.8	224.3	227.2	227.2
177.5°	225.8	225.8	224.6	226.9	225.8
180°	225.8	225.8	225.8	225.8	225.8

(END OF REPORT)