

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519539

Luminaire Tested: **SQ4-WB-125U-125D-935-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519539
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-125D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23736.6 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 233.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519539
CATALOG NUMBER: SQ4-WB-125U-125D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519539

CATALOG NUMBER: SQ4-WB-125U-125D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	98	94	90	87	90	86	83	81	72	70	68	59	58	57	47	46	46	40
2	90	83	78	73	82	77	72	68	64	61	58	53	51	49	43	41	40	35
3	83	74	67	62	76	68	63	58	58	54	50	48	45	43	39	37	35	31
4	76	66	59	54	70	61	55	50	52	47	44	44	40	38	36	33	31	28
5	70	60	52	47	65	55	49	44	47	42	39	40	36	33	33	30	28	25
6	65	54	46	41	60	50	44	39	43	38	34	36	33	30	30	27	25	23
7	61	49	42	36	56	46	39	34	39	34	31	33	30	27	28	25	23	20
8	56	45	38	33	52	42	35	31	36	31	28	31	27	24	26	23	21	19
9	53	41	34	29	49	39	32	28	33	28	25	29	25	22	24	21	19	17
10	49	38	31	27	46	36	29	25	31	26	23	27	23	20	22	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22583	22583	22583
5°	22301	22222	22351
10°	21070	21261	21754
15°	19451	19902	20795
20°	17663	18328	19540
25°	15843	16706	18205
30°	14165	15092	16820
35°	12387	13283	15182
40°	10426	11254	13142
45°	8605	9347	10973
50°	7184	7831	9142
55°	6099	6720	7550
60°	5212	5827	6025
65°	4150	4900	3892
70°	3679	3824	2376
75°	3408	3101	1454
80°	3138	2853	1256
85°	2844	2615	1023



TEST NUMBER: P519539

CATALOG NUMBER: SQ4-WB-125U-125D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	673.5	2.8
10°-20°	1751.9	7.4
20°-30°	2269.2	9.6
30°-40°	2222.1	9.4
40°-50°	1700.9	7.2
50°-60°	1133.4	4.8
60°-70°	618.5	2.6
70°-80°	257.7	1.1
80°-90°	77.7	0.3
90°-100°	944.3	4.0
100°-110°	2543.8	10.7
110°-120°	2669.6	11.2
120°-130°	2166.3	9.1
130°-140°	1699.0	7.2
140°-150°	1304.4	5.5
150°-160°	937.9	4.0
160°-170°	573.0	2.4
170°-180°	193.2	0.8
0°-30°	4694.7	19.8
0°-40°	6916.8	29.1
0°-60°	9751.1	41.1
0°-90°	10705.0	45.1
90°-120°	6157.8	25.9
90°-150°	11327.5	47.7
90°-180°	13032.0	54.9
0°-180°	23736.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	7343	7343	7343	7343	7343	
5°	7224	7152	7198	7215	7240	672
15°	6109	6087	6251	6421	6531	1706
25°	4669	4681	4923	5138	5365	2147
35°	3299	3315	3538	3776	4044	2051
45°	1978	2016	2149	2312	2523	1543
55°	1137	1185	1253	1301	1408	1031
65°	570	618	673	588	535	593
75°	287	287	261	179	122	306
85°	81	81	74	48	29	88
90°	5	15	31	33	33	14
95°	144	514	1548	792	548	150
105°	471	732	2813	4209	3950	495
115°	831	1017	2343	4526	5120	817
125°	1134	1302	2104	3555	4184	1013
135°	1366	1524	2044	2868	3248	1054
145°	1579	1702	2019	2452	2633	990
155°	1792	1858	2001	2200	2271	825
165°	1944	1967	2008	2088	2098	548
175°	2021	2019	2011	2039	2034	192
180°	2019	2019	2019	2019	2019	

TEST NUMBER: P519539

CATALOG NUMBER: SQ4-WB-125U-125D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	7343.1	7343.1	7343.1	7343.1	7343.1
2.5°	7361.2	7295.6	7312.2	7311.7	7291.6
5°	7223.9	7151.5	7198.1	7214.8	7240.0
7.5°	6955.8	6901.0	6986.1	7049.2	7100.2
10°	6747.0	6699.8	6808.3	6900.0	6966.2
12.5°	6504.7	6465.1	6599.5	6722.6	6808.9
15°	6109.1	6087.0	6250.8	6420.9	6531.2
17.5°	5685.7	5675.0	5862.9	6061.4	6202.5
20°	5397.0	5393.8	5600.0	5806.7	5970.5
22.5°	5105.7	5112.6	5329.3	5544.3	5730.8
25°	4668.8	4681.4	4923.3	5137.9	5364.8
27.5°	4264.8	4270.4	4520.6	4747.1	4989.1
30°	3988.9	4004.7	4249.9	4484.4	4736.5
32.5°	3713.1	3731.4	3971.5	4213.9	4471.0
35°	3299.4	3315.2	3537.9	3775.9	4043.7
37.5°	2872.8	2894.2	3091.9	3317.0	3580.4
40°	2597.0	2628.5	2803.2	3015.3	3273.6
42.5°	2331.5	2370.6	2532.6	2733.8	2966.9
45°	1978.4	2016.2	2149.1	2311.8	2522.9
47.5°	1674.2	1717.7	1819.8	1959.9	2140.1
50°	1501.5	1542.4	1636.8	1740.6	1910.7
52.5°	1349.4	1390.4	1474.4	1554.4	1699.3
55°	1137.4	1184.7	1253.4	1300.9	1408.1
57.5°	963.4	1008.8	1063.3	1084.7	1149.6
60°	847.4	897.8	947.3	944.9	979.5
62.5°	741.7	784.6	833.9	799.8	801.7
65°	570.3	617.6	673.4	588.4	534.9
67.5°	460.8	470.8	528.4	410.3	346.7
70°	409.2	409.2	425.3	317.8	264.2
72.5°	360.2	360.2	345.4	258.4	202.3
75°	286.8	286.8	261.0	179.1	122.4
77.5°	221.0	218.5	199.8	133.7	88.9
80°	177.2	177.2	161.1	105.5	70.9
82.5°	138.5	138.5	125.0	82.5	52.8
85°	80.6	80.6	74.1	47.9	29.0
87.5°	29.4	31.4	31.9	22.1	19.6
90°	5.1	15.2	30.9	33.4	33.4
92.5°	62.7	221.7	438.2	210.9	146.6
95°	144.0	513.6	1548.1	791.6	547.7
97.5°	229.9	587.9	2428.0	2028.4	1529.6
100°	295.7	617.6	2707.8	2833.2	2350.4
102.5°	359.5	659.2	2800.4	3435.8	3039.6
105°	470.6	732.1	2813.3	4208.9	3949.9
107.5°	575.5	808.8	2693.4	4606.1	4673.0
110°	645.5	866.7	2584.4	4729.5	4973.4



TEST NUMBER: P519539

CATALOG NUMBER: SQ4-WB-125U-125D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	719.5	924.7	2479.5	4702.2	5103.0
115°	830.6	1016.7	2342.7	4526.5	5119.9
117.5°	931.9	1106.4	2236.7	4246.2	4907.0
120°	997.8	1166.2	2183.2	4045.0	4723.9
122.5°	1055.4	1221.8	2144.2	3839.3	4516.1
125°	1134.0	1302.5	2103.5	3555.3	4183.9
127.5°	1209.7	1375.6	2077.8	3304.8	3866.1
130°	1254.9	1420.9	2067.5	3161.3	3654.2
132.5°	1300.2	1464.1	2057.2	3034.9	3487.5
135°	1365.5	1523.9	2044.4	2868.2	3247.9
137.5°	1427.7	1579.6	2037.7	2726.7	3038.5
140°	1470.9	1616.8	2031.5	2639.7	2921.3
142.5°	1516.2	1652.0	2027.4	2558.4	2795.8
145°	1578.9	1702.1	2018.7	2452.2	2633.3
147.5°	1646.8	1753.9	2009.9	2362.9	2505.2
150°	1692.1	1785.1	2005.8	2306.8	2425.0
152.5°	1733.2	1814.2	2003.7	2261.0	2357.1
155°	1792.4	1857.7	2000.7	2200.3	2270.7
157.5°	1844.3	1895.1	2001.2	2157.6	2204.8
160°	1877.2	1920.0	2003.2	2132.6	2167.8
162.5°	1906.0	1940.7	2005.3	2111.8	2137.0
165°	1944.1	1966.7	2008.4	2088.3	2098.4
167.5°	1974.9	1988.0	2010.9	2070.2	2074.2
170°	1995.5	2000.5	2010.9	2059.8	2059.8
172.5°	2007.9	2008.9	2013.0	2049.5	2049.5
175°	2021.2	2018.7	2010.9	2039.1	2034.1
177.5°	2026.9	2022.9	2012.5	2028.9	2024.8
180°	2018.7	2018.7	2018.7	2018.7	2018.7

(END OF REPORT)