

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P519748

Luminaire Tested: **SQ4-125U-0D-840-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519748  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-125U-0D-840-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5049.6 lumens  
Efficiency: N/A  
Efficacy: 159.3 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect

Input Watts (W): 31.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519748  
CATALOG NUMBER: SQ4-125U-0D-840-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P519748

CATALOG NUMBER: SQ4-125U-0D-840-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20								20				20				20			
RC	80								50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0		
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0		
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0		
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0		
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0		
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0		
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0		
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0		
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0		
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0		
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	5907	63505	22463
100°	6089	55751	48392
105°	6499	38859	54558
110°	6747	27013	51985
115°	7027	19818	43311
120°	7134	15611	33777
125°	7068	13111	26078
130°	6980	11499	20324
135°	6904	10336	16421
140°	6865	9481	13634
145°	6891	8810	11493
150°	6986	8280	10010
155°	7070	7892	8957
160°	7142	7621	8247
165°	7195	7433	7766
170°	7244	7300	7478
175°	7254	7217	7300



TEST NUMBER: P519748

CATALOG NUMBER: SQ4-125U-0D-840-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	365.9	7.2
100°-110°	985.7	19.5
110°-120°	1034.5	20.5
120°-130°	839.4	16.6
130°-140°	658.3	13.0
140°-150°	505.4	10.0
150°-160°	363.4	7.2
160°-170°	222.0	4.4
170°-180°	74.9	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2386.1	47.3
90°-150°	4389.3	86.9
90°-180°	5050.0	100.0
0°-180°	5049.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	6	12	13	13	
95°	56	199	600	307	212	62
105°	182	284	1090	1631	1530	192
115°	322	394	908	1754	1984	317
125°	439	505	815	1378	1621	392
135°	529	590	792	1111	1258	408
145°	612	660	782	950	1020	384
155°	694	720	775	853	880	320
165°	753	762	778	809	813	212
175°	783	782	779	790	788	74
180°	782	782	782	782	782	



TEST NUMBER: P519748

CATALOG NUMBER: SQ4-125U-0D-840-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	2.0	5.9	12.0	13.0	13.0
92.5°	24.3	85.9	169.8	81.7	56.8
95°	55.8	199.0	599.9	306.8	212.2
97.5°	89.1	227.8	940.8	786.0	592.7
100°	114.6	239.3	1049.3	1097.8	910.8
102.5°	139.3	255.4	1085.1	1331.4	1177.8
105°	182.3	283.7	1090.1	1630.9	1530.5
107.5°	223.0	313.4	1043.7	1784.8	1810.7
110°	250.1	335.8	1001.4	1832.6	1927.1
112.5°	278.8	358.3	960.8	1822.0	1977.3
115°	321.9	394.0	907.8	1754.0	1983.9
117.5°	361.1	428.7	866.7	1645.4	1901.4
120°	386.6	451.9	846.0	1567.4	1830.5
122.5°	408.9	473.4	830.8	1487.7	1750.0
125°	439.4	504.7	815.1	1377.6	1621.2
127.5°	468.7	533.0	805.1	1280.6	1498.1
130°	486.3	550.6	801.1	1225.0	1416.0
132.5°	503.8	567.3	797.2	1176.0	1351.4
135°	529.1	590.5	792.2	1111.4	1258.5
137.5°	553.2	612.1	789.6	1056.6	1177.4
140°	570.0	626.5	787.2	1022.8	1132.0
142.5°	587.5	640.1	785.6	991.4	1083.3
145°	611.8	659.6	782.2	950.2	1020.4
147.5°	638.1	679.6	778.8	915.6	970.7
150°	655.7	691.7	777.2	893.9	939.6
152.5°	671.6	703.0	776.4	876.1	913.3
155°	694.5	719.9	775.2	852.6	879.9
157.5°	714.7	734.3	775.4	836.0	854.4
160°	727.4	744.0	776.2	826.4	840.0
162.5°	738.6	752.0	777.0	818.3	828.0
165°	753.3	762.1	778.2	809.2	813.1
167.5°	765.3	770.3	779.2	802.2	803.7
170°	773.2	775.2	779.2	798.2	798.2
172.5°	778.0	778.4	780.0	794.2	794.2
175°	783.2	782.2	779.2	790.1	788.2
177.5°	785.4	783.8	779.8	786.2	784.6
180°	782.2	782.2	782.2	782.2	782.2

(END OF REPORT)