

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564507

Luminaire Tested: **SQ4-PR1-150U-125D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564507
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-150U-125D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16467.2 lumens
Efficiency: N/A
Efficacy: 129.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 127.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564507
CATALOG NUMBER: SQ4-PR1-150U-125D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564507

CATALOG NUMBER: SQ4-PR1-150U-125D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38				
2	88	81	75	70	81	75	69	65	62	59	55	51	48	46	40	39	37	32				
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				
4	74	63	56	50	68	58	52	47	49	44	40	40	37	34	32	30	28	24				
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21				
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18				
7	58	46	38	33	53	42	35	31	36	31	27	30	26	23	24	21	19	16				
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	15	13				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18053	18053	18053
5°	18215	18075	17981
10°	18158	18031	17937
15°	18078	17965	17869
20°	17987	17871	17739
25°	17860	17740	17535
30°	17668	17542	17291
35°	17407	17255	17008
40°	17010	16828	16523
45°	16317	16031	15701
50°	15095	14732	14441
55°	13175	12877	12606
60°	11102	11009	10791
65°	9603	9639	9566
70°	8819	8866	8866
75°	8472	8472	8532
80°	7970	8058	7970
85°	6422	7135	7135



TEST NUMBER: P564507

CATALOG NUMBER: SQ4-PR1-150U-125D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.6	1.7
10°-20°	794.1	4.8
20°-30°	1197.8	7.3
30°-40°	1427.1	8.7
40°-50°	1407.0	8.5
50°-60°	1075.3	6.5
60°-70°	665.4	4.0
70°-80°	378.0	2.3
80°-90°	117.9	0.7
90°-100°	657.9	4.0
100°-110°	1778.8	10.8
110°-120°	1870.1	11.4
120°-130°	1519.0	9.2
130°-140°	1191.6	7.2
140°-150°	914.5	5.6
150°-160°	657.7	4.0
160°-170°	401.8	2.4
170°-180°	135.5	0.8
0°-30°	2269.4	13.8
0°-40°	3696.6	22.4
0°-60°	6178.9	37.5
0°-90°	7340.3	44.6
90°-120°	4306.8	26.2
90°-150°	7931.9	48.2
90°-180°	9127.0	55.4
0°-180°	16467.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2935	2935	2935	2935	2935	
5°	2950	2918	2928	2917	2912	280
15°	2839	2809	2821	2811	2806	801
25°	2632	2600	2614	2586	2584	1211
35°	2318	2291	2298	2268	2265	1447
45°	1876	1851	1843	1810	1805	1437
55°	1229	1209	1201	1180	1176	1101
65°	660	655	662	657	657	668
75°	356	356	356	359	359	376
85°	91	96	101	101	101	106
90°	3	9	20	21	20	10
95°	102	358	1094	566	337	107
105°	331	511	1973	2911	2792	348
115°	582	712	1636	3168	3576	575
125°	797	913	1475	2489	2924	710
135°	955	1069	1435	2010	2275	738
145°	1111	1194	1416	1720	1851	695
155°	1254	1303	1403	1543	1594	578
165°	1365	1379	1410	1464	1472	385
175°	1417	1416	1411	1429	1426	135
180°	1416	1416	1416	1416	1416	

TEST NUMBER: P564507

CATALOG NUMBER: SQ4-PR1-150U-125D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2935.1	2935.1	2935.1	2935.1	2935.1
2.5°	2953.3	2927.6	2935.1	2928.7	2914.8
5°	2950.2	2918.1	2927.5	2917.3	2912.3
7.5°	2927.5	2895.8	2905.2	2895.1	2892.1
10°	2907.3	2877.6	2887.0	2876.8	2871.9
12.5°	2885.0	2853.4	2864.8	2852.5	2847.6
15°	2839.0	2809.3	2821.3	2811.1	2806.1
17.5°	2788.4	2756.8	2768.7	2756.9	2750.5
20°	2748.0	2718.3	2730.3	2712.5	2710.1
22.5°	2703.5	2673.8	2685.8	2662.0	2661.5
25°	2631.7	2599.6	2614.0	2586.1	2583.7
27.5°	2546.2	2516.6	2528.6	2500.2	2497.2
30°	2487.6	2457.9	2469.9	2439.5	2434.5
32.5°	2420.9	2393.2	2403.2	2372.8	2369.8
35°	2318.2	2291.0	2298.0	2267.6	2265.1
37.5°	2201.4	2176.7	2180.7	2147.3	2144.8
40°	2118.5	2093.8	2095.8	2060.3	2057.8
42.5°	2027.5	2002.8	2000.7	1965.2	1962.8
45°	1875.8	1851.1	1842.9	1810.0	1805.0
47.5°	1702.9	1678.2	1662.9	1636.1	1632.6
50°	1577.5	1552.8	1539.6	1516.7	1509.2
52.5°	1442.0	1417.3	1406.1	1385.2	1377.8
55°	1228.6	1208.9	1200.8	1180.5	1175.5
57.5°	1025.9	1012.5	1010.2	990.4	988.5
60°	902.5	895.1	894.9	877.2	877.2
62.5°	797.3	791.9	795.8	784.2	782.2
65°	659.8	654.9	662.3	657.3	657.3
67.5°	551.1	551.1	555.7	553.6	553.6
70°	490.4	490.4	493.0	493.0	493.0
72.5°	435.8	433.9	440.4	440.3	438.4
75°	356.5	356.5	356.5	359.0	359.0
77.5°	277.6	278.1	280.1	279.6	277.6
80°	225.0	227.5	227.5	225.0	225.0
82.5°	172.4	174.9	174.9	174.4	172.4
85°	91.0	96.0	101.1	101.1	101.1
87.5°	26.9	36.0	44.4	44.7	42.4
90°	3.0	9.0	19.8	21.3	19.8
92.5°	43.3	157.7	311.2	135.1	97.8
95°	102.1	358.4	1094.1	566.2	336.8
97.5°	164.0	411.0	1705.4	1411.3	1036.5
100°	210.3	432.3	1895.6	1976.9	1598.4
102.5°	252.9	461.8	1962.6	2405.7	2122.6
105°	330.7	510.9	1973.3	2910.8	2791.6
107.5°	402.6	567.1	1887.1	3225.8	3265.5
110°	458.7	607.7	1810.3	3310.4	3478.8



TEST NUMBER: P564507

CATALOG NUMBER: SQ4-PR1-150U-125D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	508.6	648.1	1739.5	3293.5	3576.3
115°	582.1	711.7	1636.5	3168.1	3576.3
117.5°	654.0	775.6	1568.6	2976.4	3439.2
120°	697.9	817.1	1528.4	2838.9	3311.2
122.5°	739.3	856.1	1504.0	2691.5	3167.3
125°	796.9	913.2	1475.0	2489.1	2924.1
127.5°	850.0	964.1	1458.0	2323.9	2706.5
130°	879.2	996.9	1450.6	2221.9	2567.6
132.5°	909.7	1026.2	1443.3	2129.9	2448.1
135°	955.4	1068.6	1435.4	2009.8	2275.0
137.5°	1001.4	1108.4	1428.7	1912.4	2128.4
140°	1033.1	1132.9	1426.3	1849.7	2041.9
142.5°	1063.6	1157.5	1421.4	1793.1	1961.4
145°	1110.8	1194.3	1415.6	1720.3	1851.4
147.5°	1153.8	1227.7	1408.9	1654.4	1755.1
150°	1185.5	1251.1	1406.5	1618.6	1699.0
152.5°	1214.8	1272.0	1405.2	1585.3	1651.5
155°	1254.1	1303.2	1403.4	1543.2	1593.9
157.5°	1294.9	1329.2	1403.7	1513.9	1547.2
160°	1318.1	1346.4	1404.9	1495.4	1519.2
162.5°	1336.4	1359.9	1406.1	1480.6	1498.5
165°	1365.3	1378.7	1409.5	1464.5	1472.0
167.5°	1385.1	1394.4	1409.8	1450.7	1454.3
170°	1397.3	1401.8	1411.0	1444.5	1444.5
172.5°	1407.1	1408.0	1411.0	1437.2	1436.0
175°	1417.1	1415.6	1411.0	1429.2	1426.3
177.5°	1420.5	1416.9	1410.7	1422.8	1419.3
180°	1415.6	1415.6	1415.6	1415.6	1415.6

(END OF REPORT)