

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P520228

Luminaire Tested: **SQ4-F-100U-100D-840-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P520228
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G3-1910-536-19)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-F-100U-100D-840-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8035.1 lumens
Efficiency: N/A
Efficacy: 138.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 57.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520228
CATALOG NUMBER: SQ4-F-100U-100D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P520228

CATALOG NUMBER: SQ4-F-100U-100D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47	42
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39	35
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33	29
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	31	27	25	22
6	63	50	42	36	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	45	37	32	53	42	35	30	36	31	26	31	26	23	25	22	19	17
8	54	41	33	28	49	38	31	27	33	27	23	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	34	27	22	43	32	26	21	28	23	19	24	19	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13454	13454	13454
5°	13514	13329	13431
10°	13445	13276	13380
15°	13364	13182	13287
20°	13225	13069	13177
25°	13081	12929	13030
30°	12923	12784	12847
35°	12760	12602	12670
40°	12547	12404	12416
45°	12326	12158	12118
50°	12010	11865	11837
55°	11655	11527	11446
60°	11302	11097	11060
65°	10750	10507	10422
70°	9989	9746	9557
75°	8919	8634	8456
80°	7337	7072	6753
85°	4340	4774	4880



TEST NUMBER: P520228

CATALOG NUMBER: SQ4-F-100U-100D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.6	1.7
10°-20°	391.9	4.9
20°-30°	588.6	7.3
30°-40°	702.4	8.7
40°-50°	719.9	9.0
50°-60°	641.1	8.0
60°-70°	477.9	5.9
70°-80°	258.8	3.2
80°-90°	60.2	0.7
90°-100°	292.4	3.6
100°-110°	807.2	10.0
110°-120°	832.5	10.4
120°-130°	669.0	8.3
130°-140°	525.7	6.5
140°-150°	403.2	5.0
150°-160°	289.8	3.6
160°-170°	177.2	2.2
170°-180°	59.7	0.7
0°-30°	1118.1	13.9
0°-40°	1820.5	22.7
0°-60°	3181.5	39.6
0°-90°	3978.4	49.5
90°-120°	1932.1	24.0
90°-150°	3530.0	43.9
90°-180°	4057.0	50.5
0°-180°	8035.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1458	1458	1458	1458	1458	
5°	1459	1456	1439	1452	1450	138
15°	1399	1394	1380	1391	1391	394
25°	1285	1282	1270	1277	1280	592
35°	1133	1128	1119	1121	1125	707
45°	945	940	932	927	929	727
55°	725	726	717	710	712	649
65°	492	490	481	476	477	487
75°	250	247	242	237	237	266
85°	41	45	45	46	46	57
90°	2	4	8	9	10	4
95°	43	158	530	218	142	46
105°	144	222	888	1356	1277	153
115°	258	312	715	1416	1610	253
125°	354	402	648	1097	1288	315
135°	426	472	630	889	1002	329
145°	494	528	622	757	814	309
155°	556	575	617	679	700	256
165°	602	610	620	644	649	170
175°	624	625	621	630	628	59
180°	624	624	624	624	624	

TEST NUMBER: P520228

CATALOG NUMBER: SQ4-F-100U-100D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1458.2	1458.2	1458.2	1458.2	1458.2
2.5°	1463.7	1460.7	1447.8	1458.1	1456.5
5°	1459.2	1456.2	1439.2	1452.1	1450.2
7.5°	1445.5	1442.6	1427.6	1439.5	1437.8
10°	1435.1	1432.2	1417.1	1429.1	1428.2
12.5°	1421.5	1418.6	1403.5	1415.5	1414.5
15°	1399.1	1394.2	1380.1	1391.1	1391.1
17.5°	1369.5	1365.7	1352.7	1361.9	1362.1
20°	1347.0	1344.1	1331.1	1341.1	1342.1
22.5°	1324.6	1321.8	1307.0	1316.3	1318.1
25°	1285.0	1282.1	1270.0	1277.1	1280.0
27.5°	1244.2	1239.9	1227.9	1234.3	1236.3
30°	1213.0	1211.0	1200.0	1203.1	1205.9
32.5°	1180.2	1178.2	1168.8	1170.3	1175.5
35°	1132.9	1128.1	1118.9	1121.0	1124.9
37.5°	1077.0	1074.7	1065.8	1064.7	1068.4
40°	1041.8	1037.9	1029.9	1027.9	1030.9
42.5°	1003.4	999.4	989.8	987.9	991.6
45°	944.7	939.9	931.8	926.8	928.7
47.5°	879.1	879.1	870.7	865.0	867.9
50°	836.7	836.7	826.6	821.7	824.7
52.5°	792.7	793.5	782.7	780.0	779.0
55°	724.6	725.6	716.6	709.6	711.6
57.5°	658.9	656.8	646.3	641.8	642.7
60°	612.5	609.6	601.4	594.6	599.4
62.5°	565.3	563.9	555.9	548.0	547.4
65°	492.4	490.5	481.3	476.4	477.4
67.5°	419.9	417.6	409.3	402.2	404.8
70°	370.3	370.3	361.3	357.2	354.3
72.5°	324.7	320.7	314.1	308.4	306.3
75°	250.2	247.3	242.2	237.2	237.2
77.5°	182.1	179.6	176.4	172.9	171.9
80°	138.1	137.1	133.1	132.0	127.1
82.5°	97.3	97.1	94.7	92.0	91.8
85°	41.0	45.0	45.1	46.1	46.1
87.5°	7.6	12.7	12.8	11.4	11.6
90°	2.0	4.0	8.0	9.0	10.0
92.5°	18.0	74.6	133.4	48.7	38.0
95°	42.9	158.2	530.4	218.0	141.9
97.5°	71.1	177.2	785.8	605.0	438.1
100°	91.9	188.6	880.1	886.3	720.2
102.5°	111.9	201.5	898.5	1095.1	937.7
105°	143.8	222.0	888.1	1355.8	1276.7
107.5°	177.9	247.4	838.6	1481.6	1510.4
110°	201.8	264.3	800.2	1508.6	1602.3



TEST NUMBER: P520228

CATALOG NUMBER: SQ4-F-100U-100D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.4	283.5	764.2	1487.2	1625.5
115°	257.7	311.5	715.3	1416.0	1610.3
117.5°	287.7	341.2	683.1	1315.7	1536.8
120°	307.6	360.5	670.3	1247.8	1470.5
122.5°	326.8	377.3	659.9	1184.4	1395.4
125°	353.6	402.5	648.3	1097.2	1287.7
127.5°	376.4	425.3	641.5	1023.4	1187.8
130°	391.6	440.4	638.3	978.4	1127.8
132.5°	406.0	452.5	635.2	940.5	1075.9
135°	425.6	471.5	630.3	888.6	1002.0
137.5°	447.5	489.4	628.0	845.1	941.8
140°	459.5	500.5	626.4	816.1	901.1
142.5°	473.1	511.0	624.8	790.3	865.1
145°	493.5	527.6	622.3	756.6	814.1
147.5°	513.1	543.0	620.1	728.1	772.8
150°	527.5	551.9	619.3	711.1	747.3
152.5°	538.6	561.5	618.6	696.6	726.5
155°	556.4	575.0	617.4	678.8	700.3
157.5°	572.9	587.1	617.6	665.8	680.5
160°	582.4	595.1	618.4	658.5	669.3
162.5°	590.4	601.5	619.2	652.1	660.5
165°	602.3	610.1	620.3	644.5	649.3
167.5°	611.5	616.3	621.3	639.7	641.3
170°	616.4	620.2	621.3	637.4	637.4
172.5°	620.3	622.7	621.3	634.1	633.3
175°	624.4	625.3	621.3	630.3	628.4
177.5°	626.0	625.2	621.1	626.7	625.2
180°	624.4	624.4	624.4	624.4	624.4

(END OF REPORT)