

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P562730

Luminaire Tested: **SQ4-PC3-075U-075D-840-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562730
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-075D-840-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5954.8 lumens
Efficiency: N/A
Efficacy: 140.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 42.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562730
CATALOG NUMBER: SQ4-PC3-075U-075D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562730

CATALOG NUMBER: SQ4-PC3-075U-075D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49		
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42		
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	40	35		
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34	29		
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25		
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22		
6	63	51	42	37	58	47	40	34	40	34	30	34	29	26	28	25	22	19		
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17		
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15		
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14		
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9904	9904	9904
5°	9979	9914	9877
10°	9954	9908	9880
15°	9902	9902	9893
20°	9837	9866	9866
25°	9744	9815	9785
30°	9625	9742	9700
35°	9482	9628	9560
40°	9326	9457	9362
45°	9156	9221	9079
50°	8916	8916	8774
55°	8633	8522	8393
60°	8217	8053	7923
65°	7595	7442	7377
70°	6649	6703	6676
75°	5351	5917	5953
80°	3804	5016	5069
85°	2318	4213	4213



TEST NUMBER: P562730

CATALOG NUMBER: SQ4-PC3-075U-075D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.6	1.7
10°-20°	291.5	4.9
20°-30°	441.5	7.4
30°-40°	529.3	8.9
40°-50°	539.7	9.1
50°-60°	471.1	7.9
60°-70°	337.3	5.7
70°-80°	173.7	2.9
80°-90°	45.1	0.8
90°-100°	218.9	3.7
100°-110°	602.3	10.1
110°-120°	621.7	10.4
120°-130°	498.1	8.4
130°-140°	391.2	6.6
140°-150°	299.8	5.0
150°-160°	215.6	3.6
160°-170°	131.8	2.2
170°-180°	44.4	0.7
0°-30°	834.6	14.0
0°-40°	1363.9	22.9
0°-60°	2374.8	39.9
0°-90°	2930.9	49.2
90°-120°	1442.9	24.2
90°-150°	2632.1	44.2
90°-180°	3024.0	50.8
0°-180°	5954.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1074	1074	1074	1074	1074	
5°	1078	1067	1070	1068	1066	102
15°	1037	1028	1037	1037	1036	292
25°	957	950	964	961	961	441
35°	842	840	855	849	849	527
45°	702	700	707	698	696	540
55°	537	530	530	522	522	478
65°	348	340	341	338	338	344
75°	150	157	166	167	167	162
85°	22	34	40	41	40	30
90°	1	4	7	9	9	3
95°	33	120	387	166	106	34
105°	108	166	664	1011	943	113
115°	191	232	532	1060	1203	188
125°	263	299	483	817	957	234
135°	317	352	469	661	748	245
145°	366	392	462	563	606	230
155°	415	428	459	506	520	191
165°	448	454	461	480	483	126
175°	464	465	462	468	467	44
180°	464	464	464	464	464	

TEST NUMBER: P562730

CATALOG NUMBER: SQ4-PC3-075U-075D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1073.5	1073.5	1073.5	1073.5	1073.5
2.5°	1079.8	1070.5	1073.5	1071.0	1067.1
5°	1077.5	1066.8	1070.5	1067.5	1066.5
7.5°	1069.7	1059.0	1063.9	1061.9	1061.0
10°	1062.5	1051.9	1057.6	1055.6	1054.6
12.5°	1053.0	1043.1	1049.6	1047.6	1047.4
15°	1036.7	1028.0	1036.7	1036.7	1035.7
17.5°	1016.2	1008.3	1017.6	1018.2	1017.6
20°	1001.9	993.2	1004.9	1003.9	1004.9
22.5°	984.4	977.2	989.8	987.2	988.2
25°	957.2	950.4	964.1	961.2	961.2
27.5°	925.0	920.1	935.1	931.9	931.9
30°	903.5	898.7	914.4	910.5	910.5
32.5°	879.7	876.4	891.4	886.6	886.6
35°	841.9	839.9	854.8	848.8	848.8
37.5°	802.9	801.2	814.7	807.4	805.1
40°	774.3	773.3	785.2	777.3	777.3
42.5°	745.7	744.7	755.0	745.5	745.5
45°	701.7	699.8	706.7	697.7	695.8
47.5°	653.8	651.9	656.2	646.5	645.5
50°	621.2	619.3	621.2	612.3	611.3
52.5°	587.8	584.3	584.6	575.7	575.5
55°	536.7	529.9	529.8	521.8	521.8
57.5°	482.7	473.7	474.5	467.7	466.8
60°	445.3	435.6	436.4	430.4	429.4
62.5°	408.7	397.4	399.8	393.0	392.8
65°	347.9	340.1	340.9	337.9	337.9
67.5°	289.4	282.3	287.5	285.1	284.9
70°	246.5	241.6	248.5	248.5	247.5
72.5°	206.7	206.6	215.1	215.1	215.7
75°	150.1	156.9	166.0	167.0	167.0
77.5°	100.2	112.2	122.3	122.7	122.5
80°	71.6	85.2	94.4	96.4	95.4
82.5°	48.5	62.9	70.6	72.5	71.6
85°	21.9	33.5	39.8	40.7	39.8
87.5°	6.6	14.1	17.3	17.6	16.1
90°	1.0	3.9	6.9	8.9	8.9
92.5°	13.6	58.2	100.9	38.8	31.8
95°	32.6	119.5	387.1	165.5	105.7
97.5°	53.1	132.5	590.8	455.2	321.2
100°	68.1	140.6	654.8	660.9	539.2
102.5°	82.4	150.2	671.4	819.9	708.3
105°	107.6	165.6	663.7	1010.8	943.2
107.5°	131.7	184.7	625.9	1104.2	1124.3
110°	149.1	197.4	597.5	1127.4	1197.0



TEST NUMBER: P562730

CATALOG NUMBER: SQ4-PC3-075U-075D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	164.9	211.7	569.1	1112.5	1218.3
115°	190.6	232.1	532.3	1060.0	1202.9
117.5°	215.1	253.3	509.0	986.3	1148.0
120°	230.1	266.8	498.7	931.2	1098.2
122.5°	243.5	280.2	491.6	882.8	1041.3
125°	262.7	299.4	482.9	817.0	957.0
127.5°	280.9	315.8	477.2	762.1	884.9
130°	290.4	326.1	474.1	729.4	841.4
132.5°	301.4	337.1	471.7	700.7	801.9
135°	317.0	351.8	469.1	660.7	747.6
137.5°	331.6	363.9	466.9	628.4	700.0
140°	342.7	372.6	466.1	606.9	671.6
142.5°	352.2	379.8	464.6	587.7	643.1
145°	366.4	391.5	462.2	562.9	606.4
147.5°	381.6	403.2	461.0	541.0	575.8
150°	391.1	410.4	460.2	529.0	556.0
152.5°	399.8	417.6	459.4	518.6	541.0
155°	414.8	428.3	459.2	506.0	520.5
157.5°	425.7	436.7	459.2	495.6	505.7
160°	433.6	442.2	459.2	490.0	497.8
162.5°	439.9	447.0	460.0	485.3	491.4
165°	448.4	454.2	461.2	480.0	482.9
167.5°	454.3	458.7	462.2	475.6	476.4
170°	458.2	461.1	462.2	474.1	474.1
172.5°	461.4	462.8	462.2	471.7	470.9
175°	464.2	465.1	462.2	468.1	467.1
177.5°	465.0	465.0	461.8	466.5	465.0
180°	464.2	464.2	464.2	464.2	464.2

(END OF REPORT)