

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562922

Luminaire Tested: **SQ4-PC3-100U-075D-840-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562922
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-075D-840-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6987.8 lumens
Efficiency: N/A
Efficacy: 142.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 49.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562922
CATALOG NUMBER: SQ4-PC3-100U-075D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562922

CATALOG NUMBER: SQ4-PC3-100U-075D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	87	84	81	78	69	67	65	56	54	53	43	42	41	35
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	31	30	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	22
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22	19
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	22	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	13
9	49	37	29	24	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9904	9904	9904
5°	9979	9914	9877
10°	9954	9908	9880
15°	9902	9902	9893
20°	9837	9866	9866
25°	9744	9815	9785
30°	9625	9742	9700
35°	9482	9628	9560
40°	9326	9457	9362
45°	9156	9221	9079
50°	8916	8916	8774
55°	8633	8522	8393
60°	8217	8053	7923
65°	7595	7442	7377
70°	6649	6703	6676
75°	5351	5917	5953
80°	3804	5016	5069
85°	2318	4213	4213



TEST NUMBER: P562922

CATALOG NUMBER: SQ4-PC3-100U-075D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.6	1.5
10°-20°	291.5	4.2
20°-30°	441.5	6.3
30°-40°	529.3	7.6
40°-50°	539.7	7.7
50°-60°	471.1	6.7
60°-70°	337.3	4.8
70°-80°	173.7	2.5
80°-90°	45.2	0.6
90°-100°	292.4	4.2
100°-110°	807.2	11.6
110°-120°	832.5	11.9
120°-130°	669.0	9.6
130°-140°	525.7	7.5
140°-150°	403.2	5.8
150°-160°	289.8	4.1
160°-170°	177.2	2.5
170°-180°	59.8	0.9
0°-30°	834.6	11.9
0°-40°	1363.9	19.5
0°-60°	2374.8	34.0
0°-90°	2931.0	41.9
90°-120°	1932.1	27.6
90°-150°	3530.0	50.5
90°-180°	4057.0	58.1
0°-180°	6987.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1074	1074	1074	1074	1074	
5°	1078	1067	1070	1068	1066	102
15°	1037	1028	1037	1037	1036	292
25°	957	950	964	961	961	441
35°	842	840	855	849	849	527
45°	702	700	707	698	696	540
55°	537	530	530	522	522	478
65°	348	340	341	338	338	344
75°	150	157	166	167	167	162
85°	22	34	40	41	40	30
90°	2	4	8	9	10	4
95°	43	158	530	218	142	46
105°	144	222	888	1356	1277	153
115°	258	312	715	1416	1610	253
125°	354	402	648	1097	1288	315
135°	426	472	630	889	1002	329
145°	494	528	622	756	814	309
155°	556	575	617	679	700	256
165°	602	610	620	644	649	170
175°	624	625	621	630	628	59
180°	624	624	624	624	624	



TEST NUMBER: P562922

CATALOG NUMBER: SQ4-PC3-100U-075D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1073.5	1073.5	1073.5	1073.5	1073.5
2.5°	1079.8	1070.5	1073.5	1071.0	1067.1
5°	1077.5	1066.8	1070.5	1067.5	1066.5
7.5°	1069.7	1059.0	1063.9	1061.9	1061.0
10°	1062.5	1051.9	1057.6	1055.6	1054.6
12.5°	1053.0	1043.1	1049.6	1047.6	1047.4
15°	1036.7	1028.0	1036.7	1036.7	1035.7
17.5°	1016.2	1008.3	1017.6	1018.2	1017.6
20°	1001.9	993.2	1004.9	1003.9	1004.9
22.5°	984.4	977.2	989.8	987.2	988.2
25°	957.2	950.4	964.1	961.2	961.2
27.5°	925.0	920.1	935.1	931.9	931.9
30°	903.5	898.7	914.4	910.5	910.5
32.5°	879.7	876.4	891.4	886.6	886.6
35°	841.9	839.9	854.8	848.8	848.8
37.5°	802.9	801.2	814.7	807.4	805.1
40°	774.3	773.3	785.2	777.3	777.3
42.5°	745.7	744.7	755.0	745.5	745.5
45°	701.7	699.8	706.7	697.7	695.8
47.5°	653.8	651.9	656.2	646.5	645.5
50°	621.2	619.3	621.2	612.3	611.3
52.5°	587.8	584.3	584.6	575.7	575.5
55°	536.7	529.9	529.8	521.8	521.8
57.5°	482.7	473.7	474.5	467.7	466.8
60°	445.3	435.6	436.4	430.4	429.4
62.5°	408.7	397.4	399.8	393.0	392.8
65°	347.9	340.1	340.9	337.9	337.9
67.5°	289.4	282.3	287.5	285.1	284.9
70°	246.5	241.6	248.5	248.5	247.5
72.5°	206.7	206.6	215.1	215.1	215.7
75°	150.1	156.9	166.0	167.0	167.0
77.5°	100.2	112.2	122.3	122.7	122.5
80°	71.6	85.2	94.4	96.4	95.4
82.5°	48.5	62.9	70.6	72.5	71.6
85°	21.9	33.5	39.8	40.7	39.8
87.5°	6.8	14.1	17.5	17.7	16.3
90°	2.0	4.0	8.0	9.0	10.0
92.5°	18.0	74.6	133.5	48.7	38.0
95°	43.0	158.2	530.5	218.0	141.9
97.5°	71.1	177.2	785.8	605.0	438.1
100°	91.9	188.6	880.1	886.3	720.3
102.5°	111.9	201.6	898.5	1095.1	937.6
105°	143.9	222.0	888.1	1355.8	1276.7
107.5°	177.8	247.4	838.5	1481.5	1510.4
110°	201.8	264.3	800.2	1508.6	1602.3



TEST NUMBER: P562922

CATALOG NUMBER: SQ4-PC3-100U-075D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.4	283.5	764.2	1487.2	1625.5
115°	257.7	311.5	715.3	1416.0	1610.3
117.5°	287.7	341.2	683.1	1315.7	1536.8
120°	307.7	360.4	670.3	1247.8	1470.5
122.5°	326.9	377.3	659.9	1184.4	1395.4
125°	353.6	402.5	648.3	1097.2	1287.7
127.5°	376.4	425.2	641.5	1023.5	1187.8
130°	391.6	440.4	638.3	978.4	1127.8
132.5°	406.0	452.5	635.1	940.5	1075.9
135°	425.6	471.5	630.3	888.7	1002.0
137.5°	447.5	489.3	628.0	845.1	941.8
140°	459.5	500.5	626.4	816.1	901.1
142.5°	473.1	511.0	624.8	790.3	865.1
145°	493.5	527.7	622.4	756.5	814.2
147.5°	513.1	543.0	620.2	728.1	772.8
150°	527.5	551.9	619.4	711.1	747.2
152.5°	538.6	561.5	618.6	696.6	726.4
155°	556.4	575.0	617.4	678.8	700.3
157.5°	572.8	587.1	617.6	665.8	680.5
160°	582.4	595.1	618.4	658.6	669.3
162.5°	590.4	601.5	619.2	652.1	660.5
165°	602.4	610.2	620.4	644.4	649.3
167.5°	611.6	616.3	621.4	639.8	641.3
170°	616.4	620.3	621.4	637.3	637.3
172.5°	620.4	622.7	621.4	634.1	633.3
175°	624.4	625.3	621.4	630.3	628.4
177.5°	626.0	625.2	621.2	626.7	625.2
180°	624.4	624.4	624.4	624.4	624.4

(END OF REPORT)