

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518550

Luminaire Tested: **SQ4-BB-075U-100D-840-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518550
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-075U-100D-840-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10985.1 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 108.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518550
CATALOG NUMBER: SQ4-BB-075U-100D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P518550

CATALOG NUMBER: SQ4-BB-075U-100D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45
1	98	95	91	88	90	87	84	82	73	71	69	60	59	58	48	47	47	41
2	91	84	79	75	83	78	74	70	66	63	60	55	53	51	44	43	42	37
3	84	76	69	64	77	70	65	60	60	56	52	50	47	45	41	39	38	33
4	78	68	61	56	71	63	57	53	54	50	46	46	42	40	38	36	34	30
5	72	62	55	49	66	57	51	46	49	45	41	42	38	36	35	32	31	28
6	67	56	49	44	62	52	46	41	45	40	37	38	35	32	32	30	28	25
7	62	51	44	39	57	48	42	37	41	37	33	36	32	29	30	27	26	23
8	58	47	40	35	54	44	38	33	38	33	30	33	29	27	28	25	23	21
9	54	43	36	32	50	41	34	30	35	31	27	31	27	25	26	24	22	20
10	51	40	33	29	47	38	32	28	33	28	25	29	25	23	24	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19083	19083	19083
5°	18777	18730	18869
10°	17569	17803	18300
15°	15972	16479	17396
20°	14178	14915	16221
25°	12347	13325	14904
30°	10576	11737	13657
35°	8769	9963	12150
40°	6737	7966	10353
45°	4870	6032	8330
50°	3318	4495	6607
55°	2157	3252	5134
60°	1237	2290	3712
65°	327	1398	1879
70°	162	432	540
75°	71	36	0
80°	53	0	0
85°	0	0	0



TEST NUMBER: P518550

CATALOG NUMBER: SQ4-BB-075U-100D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	377.5	3.4
10°-20°	965.5	8.8
20°-30°	1208.7	11.0
30°-40°	1116.4	10.2
40°-50°	750.2	6.8
50°-60°	387.5	3.5
60°-70°	121.4	1.1
70°-80°	7.7	0.1
80°-90°	2.5	0.0
90°-100°	437.9	4.0
100°-110°	1204.6	11.0
110°-120°	1243.4	11.3
120°-130°	996.2	9.1
130°-140°	782.5	7.1
140°-150°	599.6	5.5
150°-160°	431.1	3.9
160°-170°	263.6	2.4
170°-180°	88.9	0.8
0°-30°	2551.7	23.2
0°-40°	3668.1	33.4
0°-60°	4805.7	43.7
0°-90°	4937.3	44.9
90°-120°	2885.9	26.3
90°-150°	5264.2	47.9
90°-180°	6048.0	55.1
0°-180°	10985.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4137	4137	4137	4137	4137	
5°	4055	4014	4045	4059	4075	376
15°	3344	3333	3450	3566	3642	931
25°	2426	2445	2618	2797	2928	1112
35°	1557	1596	1769	1977	2158	965
45°	746	792	925	1105	1277	586
55°	268	313	404	519	638	250
65°	30	57	128	154	172	51
75°	4	4	2	0	0	6
85°	0	0	0	0	0	0
90°	2	8	14	18	18	4
95°	65	239	774	331	211	69
105°	215	331	1327	2022	1886	227
115°	381	464	1065	2120	2406	376
125°	525	599	966	1634	1914	469
135°	634	704	938	1321	1495	489
145°	733	783	924	1126	1213	460
155°	830	857	918	1012	1041	381
165°	897	908	922	960	966	253
175°	928	930	924	936	934	88
180°	928	928	928	928	928	



TEST NUMBER: P518550

CATALOG NUMBER: SQ4-BB-075U-100D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4136.8	4136.8	4136.8	4136.8	4136.8
2.5°	4146.5	4107.3	4117.6	4117.4	4106.4
5°	4054.8	4013.7	4044.8	4059.1	4074.8
7.5°	3883.5	3851.4	3911.1	3955.9	3988.3
10°	3750.6	3723.2	3800.6	3861.7	3906.7
12.5°	3596.9	3575.7	3669.3	3753.1	3810.6
15°	3344.3	3332.6	3450.4	3566.2	3642.5
17.5°	3073.7	3073.3	3207.8	3351.6	3443.6
20°	2888.0	2893.9	3038.1	3196.6	3304.3
22.5°	2702.3	2716.0	2870.0	3035.3	3158.6
25°	2425.7	2445.2	2617.8	2796.9	2928.0
27.5°	2159.9	2188.5	2370.0	2556.2	2715.9
30°	1985.4	2018.6	2203.5	2399.4	2563.8
32.5°	1814.0	1853.6	2033.8	2240.9	2408.5
35°	1557.1	1596.2	1769.2	1977.4	2157.5
37.5°	1291.7	1330.0	1499.0	1704.0	1898.5
40°	1118.8	1161.8	1322.9	1521.5	1719.2
42.5°	961.9	1004.9	1156.4	1351.6	1538.3
45°	746.5	791.5	924.6	1104.7	1276.9
47.5°	568.0	616.9	733.7	896.6	1053.5
50°	462.3	511.2	626.4	770.0	920.6
52.5°	377.5	424.8	528.8	664.0	802.2
55°	268.2	313.2	404.3	519.1	638.4
57.5°	185.3	224.1	305.8	401.6	495.1
60°	134.1	171.3	248.2	326.0	402.3
62.5°	89.3	123.3	198.5	258.1	309.4
65°	30.0	57.4	128.1	154.5	172.1
67.5°	15.2	18.3	67.2	71.0	76.9
70°	12.0	12.0	32.0	34.2	40.0
72.5°	8.8	8.8	12.8	16.4	17.6
75°	4.0	4.0	2.0	0.0	0.0
77.5°	2.0	2.0	1.6	0.0	0.0
80°	2.0	2.0	0.0	0.0	0.0
82.5°	0.4	0.4	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.4	1.6	2.8	3.6	3.6
90°	2.0	7.8	13.8	17.8	17.8
92.5°	27.3	116.5	201.9	77.5	63.6
95°	65.2	239.0	774.3	331.1	211.3
97.5°	106.3	265.0	1181.6	910.4	642.3
100°	136.3	281.1	1309.6	1321.8	1078.5
102.5°	164.7	300.3	1342.7	1639.9	1416.6
105°	215.3	331.2	1327.3	2021.5	1886.3
107.5°	263.5	369.3	1251.9	2208.4	2248.6
110°	298.3	394.8	1195.0	2254.9	2394.0

TEST NUMBER: P518550

CATALOG NUMBER: SQ4-BB-075U-100D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	329.9	423.3	1138.1	2224.9	2436.6
115°	381.2	464.3	1064.6	2120.0	2405.8
117.5°	430.2	506.7	1018.0	1972.7	2296.0
120°	460.2	533.6	997.5	1862.3	2196.4
122.5°	487.1	560.5	983.3	1765.5	2082.7
125°	525.4	598.8	965.9	1633.9	1914.0
127.5°	561.7	631.7	954.4	1524.1	1769.8
130°	580.7	652.2	948.1	1458.8	1682.9
132.5°	602.8	674.3	943.4	1401.5	1603.9
135°	634.0	703.6	938.2	1321.4	1495.2
137.5°	663.3	727.8	933.9	1256.7	1400.0
140°	685.4	745.3	932.3	1213.7	1343.1
142.5°	704.4	759.6	929.1	1175.4	1286.3
145°	732.8	783.0	924.4	1125.9	1212.8
147.5°	763.2	806.5	922.0	1082.0	1151.5
150°	782.2	820.8	920.4	1058.0	1112.0
152.5°	799.6	835.1	918.9	1037.2	1082.0
155°	829.6	856.6	918.5	1012.0	1040.9
157.5°	851.3	873.3	918.5	991.2	1011.3
160°	867.1	884.5	918.5	980.1	995.5
162.5°	879.8	894.0	920.1	970.5	982.9
165°	896.7	908.3	922.4	960.1	965.9
167.5°	908.6	917.5	924.4	951.3	952.8
170°	916.5	922.3	924.4	948.1	948.1
172.5°	922.8	925.5	924.4	943.3	941.8
175°	928.3	930.3	924.4	936.2	934.3
177.5°	929.9	929.9	923.6	933.0	929.9
180°	928.3	928.3	928.3	928.3	928.3

(END OF REPORT)