

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563282

Luminaire Tested: **SQ4-PP3-050U-050D-840-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563282
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-050D-840-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3982.1 lumens
Efficiency: N/A
Efficacy: 139.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 28.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563282
CATALOG NUMBER: SQ4-PP3-050U-050D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563282

CATALOG NUMBER: SQ4-PP3-050U-050D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49				
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42				
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	36				
3	82	72	65	59	75	67	61	55	57	52	48	48	44	41	39	36	34	30				
4	75	64	56	50	69	59	52	47	51	45	41	42	38	35	35	32	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23				
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7098	7098	7098
5°	7150	7106	7081
10°	7138	7087	7055
15°	7090	7052	7013
20°	7044	7003	6950
25°	6960	6911	6843
30°	6831	6795	6709
35°	6652	6607	6524
40°	6440	6399	6325
45°	6263	6220	6159
50°	6038	6000	5942
55°	5726	5651	5607
60°	5213	5063	5039
65°	4593	4401	4386
70°	3965	3801	3801
75°	3411	3365	3315
80°	3007	3044	2975
85°	2350	2572	2572



TEST NUMBER: P563282

CATALOG NUMBER: SQ4-PP3-050U-050D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.7	1.8
10°-20°	207.7	5.2
20°-30°	311.1	7.8
30°-40°	364.9	9.2
40°-50°	366.1	9.2
50°-60°	312.3	7.8
60°-70°	203.7	5.1
70°-80°	102.2	2.6
80°-90°	29.5	0.7
90°-100°	147.9	3.7
100°-110°	401.8	10.1
110°-120°	413.2	10.4
120°-130°	330.3	8.3
130°-140°	259.5	6.5
140°-150°	199.0	5.0
150°-160°	143.1	3.6
160°-170°	87.5	2.2
170°-180°	29.5	0.7
0°-30°	591.6	14.9
0°-40°	956.5	24.0
0°-60°	1634.8	41.1
0°-90°	1970.1	49.5
90°-120°	962.9	24.2
90°-150°	1751.8	44.0
90°-180°	2012.0	50.5
0°-180°	3982.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	772	765	767	765	765	73
15°	742	735	738	736	734	209
25°	684	676	679	673	672	314
35°	591	585	587	580	579	369
45°	480	477	477	472	472	370
55°	356	355	351	349	349	316
65°	210	206	202	200	201	210
75°	96	96	94	94	93	104
85°	22	24	24	24	24	26
90°	1	4	7	9	9	2
95°	22	81	258	112	75	23
105°	71	111	442	673	633	76
115°	127	154	354	704	802	125
125°	174	199	320	539	636	155
135°	210	233	311	439	495	162
145°	243	260	307	373	401	152
155°	274	284	305	335	345	127
165°	297	301	306	319	320	84
175°	308	309	307	311	310	29
180°	308	308	308	308	308	



TEST NUMBER: P563282

CATALOG NUMBER: SQ4-PP3-050U-050D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	769.3	769.3	769.3	769.3	769.3
2.5°	774.1	767.8	769.3	768.1	765.0
5°	772.0	764.7	767.3	764.6	764.6
7.5°	766.7	758.8	761.3	758.6	758.5
10°	761.9	754.0	756.5	753.8	753.1
12.5°	754.9	747.0	750.0	746.8	746.6
15°	742.3	735.1	738.3	735.5	734.2
17.5°	728.2	720.3	724.1	720.3	719.8
20°	717.4	709.5	713.3	707.9	707.9
22.5°	704.4	696.5	700.9	693.9	693.9
25°	683.7	675.8	678.9	672.9	672.2
27.5°	659.0	651.2	654.5	647.7	647.5
30°	641.2	633.9	637.8	630.4	629.7
32.5°	621.8	615.0	617.9	610.4	609.8
35°	590.6	584.7	586.6	579.8	579.2
37.5°	557.9	551.8	553.9	548.1	547.9
40°	534.7	530.7	531.3	526.5	525.2
42.5°	513.1	508.6	509.2	504.4	504.2
45°	480.0	476.8	476.7	472.0	472.0
47.5°	445.0	442.5	441.8	437.8	437.7
50°	420.7	418.7	418.0	414.6	414.0
52.5°	395.4	394.4	392.1	389.3	389.2
55°	356.0	354.7	351.3	349.2	348.6
57.5°	313.2	310.6	306.8	303.8	304.3
60°	282.5	279.9	274.4	273.1	273.1
62.5°	252.8	249.7	244.2	242.3	243.4
65°	210.4	206.4	201.6	200.3	200.9
67.5°	171.8	168.2	163.0	163.0	162.5
70°	147.0	145.0	140.9	140.9	140.9
72.5°	124.9	123.9	121.0	120.9	120.4
75°	95.7	95.7	94.4	93.7	93.0
77.5°	71.7	72.0	71.3	70.6	69.4
80°	56.6	58.0	57.3	56.6	56.0
82.5°	42.6	43.9	43.8	42.6	42.5
85°	22.2	24.2	24.3	24.3	24.3
87.5°	6.1	8.8	10.0	10.4	11.0
90°	1.0	3.9	6.9	8.9	8.9
92.5°	8.9	40.5	70.3	30.2	25.6
95°	21.8	80.9	257.6	112.1	75.3
97.5°	36.1	89.3	394.9	307.3	215.8
100°	45.6	95.0	437.0	442.9	357.7
102.5°	55.1	100.6	448.0	547.8	472.6
105°	71.3	111.1	441.9	672.9	633.1
107.5°	88.2	123.3	416.3	737.4	748.5
110°	100.1	132.0	397.3	750.1	797.6



TEST NUMBER: P563282

CATALOG NUMBER: SQ4-PP3-050U-050D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	110.4	140.8	378.3	739.6	811.1
115°	126.8	154.0	353.7	703.7	801.6
117.5°	142.3	168.2	338.1	652.9	763.1
120°	152.6	177.8	330.9	618.8	728.3
122.5°	161.3	186.5	326.2	584.6	690.2
125°	174.4	198.6	320.0	539.2	636.1
127.5°	186.1	210.1	316.7	504.8	588.0
130°	193.2	216.5	315.1	483.2	557.8
132.5°	200.3	223.6	313.5	464.8	530.9
135°	210.1	233.3	311.1	439.2	495.4
137.5°	220.6	241.7	309.9	416.6	463.9
140°	226.9	247.2	309.1	402.2	444.9
142.5°	233.2	252.0	308.3	391.0	426.6
145°	242.8	260.2	307.2	373.2	401.3
147.5°	253.5	268.4	306.2	359.2	381.3
150°	260.6	273.2	306.2	351.1	368.6
152.5°	266.1	277.2	305.4	343.9	358.3
155°	274.5	284.1	305.2	335.1	344.8
157.5°	282.6	290.1	305.2	329.1	336.5
160°	287.3	294.1	305.2	325.1	330.9
162.5°	292.1	297.3	306.0	321.9	326.2
165°	297.2	301.1	306.2	319.1	320.0
167.5°	302.6	304.5	307.2	315.7	316.5
170°	304.2	306.1	307.2	314.1	314.1
172.5°	305.8	306.9	307.2	312.5	312.5
175°	308.1	309.1	307.2	311.1	310.1
177.5°	308.9	308.9	306.6	309.7	308.1
180°	308.1	308.1	308.1	308.1	308.1

(END OF REPORT)