

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518646

Luminaire Tested: **SQ4-BB-0U-100D-840-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518646
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-0U-100D-840-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4934.9 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Direct

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518646
CATALOG NUMBER: SQ4-BB-0U-100D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P518646

CATALOG NUMBER: SQ4-BB-0U-100D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	50	71	61	54	49	59	53	49	58	53	49	57	52	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19083	19083	19083
5°	18777	18730	18869
10°	17569	17803	18300
15°	15972	16479	17396
20°	14178	14915	16221
25°	12347	13325	14904
30°	10576	11737	13657
35°	8769	9963	12150
40°	6737	7966	10353
45°	4870	6032	8330
50°	3318	4495	6607
55°	2157	3252	5134
60°	1237	2290	3712
65°	327	1398	1879
70°	162	432	540
75°	71	36	0
80°	53	0	0
85°	0	0	0



TEST NUMBER: P518646

CATALOG NUMBER: SQ4-BB-0U-100D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	377.5	7.7
10°-20°	965.5	19.6
20°-30°	1208.7	24.5
30°-40°	1116.4	22.6
40°-50°	750.2	15.2
50°-60°	387.5	7.9
60°-70°	121.4	2.5
70°-80°	7.7	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2551.7	51.7
0°-40°	3668.1	74.3
0°-60°	4805.7	97.4
0°-90°	4934.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4934.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4137	4137	4137	4137	4137	
5°	4055	4014	4045	4059	4075	376
15°	3344	3333	3450	3566	3642	931
25°	2426	2445	2618	2797	2928	1112
35°	1557	1596	1769	1977	2158	965
45°	746	792	925	1105	1277	586
55°	268	313	404	519	638	250
65°	30	57	128	154	172	51
75°	4	4	2	0	0	6
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P518646

CATALOG NUMBER: SQ4-BB-0U-100D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4136.8	4136.8	4136.8	4136.8	4136.8
2.5°	4146.5	4107.3	4117.6	4117.4	4106.4
5°	4054.8	4013.7	4044.8	4059.1	4074.8
7.5°	3883.5	3851.4	3911.1	3955.9	3988.3
10°	3750.6	3723.2	3800.6	3861.7	3906.7
12.5°	3596.9	3575.7	3669.3	3753.1	3810.6
15°	3344.3	3332.6	3450.4	3566.2	3642.5
17.5°	3073.7	3073.3	3207.8	3351.6	3443.6
20°	2888.0	2893.9	3038.1	3196.6	3304.3
22.5°	2702.3	2716.0	2870.0	3035.3	3158.6
25°	2425.7	2445.2	2617.8	2796.9	2928.0
27.5°	2159.9	2188.5	2370.0	2556.2	2715.9
30°	1985.4	2018.6	2203.5	2399.4	2563.8
32.5°	1814.0	1853.6	2033.8	2240.9	2408.5
35°	1557.1	1596.2	1769.2	1977.4	2157.5
37.5°	1291.7	1330.0	1499.0	1704.0	1898.5
40°	1118.8	1161.8	1322.9	1521.5	1719.2
42.5°	961.9	1004.9	1156.4	1351.6	1538.3
45°	746.5	791.5	924.6	1104.7	1276.9
47.5°	568.0	616.9	733.7	896.6	1053.5
50°	462.3	511.2	626.4	770.0	920.6
52.5°	377.5	424.8	528.8	664.0	802.2
55°	268.2	313.2	404.3	519.1	638.4
57.5°	185.3	224.1	305.8	401.6	495.1
60°	134.1	171.3	248.2	326.0	402.3
62.5°	89.3	123.3	198.5	258.1	309.4
65°	30.0	57.4	128.1	154.5	172.1
67.5°	15.2	18.3	67.2	71.0	76.9
70°	12.0	12.0	32.0	34.2	40.0
72.5°	8.8	8.8	12.8	16.4	17.6
75°	4.0	4.0	2.0	0.0	0.0
77.5°	2.0	2.0	1.6	0.0	0.0
80°	2.0	2.0	0.0	0.0	0.0
82.5°	0.4	0.4	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)