

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518766

Luminaire Tested: **SQ4-BB-100U-125D-840-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518766
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-100U-125D-840-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14272.6 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 140.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518766
CATALOG NUMBER: SQ4-BB-100U-125D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P518766

CATALOG NUMBER: SQ4-BB-100U-125D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	98	94	91	88	89	86	84	81	72	70	68	59	57	56	46	46	45	39
2	90	84	79	74	83	77	73	69	65	62	59	53	51	50	43	42	40	36
3	83	75	69	64	76	70	64	60	59	55	52	49	46	44	39	38	36	32
4	77	68	61	56	71	63	57	52	53	49	45	44	41	39	36	34	33	29
5	71	61	54	49	66	57	51	46	49	44	40	41	38	35	34	31	30	26
6	66	56	48	43	61	52	45	41	44	40	36	38	34	31	31	29	27	24
7	62	51	44	39	57	47	41	37	41	36	32	35	31	29	29	27	25	22
8	58	46	39	35	53	43	37	33	38	33	29	32	29	26	27	24	23	20
9	54	43	36	31	50	40	34	30	35	30	27	30	26	24	25	23	21	19
10	51	40	33	29	47	37	31	27	32	28	25	28	24	22	24	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23808	23808	23808
5°	23425	23367	23541
10°	21918	22210	22830
15°	19926	20558	21702
20°	17687	18607	20237
25°	15403	16623	18593
30°	13194	14643	17037
35°	10939	12430	15158
40°	8405	9939	12916
45°	6076	7525	10393
50°	4140	5609	8242
55°	2691	4057	6406
60°	1544	2856	4631
65°	409	1744	2344
70°	202	538	673
75°	89	45	0
80°	66	0	0
85°	0	0	0



TEST NUMBER: P518766

CATALOG NUMBER: SQ4-BB-100U-125D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	471.0	3.3
10°-20°	1204.5	8.4
20°-30°	1507.9	10.6
30°-40°	1392.8	9.8
40°-50°	935.9	6.6
50°-60°	483.4	3.4
60°-70°	151.4	1.1
70°-80°	9.6	0.1
80°-90°	2.8	0.0
90°-100°	584.8	4.1
100°-110°	1614.4	11.3
110°-120°	1664.9	11.7
120°-130°	1337.9	9.4
130°-140°	1051.5	7.4
140°-150°	806.4	5.7
150°-160°	579.6	4.1
160°-170°	354.4	2.5
170°-180°	119.5	0.8
0°-30°	3183.4	22.3
0°-40°	4576.2	32.1
0°-60°	5995.4	42.0
0°-90°	6159.2	43.2
90°-120°	3864.1	27.1
90°-150°	7060.0	49.5
90°-180°	8113.0	56.8
0°-180°	14272.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5161	5161	5161	5161	5161	
5°	5059	5007	5046	5064	5084	469
15°	4172	4158	4304	4449	4544	1162
25°	3026	3051	3266	3489	3653	1387
35°	1942	1991	2207	2467	2692	1203
45°	931	988	1154	1378	1593	731
55°	335	391	504	648	796	312
65°	38	72	160	193	215	63
75°	5	5	2	0	0	7
85°	0	0	0	0	0	1
90°	4	8	16	18	20	6
95°	86	316	1061	436	284	92
105°	288	444	1776	2712	2553	306
115°	516	623	1430	2832	3221	507
125°	707	805	1297	2194	2575	629
135°	851	943	1261	1777	2004	659
145°	987	1055	1245	1513	1628	618
155°	1113	1150	1235	1358	1401	513
165°	1205	1220	1241	1289	1299	340
175°	1249	1251	1243	1261	1257	119
180°	1249	1249	1249	1249	1249	



TEST NUMBER: P518766

CATALOG NUMBER: SQ4-BB-100U-125D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5161.0	5161.0	5161.0	5161.0	5161.0
2.5°	5172.9	5124.1	5137.0	5136.7	5123.0
5°	5058.6	5007.3	5046.1	5064.0	5083.6
7.5°	4844.9	4804.8	4879.3	4935.2	4975.7
10°	4679.1	4644.9	4741.5	4817.7	4873.8
12.5°	4487.3	4460.9	4577.7	4682.2	4754.0
15°	4172.2	4157.6	4304.5	4449.0	4544.2
17.5°	3834.6	3834.1	4001.9	4181.3	4296.1
20°	3602.9	3610.3	3790.2	3988.0	4122.3
22.5°	3371.2	3388.3	3580.5	3786.7	3940.5
25°	3026.2	3050.6	3265.9	3489.3	3652.9
27.5°	2694.6	2730.2	2956.7	3189.0	3388.2
30°	2476.9	2518.4	2749.0	2993.4	3198.4
32.5°	2263.1	2312.4	2537.3	2795.7	3004.7
35°	1942.5	1991.4	2207.2	2467.0	2691.6
37.5°	1611.5	1659.3	1870.1	2125.8	2368.5
40°	1395.7	1449.4	1650.4	1898.2	2144.8
42.5°	1200.0	1253.7	1442.7	1686.2	1919.1
45°	931.3	987.5	1153.5	1378.1	1593.0
47.5°	708.6	769.6	915.3	1118.5	1314.3
50°	576.8	637.8	781.5	960.6	1148.5
52.5°	470.9	530.0	659.7	828.4	1000.7
55°	334.6	390.7	504.4	647.6	796.5
57.5°	231.2	279.5	381.5	501.0	617.7
60°	167.3	213.7	309.6	406.7	501.9
62.5°	111.4	153.8	247.7	322.0	386.0
65°	37.5	71.6	159.8	192.8	214.7
67.5°	19.0	22.9	83.9	88.6	95.9
70°	15.0	15.0	39.9	42.6	49.9
72.5°	11.0	11.0	16.0	20.5	22.0
75°	5.0	5.0	2.5	0.0	0.0
77.5°	2.5	2.5	2.0	0.0	0.0
80°	2.5	2.5	0.0	0.0	0.0
82.5°	0.5	0.5	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.8	1.6	3.2	3.6	4.0
90°	4.0	7.9	16.0	18.0	20.0
92.5°	36.0	149.3	266.9	97.4	75.9
95°	85.9	316.4	1060.9	436.1	283.7
97.5°	142.3	354.4	1571.6	1210.0	876.3
100°	183.8	377.2	1760.2	1772.6	1440.5
102.5°	223.8	403.1	1796.9	2190.2	1875.3
105°	287.7	444.0	1776.2	2711.6	2553.4
107.5°	355.6	494.7	1677.1	2963.1	3020.9
110°	403.6	528.6	1600.3	3017.1	3204.7

TEST NUMBER: P518766

CATALOG NUMBER: SQ4-BB-100U-125D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	446.7	567.1	1528.4	2974.4	3251.0
115°	515.5	622.9	1430.5	2831.9	3220.7
117.5°	575.4	682.5	1366.2	2631.3	3073.6
120°	615.4	720.9	1340.6	2495.6	2941.0
122.5°	653.7	754.5	1319.8	2368.8	2790.7
125°	707.3	804.9	1296.7	2194.4	2575.3
127.5°	752.8	850.5	1283.1	2047.0	2375.5
130°	783.2	880.9	1276.7	1956.8	2255.7
132.5°	812.0	904.9	1270.3	1881.0	2151.8
135°	851.1	942.9	1260.7	1777.3	2003.9
137.5°	895.1	978.7	1255.9	1690.3	1883.7
140°	919.1	1001.1	1252.7	1632.2	1802.1
142.5°	946.2	1022.0	1249.5	1580.6	1730.2
145°	987.0	1055.4	1244.7	1513.1	1628.3
147.5°	1026.1	1085.9	1240.3	1456.1	1545.6
150°	1054.9	1103.7	1238.7	1422.2	1494.5
152.5°	1077.3	1123.0	1237.1	1393.1	1452.9
155°	1112.9	1150.0	1234.7	1357.6	1400.6
157.5°	1145.6	1174.1	1235.1	1331.7	1361.0
160°	1164.8	1190.2	1236.7	1317.1	1338.6
162.5°	1180.8	1203.1	1238.3	1304.2	1321.0
165°	1204.8	1220.4	1240.7	1288.9	1298.7
167.5°	1223.1	1232.5	1242.7	1279.5	1282.7
170°	1232.7	1240.5	1242.7	1274.7	1274.7
172.5°	1240.7	1245.4	1242.7	1268.3	1266.7
175°	1248.7	1250.7	1242.7	1260.6	1256.7
177.5°	1251.9	1250.3	1242.3	1253.4	1250.3
180°	1248.7	1248.7	1248.7	1248.7	1248.7

(END OF REPORT)