

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563642

Luminaire Tested: **SQ4-PP3-100U-125D-840-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563642
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-125D-840-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8978.8 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 68.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563642
CATALOG NUMBER: SQ4-PP3-100U-125D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563642

CATALOG NUMBER: SQ4-PP3-100U-125D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	34
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22	20
8	55	43	35	29	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	23	20	24	21	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17738	17738	17738
5°	17868	17759	17697
10°	17838	17711	17633
15°	17720	17623	17526
20°	17602	17503	17371
25°	17394	17273	17101
30°	17071	16982	16766
35°	16624	16511	16302
40°	16093	15992	15809
45°	15653	15544	15390
50°	15091	14995	14850
55°	14311	14121	14012
60°	13027	12655	12592
65°	11477	10998	10961
70°	9908	9501	9501
75°	8530	8409	8288
80°	7518	7608	7433
85°	5886	6426	6426



TEST NUMBER: P563642

CATALOG NUMBER: SQ4-PP3-100U-125D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.8	2.0
10°-20°	519.1	5.8
20°-30°	777.5	8.7
30°-40°	912.0	10.2
40°-50°	914.9	10.2
50°-60°	780.4	8.7
60°-70°	509.0	5.7
70°-80°	255.4	2.8
80°-90°	72.0	0.8
90°-100°	292.4	3.3
100°-110°	807.2	9.0
110°-120°	832.5	9.3
120°-130°	669.0	7.5
130°-140°	525.7	5.9
140°-150°	403.2	4.5
150°-160°	289.8	3.2
160°-170°	177.2	2.0
170°-180°	59.8	0.7
0°-30°	1478.4	16.5
0°-40°	2390.4	26.6
0°-60°	4085.7	45.5
0°-90°	4922.0	54.8
90°-120°	1932.1	21.5
90°-150°	3530.0	39.3
90°-180°	4057.0	45.2
0°-180°	8978.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1923	1923	1923	1923	1923	
5°	1929	1911	1918	1911	1911	183
15°	1855	1837	1845	1838	1835	523
25°	1709	1689	1697	1682	1680	786
35°	1476	1461	1466	1449	1447	922
45°	1200	1192	1191	1180	1180	924
55°	890	886	878	873	871	791
65°	526	516	504	500	502	525
75°	239	239	236	234	232	260
85°	56	60	61	61	61	65
90°	2	4	8	9	10	5
95°	43	158	530	218	142	46
105°	144	222	888	1356	1277	153
115°	258	312	715	1416	1610	253
125°	354	402	648	1097	1288	315
135°	426	472	630	889	1002	329
145°	494	528	622	756	814	309
155°	556	575	617	679	700	256
165°	602	610	620	644	649	170
175°	624	625	621	630	628	59
180°	624	624	624	624	624	



TEST NUMBER: P563642

CATALOG NUMBER: SQ4-PP3-100U-125D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1922.6	1922.6	1922.6	1922.6	1922.6
2.5°	1934.7	1918.9	1922.6	1919.7	1911.8
5°	1929.3	1911.2	1917.5	1910.8	1910.8
7.5°	1916.1	1896.4	1902.7	1895.9	1895.6
10°	1904.0	1884.2	1890.5	1883.8	1882.1
12.5°	1886.5	1866.7	1874.4	1866.3	1865.9
15°	1855.2	1837.0	1845.0	1838.2	1834.9
17.5°	1819.8	1800.0	1809.7	1800.2	1798.9
20°	1792.8	1773.0	1782.7	1769.2	1769.2
22.5°	1760.5	1740.7	1751.7	1734.2	1734.2
25°	1708.6	1688.8	1696.8	1681.6	1679.9
27.5°	1646.9	1627.4	1635.8	1618.6	1618.2
30°	1602.4	1584.3	1594.0	1575.4	1573.8
32.5°	1553.9	1537.1	1544.1	1525.5	1523.9
35°	1476.0	1461.2	1465.9	1449.0	1447.4
37.5°	1394.1	1379.0	1384.4	1369.9	1369.2
40°	1336.2	1326.3	1327.8	1315.9	1312.6
42.5°	1282.3	1271.1	1272.5	1260.7	1260.0
45°	1199.7	1191.5	1191.3	1179.5	1179.5
47.5°	1112.1	1105.8	1104.0	1094.2	1093.9
50°	1051.4	1046.5	1044.7	1036.2	1034.6
52.5°	988.1	985.8	980.0	972.9	972.6
55°	889.7	886.4	877.9	872.8	871.1
57.5°	782.8	776.2	766.7	759.3	760.6
60°	706.0	699.4	685.8	682.4	682.4
62.5°	631.9	624.0	610.3	605.6	608.3
65°	525.7	515.8	503.8	500.5	502.1
67.5°	429.3	420.4	407.4	407.4	406.1
70°	367.3	362.4	352.2	352.2	352.2
72.5°	312.1	309.7	302.3	302.3	300.9
75°	239.3	239.3	235.9	234.2	232.5
77.5°	179.3	179.9	178.3	176.5	173.6
80°	141.5	144.8	143.2	141.5	139.9
82.5°	106.5	109.8	109.5	106.5	106.2
85°	55.6	60.5	60.7	60.7	60.7
87.5°	15.2	20.9	23.2	23.4	24.9
90°	2.0	4.0	8.0	9.0	10.0
92.5°	18.0	74.6	133.5	48.7	38.0
95°	43.0	158.2	530.5	218.0	141.9
97.5°	71.1	177.2	785.8	605.0	438.1
100°	91.9	188.6	880.1	886.3	720.3
102.5°	111.9	201.6	898.5	1095.1	937.6
105°	143.9	222.0	888.1	1355.8	1276.7
107.5°	177.8	247.4	838.5	1481.5	1510.4
110°	201.8	264.3	800.2	1508.6	1602.3

TEST NUMBER: P563642

CATALOG NUMBER: SQ4-PP3-100U-125D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.4	283.5	764.2	1487.2	1625.5
115°	257.7	311.5	715.3	1416.0	1610.3
117.5°	287.7	341.2	683.1	1315.7	1536.8
120°	307.7	360.4	670.3	1247.8	1470.5
122.5°	326.9	377.3	659.9	1184.4	1395.4
125°	353.6	402.5	648.3	1097.2	1287.7
127.5°	376.4	425.2	641.5	1023.5	1187.8
130°	391.6	440.4	638.3	978.4	1127.8
132.5°	406.0	452.5	635.1	940.5	1075.9
135°	425.6	471.5	630.3	888.7	1002.0
137.5°	447.5	489.3	628.0	845.1	941.8
140°	459.5	500.5	626.4	816.1	901.1
142.5°	473.1	511.0	624.8	790.3	865.1
145°	493.5	527.7	622.4	756.5	814.2
147.5°	513.1	543.0	620.2	728.1	772.8
150°	527.5	551.9	619.4	711.1	747.2
152.5°	538.6	561.5	618.6	696.6	726.4
155°	556.4	575.0	617.4	678.8	700.3
157.5°	572.8	587.1	617.6	665.8	680.5
160°	582.4	595.1	618.4	658.6	669.3
162.5°	590.4	601.5	619.2	652.1	660.5
165°	602.4	610.2	620.4	644.4	649.3
167.5°	611.6	616.3	621.4	639.8	641.3
170°	616.4	620.3	621.4	637.3	637.3
172.5°	620.4	622.7	621.4	634.1	633.3
175°	624.4	625.3	621.4	630.3	628.4
177.5°	626.0	625.2	621.2	626.7	625.2
180°	624.4	624.4	624.4	624.4	624.4

(END OF REPORT)