

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563834

Luminaire Tested: **SQ4-PP3-150U-125D-840-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563834
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-125D-840-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11007.2 lumens
Efficiency: N/A
Efficacy: 132.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 83.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563834
CATALOG NUMBER: SQ4-PP3-150U-125D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563834

CATALOG NUMBER: SQ4-PP3-150U-125D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	39	37	32
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	36	34	32	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	24
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	42	37	57	47	40	34	39	34	30	33	28	25	26	23	21	18
7	58	45	38	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	34	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17738	17738	17738
5°	17868	17759	17697
10°	17838	17711	17633
15°	17720	17623	17526
20°	17602	17503	17371
25°	17394	17273	17101
30°	17071	16982	16766
35°	16624	16511	16302
40°	16093	15992	15809
45°	15653	15544	15390
50°	15091	14995	14850
55°	14311	14121	14012
60°	13027	12655	12592
65°	11477	10998	10961
70°	9908	9501	9501
75°	8530	8409	8288
80°	7518	7608	7433
85°	5886	6426	6426



TEST NUMBER: P563834

CATALOG NUMBER: SQ4-PP3-150U-125D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.8	1.7
10°-20°	519.1	4.7
20°-30°	777.5	7.1
30°-40°	912.0	8.3
40°-50°	914.9	8.3
50°-60°	780.4	7.1
60°-70°	509.0	4.6
70°-80°	255.4	2.3
80°-90°	72.6	0.7
90°-100°	438.6	4.0
100°-110°	1185.8	10.8
110°-120°	1246.8	11.3
120°-130°	1012.7	9.2
130°-140°	794.4	7.2
140°-150°	609.7	5.5
150°-160°	438.5	4.0
160°-170°	267.9	2.4
170°-180°	90.3	0.8
0°-30°	1478.4	13.4
0°-40°	2390.4	21.7
0°-60°	4085.7	37.1
0°-90°	4922.7	44.7
90°-120°	2871.2	26.1
90°-150°	5287.9	48.0
90°-180°	6085.0	55.3
0°-180°	11007.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1923	1923	1923	1923	1923	
5°	1929	1911	1918	1911	1911	183
15°	1855	1837	1845	1838	1835	523
25°	1709	1689	1697	1682	1680	786
35°	1476	1461	1466	1449	1447	922
45°	1200	1192	1191	1180	1180	924
55°	890	886	878	873	871	791
65°	526	516	504	500	502	525
75°	239	239	236	234	232	260
85°	56	60	61	61	61	65
90°	2	6	13	14	13	7
95°	68	239	729	378	224	71
105°	220	341	1316	1940	1861	232
115°	388	474	1091	2112	2384	383
125°	531	609	983	1659	1949	474
135°	637	712	957	1340	1517	492
145°	741	796	944	1147	1234	463
155°	836	869	936	1029	1063	386
165°	910	919	940	976	981	256
175°	945	944	941	953	951	90
180°	944	944	944	944	944	



TEST NUMBER: P563834

CATALOG NUMBER: SQ4-PP3-150U-125D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1922.6	1922.6	1922.6	1922.6	1922.6
2.5°	1934.7	1918.9	1922.6	1919.7	1911.8
5°	1929.3	1911.2	1917.5	1910.8	1910.8
7.5°	1916.1	1896.4	1902.7	1895.9	1895.6
10°	1904.0	1884.2	1890.5	1883.8	1882.1
12.5°	1886.5	1866.7	1874.4	1866.3	1865.9
15°	1855.2	1837.0	1845.0	1838.2	1834.9
17.5°	1819.8	1800.0	1809.7	1800.2	1798.9
20°	1792.8	1773.0	1782.7	1769.2	1769.2
22.5°	1760.5	1740.7	1751.7	1734.2	1734.2
25°	1708.6	1688.8	1696.8	1681.6	1679.9
27.5°	1646.9	1627.4	1635.8	1618.6	1618.2
30°	1602.4	1584.3	1594.0	1575.4	1573.8
32.5°	1553.9	1537.1	1544.1	1525.5	1523.9
35°	1476.0	1461.2	1465.9	1449.0	1447.4
37.5°	1394.1	1379.0	1384.4	1369.9	1369.2
40°	1336.2	1326.3	1327.8	1315.9	1312.6
42.5°	1282.3	1271.1	1272.5	1260.7	1260.0
45°	1199.7	1191.5	1191.3	1179.5	1179.5
47.5°	1112.1	1105.8	1104.0	1094.2	1093.9
50°	1051.4	1046.5	1044.7	1036.2	1034.6
52.5°	988.1	985.8	980.0	972.9	972.6
55°	889.7	886.4	877.9	872.8	871.1
57.5°	782.8	776.2	766.7	759.3	760.6
60°	706.0	699.4	685.8	682.4	682.4
62.5°	631.9	624.0	610.3	605.6	608.3
65°	525.7	515.8	503.8	500.5	502.1
67.5°	429.3	420.4	407.4	407.4	406.1
70°	367.3	362.4	352.2	352.2	352.2
72.5°	312.1	309.7	302.3	302.3	300.9
75°	239.3	239.3	235.9	234.2	232.5
77.5°	179.3	179.9	178.3	176.5	173.6
80°	141.5	144.8	143.2	141.5	139.9
82.5°	106.5	109.8	109.5	106.5	106.2
85°	55.6	60.5	60.7	60.7	60.7
87.5°	15.2	21.3	24.2	24.4	25.6
90°	2.0	6.0	13.2	14.2	13.2
92.5°	28.9	105.1	207.4	90.0	65.2
95°	68.1	238.9	729.4	377.5	224.5
97.5°	109.3	274.0	1136.9	940.9	691.0
100°	140.2	288.2	1263.7	1317.9	1065.6
102.5°	168.6	307.9	1308.4	1603.8	1415.1
105°	220.4	340.6	1315.5	1940.5	1861.0
107.5°	268.4	378.0	1258.0	2150.6	2177.0
110°	305.8	405.1	1206.8	2207.0	2319.2



TEST NUMBER: P563834

CATALOG NUMBER: SQ4-PP3-150U-125D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	339.1	432.1	1159.7	2195.7	2384.2
115°	388.1	474.5	1091.0	2112.1	2384.2
117.5°	436.0	517.1	1045.7	1984.3	2292.8
120°	465.3	544.7	1018.9	1892.6	2207.5
122.5°	492.9	570.8	1002.6	1794.3	2111.6
125°	531.3	608.8	983.3	1659.4	1949.4
127.5°	566.6	642.7	972.0	1549.3	1804.4
130°	586.1	664.6	967.1	1481.3	1711.7
132.5°	606.5	684.1	962.2	1419.9	1632.1
135°	636.9	712.4	956.9	1339.9	1516.7
137.5°	667.6	738.9	952.5	1274.9	1418.9
140°	688.7	755.3	950.8	1233.1	1361.2
142.5°	709.1	771.6	947.6	1195.4	1307.6
145°	740.6	796.2	943.7	1146.9	1234.3
147.5°	769.2	818.5	939.3	1102.9	1170.1
150°	790.3	834.0	937.6	1079.0	1132.7
152.5°	809.8	848.0	936.8	1056.9	1101.0
155°	836.0	868.8	935.6	1028.8	1062.6
157.5°	863.3	886.1	935.8	1009.2	1031.5
160°	878.7	897.6	936.6	996.9	1012.8
162.5°	890.9	906.6	937.4	987.1	999.0
165°	910.2	919.1	939.7	976.3	981.3
167.5°	923.4	929.6	939.9	967.1	969.5
170°	931.5	934.5	940.7	963.0	963.0
172.5°	938.0	938.6	940.7	958.1	957.3
175°	944.7	943.8	940.7	952.8	950.8
177.5°	947.0	944.6	940.5	948.6	946.2
180°	943.7	943.7	943.7	943.7	943.7

(END OF REPORT)