

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562516

Luminaire Tested: **SQ4-PC3-025U-050D-840-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562516
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-025U-050D-840-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5928.4 lumens
Efficiency: N/A
Efficacy: 129.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 45.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562516
CATALOG NUMBER: SQ4-PC3-025U-050D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562516

CATALOG NUMBER: SQ4-PC3-025U-050D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	97	93	90	96	92	88	85	82	79	77	72	70	68	64	62	61	57
2	93	85	79	73	87	80	75	70	72	67	63	63	60	57	56	54	51	47
3	85	75	67	61	79	71	64	59	63	58	53	56	52	48	50	46	44	40
4	77	66	58	52	73	63	55	50	56	50	45	50	45	41	44	41	38	34
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	65	53	45	39	61	50	43	37	45	39	34	41	35	31	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23
8	56	44	36	30	53	41	34	29	38	31	27	34	29	25	30	26	23	21
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6720	6720	6720
5°	6771	6727	6702
10°	6754	6722	6703
15°	6719	6719	6712
20°	6674	6694	6694
25°	6611	6659	6639
30°	6531	6610	6581
35°	6433	6532	6486
40°	6327	6416	6351
45°	6212	6256	6159
50°	6050	6050	5953
55°	5857	5782	5695
60°	5574	5463	5376
65°	5153	5050	5006
70°	4512	4548	4529
75°	3631	4014	4039
80°	2580	3403	3440
85°	1572	2858	2858



TEST NUMBER: P562516

CATALOG NUMBER: SQ4-PC3-025U-050D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.9	2.3
10°-20°	395.6	6.7
20°-30°	599.1	10.1
30°-40°	718.3	12.1
40°-50°	732.4	12.4
50°-60°	639.3	10.8
60°-70°	457.7	7.7
70°-80°	235.7	4.0
80°-90°	61.2	1.0
90°-100°	146.7	2.5
100°-110°	385.7	6.5
110°-120°	400.0	6.7
120°-130°	320.8	5.4
130°-140°	251.7	4.2
140°-150°	193.2	3.3
150°-160°	139.2	2.3
160°-170°	85.1	1.4
170°-180°	28.8	0.5
0°-30°	1132.6	19.1
0°-40°	1850.8	31.2
0°-60°	3222.5	54.4
0°-90°	3977.2	67.1
90°-120°	932.4	15.7
90°-150°	1698.2	28.6
90°-180°	1951.0	32.9
0°-180°	5928.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1457	1457	1457	1457	1457	
5°	1462	1448	1453	1448	1447	139
15°	1407	1395	1407	1407	1405	397
25°	1299	1290	1308	1304	1304	598
35°	1142	1140	1160	1152	1152	714
45°	952	950	959	947	944	733
55°	728	719	719	708	708	649
65°	472	462	463	459	459	467
75°	204	213	225	227	227	220
85°	30	46	54	55	54	40
90°	2	6	15	8	8	3
95°	19	76	253	130	89	22
105°	70	105	426	647	604	74
115°	124	150	342	682	778	122
125°	172	192	311	525	620	152
135°	205	225	301	424	480	158
145°	237	252	297	362	390	149
155°	268	276	297	326	336	123
165°	290	293	297	309	313	82
175°	301	301	299	303	303	29
180°	301	301	301	301	301	

TEST NUMBER: P562516

CATALOG NUMBER: SQ4-PC3-025U-050D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1456.7	1456.7	1456.7	1456.7	1456.7
2.5°	1465.3	1452.6	1456.7	1453.3	1448.0
5°	1462.1	1447.6	1452.6	1448.5	1447.2
7.5°	1451.5	1437.0	1443.7	1441.0	1439.7
10°	1441.8	1427.3	1435.1	1432.4	1431.0
12.5°	1428.9	1415.4	1424.3	1421.6	1421.3
15°	1406.8	1394.9	1406.8	1406.7	1405.4
17.5°	1379.0	1368.2	1380.9	1381.7	1380.9
20°	1359.6	1347.7	1363.6	1362.3	1363.6
22.5°	1335.8	1326.1	1343.1	1339.6	1340.9
25°	1298.9	1289.6	1308.3	1304.3	1304.3
27.5°	1255.2	1248.6	1268.9	1264.6	1264.6
30°	1226.0	1219.4	1240.9	1235.5	1235.5
32.5°	1193.7	1189.2	1209.6	1203.1	1203.1
35°	1142.4	1139.8	1159.9	1151.8	1151.8
37.5°	1089.5	1087.2	1105.5	1095.7	1092.5
40°	1050.7	1049.4	1065.5	1054.7	1054.7
42.5°	1011.8	1010.5	1024.5	1011.6	1011.6
45°	952.2	949.6	959.0	946.8	944.1
47.5°	887.2	884.6	890.5	877.2	875.9
50°	843.0	840.3	843.0	830.8	829.5
52.5°	797.7	792.9	793.3	781.2	780.9
55°	728.3	719.1	718.9	708.1	708.1
57.5°	655.0	642.8	643.9	634.7	633.4
60°	604.2	591.1	592.1	584.0	582.7
62.5°	554.6	539.3	542.5	533.3	533.0
65°	472.1	461.5	462.6	458.6	458.6
67.5°	392.8	383.0	390.1	386.8	386.6
70°	334.5	327.9	337.2	337.2	335.8
72.5°	280.5	280.3	291.9	291.9	292.7
75°	203.7	212.9	225.2	226.6	226.6
77.5°	136.0	152.3	165.9	166.4	166.2
80°	97.1	115.6	128.1	130.8	129.5
82.5°	65.8	85.3	95.8	98.4	97.1
85°	29.7	45.5	54.0	55.3	54.0
87.5°	9.0	19.3	24.7	23.1	21.0
90°	1.9	5.7	15.4	7.7	7.7
92.5°	8.1	39.1	86.5	38.3	24.7
95°	19.3	75.9	252.8	130.3	88.8
97.5°	33.6	83.4	378.2	300.8	221.5
100°	44.4	89.7	416.8	422.4	328.1
102.5°	53.6	95.9	427.6	526.2	445.4
105°	69.5	105.3	426.5	647.4	604.0
107.5°	85.7	118.9	402.2	710.4	721.0
110°	96.5	126.7	382.1	726.6	771.9

TEST NUMBER: P562516

CATALOG NUMBER: SQ4-PC3-025U-050D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	107.3	136.0	363.6	716.4	785.8
115°	123.5	149.9	341.6	681.5	777.7
117.5°	139.3	163.5	326.5	633.1	739.9
120°	148.6	171.2	320.3	600.6	704.4
122.5°	157.9	180.5	315.7	568.1	670.4
125°	171.8	192.5	310.7	525.1	619.5
127.5°	182.9	204.1	306.5	490.4	570.1
130°	189.1	211.8	304.9	468.7	542.3
132.5°	195.3	217.9	303.4	450.0	516.0
135°	204.6	225.3	301.0	423.9	480.5
137.5°	214.2	234.6	300.7	404.4	450.8
140°	221.9	240.8	299.1	388.9	432.3
142.5°	228.1	245.5	299.1	377.9	415.3
145°	237.4	252.5	297.2	361.5	389.8
147.5°	246.6	261.3	297.2	347.9	371.3
150°	252.8	266.0	297.2	340.1	358.9
152.5°	259.0	269.2	297.2	333.8	348.1
155°	268.2	275.8	297.2	326.4	335.8
157.5°	275.2	282.4	297.2	319.7	326.5
160°	279.8	285.5	297.2	316.6	320.3
162.5°	284.5	288.6	297.2	313.5	317.3
165°	289.5	293.2	297.2	308.9	312.6
167.5°	294.1	296.0	299.1	306.9	308.4
170°	297.2	299.1	299.1	306.8	306.8
172.5°	298.7	299.1	299.1	305.3	303.8
175°	301.0	301.0	299.1	303.0	303.0
177.5°	301.0	301.0	299.5	302.6	301.0
180°	301.0	301.0	301.0	301.0	301.0

(END OF REPORT)