

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562588

Luminaire Tested: **SQ4-PC3-025U-125D-840-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562588  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-025U-125D-840-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11888.2 lumens  
Efficiency: N/A  
Efficacy: 117.0 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 101.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562588  
CATALOG NUMBER: SQ4-PC3-025U-125D-840-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P562588

CATALOG NUMBER: SQ4-PC3-025U-125D-840-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	115	115	115	115	111	111	111	111	102	102	102	94	94	94	87	87	87	84				
1	105	101	97	93	101	97	93	90	90	87	84	83	81	79	77	75	74	71				
2	96	88	82	76	92	85	79	74	79	74	70	73	69	66	68	65	62	59				
3	88	78	70	64	84	75	68	62	70	64	59	65	60	56	60	56	53	50				
4	80	69	60	54	77	66	59	53	62	55	50	58	52	48	54	49	46	43				
5	74	61	53	46	71	59	51	45	55	49	43	52	46	42	48	44	40	37				
6	68	55	47	40	65	53	45	40	50	43	38	47	41	36	44	39	35	33				
7	63	50	42	36	60	48	41	35	45	39	34	43	37	32	40	35	31	29				
8	59	46	37	32	56	44	37	31	42	35	30	39	33	29	37	32	28	26				
9	55	42	34	28	53	41	33	28	38	32	27	36	30	26	34	29	25	23				
10	51	38	31	26	49	37	30	25	35	29	24	33	28	24	31	26	23	21				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16794	16794	16794
5°	16920	16811	16748
10°	16879	16800	16753
15°	16790	16790	16774
20°	16680	16729	16729
25°	16522	16642	16591
30°	16321	16519	16447
35°	16078	16325	16211
40°	15813	16036	15873
45°	15525	15635	15393
50°	15119	15119	14877
55°	14639	14450	14232
60°	13932	13653	13435
65°	12878	12621	12510
70°	11274	11366	11320
75°	9072	10033	10094
80°	6448	8506	8597
85°	3927	7135	7135



TEST NUMBER: P562588

CATALOG NUMBER: SQ4-PC3-025U-125D-840-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	344.5	2.9
10°-20°	988.7	8.3
20°-30°	1497.2	12.6
30°-40°	1795.0	15.1
40°-50°	1830.3	15.4
50°-60°	1597.7	13.4
60°-70°	1143.8	9.6
70°-80°	589.1	5.0
80°-90°	150.6	1.3
90°-100°	146.7	1.2
100°-110°	385.7	3.2
110°-120°	400.0	3.4
120°-130°	320.8	2.7
130°-140°	251.7	2.1
140°-150°	193.2	1.6
150°-160°	139.2	1.2
160°-170°	85.1	0.7
170°-180°	28.8	0.2
0°-30°	2830.4	23.8
0°-40°	4625.4	38.9
0°-60°	8053.4	67.7
0°-90°	9937.0	83.6
90°-120°	932.4	7.8
90°-150°	1698.2	14.3
90°-180°	1951.0	16.4
0°-180°	11888.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3640	3640	3640	3640	3640	
5°	3654	3618	3630	3620	3617	347
15°	3516	3486	3516	3516	3512	991
25°	3246	3223	3270	3260	3260	1494
35°	2855	2848	2899	2879	2879	1786
45°	2380	2373	2397	2366	2360	1832
55°	1820	1797	1797	1770	1770	1623
65°	1180	1153	1156	1146	1146	1167
75°	509	532	563	566	566	550
85°	74	114	135	138	135	101
90°	2	6	15	8	8	5
95°	19	76	253	130	89	22
105°	70	105	426	647	604	74
115°	124	150	342	682	778	122
125°	172	192	311	525	620	152
135°	205	225	301	424	480	158
145°	237	252	297	362	390	149
155°	268	276	297	326	336	123
165°	290	293	297	309	313	82
175°	301	301	299	303	303	29
180°	301	301	301	301	301	

TEST NUMBER: P562588

CATALOG NUMBER: SQ4-PC3-025U-125D-840-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3640.4	3640.4	3640.4	3640.4	3640.4
2.5°	3662.0	3630.3	3640.4	3632.0	3618.8
5°	3653.9	3617.6	3630.3	3620.1	3616.8
7.5°	3627.6	3591.3	3608.0	3601.2	3597.9
10°	3603.3	3567.1	3586.5	3579.6	3576.4
12.5°	3571.0	3537.3	3559.5	3552.7	3552.1
15°	3515.7	3486.0	3515.7	3515.6	3512.3
17.5°	3446.2	3419.2	3451.0	3452.9	3451.0
20°	3397.7	3368.0	3407.8	3404.5	3407.8
22.5°	3338.4	3314.0	3356.6	3347.9	3351.2
25°	3246.0	3222.9	3269.6	3259.5	3259.5
27.5°	3136.8	3120.3	3171.2	3160.4	3160.4
30°	3064.0	3047.5	3101.1	3087.6	3087.6
32.5°	2983.1	2971.9	3022.9	3006.7	3006.7
35°	2855.0	2848.4	2898.8	2878.6	2878.6
37.5°	2722.9	2716.9	2762.7	2738.2	2730.3
40°	2625.8	2622.5	2662.9	2635.9	2635.9
42.5°	2528.7	2525.4	2560.4	2528.1	2528.1
45°	2379.7	2373.1	2396.6	2366.1	2359.5
47.5°	2217.3	2210.7	2225.4	2192.3	2189.0
50°	2106.7	2100.1	2106.7	2076.3	2073.0
52.5°	1993.5	1981.6	1982.7	1952.3	1951.7
55°	1820.2	1797.1	1796.6	1769.6	1769.6
57.5°	1636.8	1606.5	1609.2	1586.2	1582.9
60°	1510.1	1477.1	1479.8	1459.5	1456.2
62.5°	1386.0	1347.8	1355.7	1332.8	1332.1
65°	1179.8	1153.4	1156.2	1146.1	1146.1
67.5°	981.6	957.2	974.8	966.7	966.1
70°	835.9	819.5	842.7	842.6	839.3
72.5°	701.1	700.5	729.4	729.5	731.4
75°	509.0	532.1	562.9	566.3	566.3
77.5°	339.8	380.6	414.6	415.9	415.3
80°	242.7	288.8	320.2	326.9	323.6
82.5°	164.5	213.3	239.3	246.0	242.7
85°	74.2	113.7	134.8	138.1	134.8
87.5°	22.0	46.4	57.0	55.4	50.1
90°	1.9	5.7	15.4	7.7	7.7
92.5°	8.1	39.1	86.5	38.3	24.7
95°	19.3	75.9	252.8	130.3	88.8
97.5°	33.6	83.4	378.2	300.8	221.5
100°	44.4	89.7	416.8	422.4	328.1
102.5°	53.6	95.9	427.6	526.2	445.4
105°	69.5	105.3	426.5	647.4	604.0
107.5°	85.7	118.9	402.2	710.4	721.0
110°	96.5	126.7	382.1	726.6	771.9



TEST NUMBER: P562588

CATALOG NUMBER: SQ4-PC3-025U-125D-840-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	107.3	136.0	363.6	716.4	785.8
115°	123.5	149.9	341.6	681.5	777.7
117.5°	139.3	163.5	326.5	633.1	739.9
120°	148.6	171.2	320.3	600.6	704.4
122.5°	157.9	180.5	315.7	568.1	670.4
125°	171.8	192.5	310.7	525.1	619.5
127.5°	182.9	204.1	306.5	490.4	570.1
130°	189.1	211.8	304.9	468.7	542.3
132.5°	195.3	217.9	303.4	450.0	516.0
135°	204.6	225.3	301.0	423.9	480.5
137.5°	214.2	234.6	300.7	404.4	450.8
140°	221.9	240.8	299.1	388.9	432.3
142.5°	228.1	245.5	299.1	377.9	415.3
145°	237.4	252.5	297.2	361.5	389.8
147.5°	246.6	261.3	297.2	347.9	371.3
150°	252.8	266.0	297.2	340.1	358.9
152.5°	259.0	269.2	297.2	333.8	348.1
155°	268.2	275.8	297.2	326.4	335.8
157.5°	275.2	282.4	297.2	319.7	326.5
160°	279.8	285.5	297.2	316.6	320.3
162.5°	284.5	288.6	297.2	313.5	317.3
165°	289.5	293.2	297.2	308.9	312.6
167.5°	294.1	296.0	299.1	306.9	308.4
170°	297.2	299.1	299.1	306.8	306.8
172.5°	298.7	299.1	299.1	305.3	303.8
175°	301.0	301.0	299.1	303.0	303.0
177.5°	301.0	301.0	299.5	302.6	301.0
180°	301.0	301.0	301.0	301.0	301.0

(END OF REPORT)