

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563404

Luminaire Tested: **SQ4-PP3-075U-075D-840-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563404
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-075D-840-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11854.2 lumens
Efficiency: N/A
Efficacy: 130.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 91
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563404
CATALOG NUMBER: SQ4-PP3-075U-075D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563404

CATALOG NUMBER: SQ4-PP3-075U-075D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	82	76	71	82	76	70	66	64	60	57	53	51	48	43	42	40	35
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	26	22
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10461	10461	10461
5°	10538	10473	10437
10°	10520	10445	10399
15°	10450	10394	10336
20°	10381	10322	10244
25°	10258	10187	10086
30°	10068	10015	9888
35°	9805	9738	9614
40°	9491	9431	9323
45°	9232	9167	9076
50°	8901	8843	8758
55°	8440	8328	8264
60°	7683	7463	7426
65°	6769	6486	6465
70°	5844	5603	5603
75°	5030	4959	4889
80°	4434	4487	4383
85°	3472	3784	3784



TEST NUMBER: P563404

CATALOG NUMBER: SQ4-PP3-075U-075D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.4	1.8
10°-20°	612.3	5.2
20°-30°	917.1	7.7
30°-40°	1075.7	9.1
40°-50°	1079.1	9.1
50°-60°	920.5	7.8
60°-70°	600.4	5.1
70°-80°	301.2	2.5
80°-90°	85.7	0.7
90°-100°	437.9	3.7
100°-110°	1204.6	10.2
110°-120°	1243.4	10.5
120°-130°	996.2	8.4
130°-140°	782.5	6.6
140°-150°	599.6	5.1
150°-160°	431.1	3.6
160°-170°	263.6	2.2
170°-180°	88.9	0.7
0°-30°	1743.8	14.7
0°-40°	2819.5	23.8
0°-60°	4819.1	40.7
0°-90°	5806.4	49.0
90°-120°	2885.9	24.3
90°-150°	5264.2	44.4
90°-180°	6048.0	51.0
0°-180°	11854.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2268	2268	2268	2268	2268	
5°	2276	2254	2262	2254	2254	216
15°	2188	2167	2176	2168	2164	617
25°	2015	1992	2001	1983	1982	927
35°	1741	1724	1729	1709	1707	1088
45°	1415	1405	1405	1391	1391	1090
55°	1049	1046	1036	1030	1028	933
65°	620	608	594	590	592	619
75°	282	282	278	276	274	306
85°	66	71	72	72	72	77
90°	2	8	14	18	18	7
95°	65	239	774	331	211	69
105°	215	331	1327	2022	1886	227
115°	381	464	1065	2120	2406	376
125°	525	599	966	1634	1914	469
135°	634	704	938	1321	1495	489
145°	733	783	924	1126	1213	460
155°	830	857	918	1012	1041	381
165°	897	908	922	960	966	253
175°	928	930	924	936	934	88
180°	928	928	928	928	928	

TEST NUMBER: P563404

CATALOG NUMBER: SQ4-PP3-075U-075D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2267.7	2267.7	2267.7	2267.7	2267.7
2.5°	2282.0	2263.3	2267.7	2264.3	2255.0
5°	2275.6	2254.3	2261.7	2253.8	2253.8
7.5°	2260.1	2236.8	2244.2	2236.3	2235.9
10°	2245.8	2222.5	2229.9	2221.9	2220.0
12.5°	2225.2	2201.8	2210.8	2201.3	2200.9
15°	2188.2	2166.8	2176.3	2168.2	2164.3
17.5°	2146.5	2123.1	2134.5	2123.4	2121.8
20°	2114.7	2091.3	2102.7	2086.8	2086.8
22.5°	2076.5	2053.2	2066.2	2045.5	2045.5
25°	2015.3	1992.0	2001.4	1983.4	1981.5
27.5°	1942.5	1919.6	1929.4	1909.1	1908.8
30°	1890.1	1868.7	1880.1	1858.2	1856.3
32.5°	1832.8	1813.0	1821.3	1799.4	1797.5
35°	1741.0	1723.5	1729.1	1709.2	1707.2
37.5°	1644.4	1626.5	1632.9	1615.8	1615.0
40°	1576.1	1564.4	1566.1	1552.1	1548.2
42.5°	1512.5	1499.2	1500.9	1487.0	1486.2
45°	1415.1	1405.4	1405.1	1391.2	1391.2
47.5°	1311.7	1304.3	1302.2	1290.6	1290.3
50°	1240.2	1234.3	1232.2	1222.2	1220.3
52.5°	1165.4	1162.7	1155.9	1147.5	1147.2
55°	1049.4	1045.5	1035.5	1029.5	1027.5
57.5°	923.4	915.6	904.3	895.6	897.1
60°	832.7	825.0	808.9	804.9	804.9
62.5°	745.3	736.0	719.9	714.4	717.5
65°	620.1	608.4	594.2	590.3	592.3
67.5°	506.4	495.9	480.6	480.5	479.0
70°	433.3	427.4	415.4	415.4	415.4
72.5°	368.1	365.4	356.5	356.5	355.0
75°	282.2	282.2	278.2	276.2	274.3
77.5°	211.5	212.2	210.3	208.2	204.7
80°	166.9	170.8	168.9	166.9	165.0
82.5°	125.6	129.5	129.2	125.6	125.2
85°	65.6	71.4	71.5	71.5	71.5
87.5°	17.9	25.3	28.2	29.0	30.6
90°	2.0	7.8	13.8	17.8	17.8
92.5°	27.3	116.5	201.9	77.5	63.6
95°	65.2	239.0	774.3	331.1	211.3
97.5°	106.3	265.0	1181.6	910.4	642.3
100°	136.3	281.1	1309.6	1321.8	1078.5
102.5°	164.7	300.3	1342.7	1639.9	1416.6
105°	215.3	331.2	1327.3	2021.5	1886.3
107.5°	263.5	369.3	1251.9	2208.4	2248.6
110°	298.3	394.8	1195.0	2254.9	2394.0



TEST NUMBER: P563404

CATALOG NUMBER: SQ4-PP3-075U-075D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	329.9	423.3	1138.1	2224.9	2436.6
115°	381.2	464.3	1064.6	2120.0	2405.8
117.5°	430.2	506.7	1018.0	1972.7	2296.0
120°	460.2	533.6	997.5	1862.3	2196.4
122.5°	487.1	560.5	983.3	1765.5	2082.7
125°	525.4	598.8	965.9	1633.9	1914.0
127.5°	561.7	631.7	954.4	1524.1	1769.8
130°	580.7	652.2	948.1	1458.8	1682.9
132.5°	602.8	674.3	943.4	1401.5	1603.9
135°	634.0	703.6	938.2	1321.4	1495.2
137.5°	663.3	727.8	933.9	1256.7	1400.0
140°	685.4	745.3	932.3	1213.7	1343.1
142.5°	704.4	759.6	929.1	1175.4	1286.3
145°	732.8	783.0	924.4	1125.9	1212.8
147.5°	763.2	806.5	922.0	1082.0	1151.5
150°	782.2	820.8	920.4	1058.0	1112.0
152.5°	799.6	835.1	918.9	1037.2	1082.0
155°	829.6	856.6	918.5	1012.0	1040.9
157.5°	851.3	873.3	918.5	991.2	1011.3
160°	867.1	884.5	918.5	980.1	995.5
162.5°	879.8	894.0	920.1	970.5	982.9
165°	896.7	908.3	922.4	960.1	965.9
167.5°	908.6	917.5	924.4	951.3	952.8
170°	916.5	922.3	924.4	948.1	948.1
172.5°	922.8	925.5	924.4	943.3	941.8
175°	928.3	930.3	924.4	936.2	934.3
177.5°	929.9	929.9	923.6	933.0	929.9
180°	928.3	928.3	928.3	928.3	928.3

(END OF REPORT)