

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563500

Luminaire Tested: **SQ4-PP3-0U-075D-840-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563500
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-075D-840-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5804.0 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Direct

Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563500
CATALOG NUMBER: SQ4-PP3-0U-075D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563500

CATALOG NUMBER: SQ4-PP3-0U-075D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	105	101	97	107	103	99	96	98	95	93		95	92	90		91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77		84	79	76		81	77	74	72
3	92	81	74	67	89	80	73	67	77	71	66		74	69	64		72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56		66	60	56		64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49		60	53	48		58	52	48	46
6	72	59	50	44	70	58	49	43	56	49	43		54	48	43		53	47	42	40
7	66	53	45	39	65	52	44	39	51	44	38		49	43	38		48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34		45	39	34		44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31		42	35	31		41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28		39	33	28		38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10461	10461	10461
5°	10538	10473	10437
10°	10520	10445	10399
15°	10450	10394	10336
20°	10381	10322	10244
25°	10258	10187	10086
30°	10068	10015	9888
35°	9805	9738	9614
40°	9491	9431	9323
45°	9232	9167	9076
50°	8901	8843	8758
55°	8440	8328	8264
60°	7683	7463	7426
65°	6769	6486	6465
70°	5844	5603	5603
75°	5030	4959	4889
80°	4434	4487	4383
85°	3472	3784	3784



TEST NUMBER: P563500

CATALOG NUMBER: SQ4-PP3-0U-075D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.4	3.7
10°-20°	612.3	10.5
20°-30°	917.1	15.8
30°-40°	1075.7	18.5
40°-50°	1079.1	18.6
50°-60°	920.5	15.9
60°-70°	600.4	10.3
70°-80°	301.2	5.2
80°-90°	83.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1743.8	30.0
0°-40°	2819.5	48.6
0°-60°	4819.1	83.0
0°-90°	5804.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5804.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2268	2268	2268	2268	2268	
5°	2276	2254	2262	2254	2254	216
15°	2188	2167	2176	2168	2164	617
25°	2015	1992	2001	1983	1982	927
35°	1741	1724	1729	1709	1707	1088
45°	1415	1405	1405	1391	1391	1090
55°	1049	1046	1036	1030	1028	933
65°	620	608	594	590	592	619
75°	282	282	278	276	274	306
85°	66	71	72	72	72	79
90°	0	0	0	0	0	



TEST NUMBER: P563500

CATALOG NUMBER: SQ4-PP3-OU-075D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2267.7	2267.7	2267.7	2267.7	2267.7
2.5°	2282.0	2263.3	2267.7	2264.3	2255.0
5°	2275.6	2254.3	2261.7	2253.8	2253.8
7.5°	2260.1	2236.8	2244.2	2236.3	2235.9
10°	2245.8	2222.5	2229.9	2221.9	2220.0
12.5°	2225.2	2201.8	2210.8	2201.3	2200.9
15°	2188.2	2166.8	2176.3	2168.2	2164.3
17.5°	2146.5	2123.1	2134.5	2123.4	2121.8
20°	2114.7	2091.3	2102.7	2086.8	2086.8
22.5°	2076.5	2053.2	2066.2	2045.5	2045.5
25°	2015.3	1992.0	2001.4	1983.4	1981.5
27.5°	1942.5	1919.6	1929.4	1909.1	1908.8
30°	1890.1	1868.7	1880.1	1858.2	1856.3
32.5°	1832.8	1813.0	1821.3	1799.4	1797.5
35°	1741.0	1723.5	1729.1	1709.2	1707.2
37.5°	1644.4	1626.5	1632.9	1615.8	1615.0
40°	1576.1	1564.4	1566.1	1552.1	1548.2
42.5°	1512.5	1499.2	1500.9	1487.0	1486.2
45°	1415.1	1405.4	1405.1	1391.2	1391.2
47.5°	1311.7	1304.3	1302.2	1290.6	1290.3
50°	1240.2	1234.3	1232.2	1222.2	1220.3
52.5°	1165.4	1162.7	1155.9	1147.5	1147.2
55°	1049.4	1045.5	1035.5	1029.5	1027.5
57.5°	923.4	915.6	904.3	895.6	897.1
60°	832.7	825.0	808.9	804.9	804.9
62.5°	745.3	736.0	719.9	714.4	717.5
65°	620.1	608.4	594.2	590.3	592.3
67.5°	506.4	495.9	480.6	480.5	479.0
70°	433.3	427.4	415.4	415.4	415.4
72.5°	368.1	365.4	356.5	356.5	355.0
75°	282.2	282.2	278.2	276.2	274.3
77.5°	211.5	212.2	210.3	208.2	204.7
80°	166.9	170.8	168.9	166.9	165.0
82.5°	125.6	129.5	129.2	125.6	125.2
85°	65.6	71.4	71.5	71.5	71.5
87.5°	17.5	23.7	25.4	25.5	27.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)