

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P519771

Luminaire Tested: **SQ4-150U-0D-840-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519771  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-150U-0D-840-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 18253.7 lumens  
Efficiency: N/A  
Efficacy: 158.0 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Indirect

Input Watts (W): 115.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519771  
CATALOG NUMBER: SQ4-150U-0D-840-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P519771

CATALOG NUMBER: SQ4-150U-0D-840-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20								20				20				20
RC	80								50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	7205	77213	23765
100°	7449	67144	56619
105°	7858	46895	66341
110°	8248	32555	62562
115°	8472	23818	52050
120°	8585	18801	40733
125°	8546	15817	31357
130°	8413	13881	24569
135°	8311	12486	19789
140°	8295	11452	16395
145°	8341	10629	13902
150°	8420	9989	12067
155°	8511	9524	10817
160°	8627	9196	9944
165°	8694	8975	9373
170°	8727	8813	9022
175°	8750	8712	8806



TEST NUMBER: P519771

CATALOG NUMBER: SQ4-150U-0D-840-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	1315.8	7.2
100°-110°	3557.5	19.5
110°-120°	3740.2	20.5
120°-130°	3038.1	16.6
130°-140°	2383.1	13.1
140°-150°	1829.1	10.0
150°-160°	1315.4	7.2
160°-170°	803.6	4.4
170°-180°	270.9	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	8613.5	47.2
90°-150°	15863.8	86.9
90°-180°	18254.0	100.0
0°-180°	18253.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	6	18	40	43	40	
95°	204	717	2188	1132	674	226
105°	661	1022	3947	5822	5583	696
115°	1164	1423	3273	6336	7153	1150
125°	1594	1826	2950	4978	5848	1421
135°	1911	2137	2871	4020	4550	1477
145°	2222	2388	2831	3441	3703	1390
155°	2508	2606	2807	3086	3188	1157
165°	2731	2757	2819	2929	2944	769
175°	2834	2831	2822	2858	2852	269
180°	2831	2831	2831	2831	2831	



TEST NUMBER: P519771

CATALOG NUMBER: SQ4-150U-OD-840-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	6.1	18.0	39.6	42.6	39.6
92.5°	86.6	315.4	622.3	270.1	195.7
95°	204.2	716.7	2188.2	1132.4	673.5
97.5°	327.9	822.0	3410.8	2822.7	2073.0
100°	420.6	864.6	3791.2	3953.8	3196.9
102.5°	505.9	923.7	3925.3	4811.4	4245.3
105°	661.3	1021.9	3946.6	5821.5	5583.1
107.5°	805.2	1134.1	3774.1	6451.7	6530.9
110°	917.3	1215.3	3620.5	6620.9	6957.6
112.5°	1017.3	1296.2	3479.1	6587.1	7152.6
115°	1164.2	1423.4	3273.1	6336.2	7152.6
117.5°	1308.0	1551.2	3137.2	5952.8	6878.3
120°	1395.8	1634.2	3056.7	5677.7	6622.4
122.5°	1478.7	1712.3	3007.9	5382.9	6334.7
125°	1593.9	1826.3	2950.0	4978.2	5848.3
127.5°	1699.9	1928.2	2915.9	4647.9	5413.1
130°	1758.4	1993.9	2901.3	4443.8	5135.1
132.5°	1819.4	2052.4	2886.7	4259.7	4896.2
135°	1910.8	2137.3	2870.8	4019.6	4550.0
137.5°	2002.9	2216.8	2857.4	3824.8	4256.8
140°	2066.2	2265.9	2852.5	3699.3	4083.7
142.5°	2127.2	2314.9	2842.8	3586.1	3922.8
145°	2221.7	2388.5	2831.2	3440.6	3702.8
147.5°	2307.6	2455.4	2817.8	3308.7	3510.2
150°	2371.0	2502.1	2812.9	3237.1	3398.0
152.5°	2429.5	2543.9	2810.5	3170.6	3302.9
155°	2508.1	2606.5	2806.8	3086.4	3187.8
157.5°	2589.8	2658.4	2807.4	3027.7	3094.5
160°	2636.1	2692.8	2809.9	2990.7	3038.4
162.5°	2672.7	2719.8	2812.3	2961.2	2997.0
165°	2730.6	2757.4	2819.0	2929.0	2943.9
167.5°	2770.2	2788.7	2819.6	2901.4	2908.6
170°	2794.6	2803.6	2822.0	2889.1	2889.1
172.5°	2814.1	2815.9	2822.0	2874.4	2872.0
175°	2834.2	2831.3	2822.0	2858.5	2852.5
177.5°	2840.9	2833.8	2821.4	2845.7	2838.5
180°	2831.2	2831.2	2831.2	2831.2	2831.2

(END OF REPORT)