

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518933

Luminaire Tested: **SQ4-BB-150U-100D-840-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518933
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-150U-100D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12831.0 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 112.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518933
CATALOG NUMBER: SQ4-BB-150U-100D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P518933

CATALOG NUMBER: SQ4-BB-150U-100D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29				
1	94	90	87	84	84	81	78	76	64	62	61	48	47	46	34	33	33	26				
2	86	80	75	70	77	72	68	64	57	54	52	44	42	40	31	30	29	24				
3	80	71	65	60	71	64	59	55	52	48	45	40	37	35	29	27	26	21				
4	73	64	57	51	66	58	52	47	46	42	39	36	33	31	26	25	24	19				
5	68	57	50	45	61	52	46	41	42	38	34	33	30	28	24	23	21	18				
6	63	52	44	39	56	47	41	36	38	34	30	30	27	25	22	21	19	16				
7	58	47	40	35	52	43	37	32	35	30	27	28	25	22	21	19	18	15				
8	54	43	36	31	49	39	33	29	32	28	24	26	22	20	19	17	16	14				
9	50	39	32	28	45	36	30	26	30	25	22	24	21	18	18	16	15	13				
10	47	36	29	25	43	33	27	23	27	23	20	22	19	17	17	15	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19083	19083	19083
5°	18777	18730	18869
10°	17568	17803	18300
15°	15972	16479	17396
20°	14178	14915	16221
25°	12347	13325	14904
30°	10575	11737	13656
35°	8769	9963	12150
40°	6737	7967	10353
45°	4870	6032	8331
50°	3318	4495	6607
55°	2157	3251	5134
60°	1238	2289	3711
65°	327	1399	1879
70°	162	432	540
75°	71	36	0
80°	53	0	0
85°	0	0	0



TEST NUMBER: P518933

CATALOG NUMBER: SQ4-BB-150U-100D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.2	2.2
10°-20°	724.1	5.6
20°-30°	906.5	7.1
30°-40°	837.3	6.5
40°-50°	562.6	4.4
50°-60°	290.6	2.3
60°-70°	91.0	0.7
70°-80°	5.7	0.0
80°-90°	3.1	0.0
90°-100°	657.9	5.1
100°-110°	1778.8	13.9
110°-120°	1870.1	14.6
120°-130°	1519.0	11.8
130°-140°	1191.6	9.3
140°-150°	914.5	7.1
150°-160°	657.7	5.1
160°-170°	401.8	3.1
170°-180°	135.5	1.1
0°-30°	1913.8	14.9
0°-40°	2751.1	21.4
0°-60°	3604.3	28.1
0°-90°	3704.1	28.9
90°-120°	4306.8	33.6
90°-150°	7931.9	61.8
90°-180°	9127.0	71.1
0°-180°	12831.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3103	3103	3103	3103	3103	
5°	3041	3010	3034	3044	3056	282
15°	2508	2499	2588	2675	2732	699
25°	1819	1834	1963	2098	2196	834
35°	1168	1197	1327	1483	1618	723
45°	560	594	694	828	958	440
55°	201	235	303	389	479	188
65°	22	43	96	116	129	38
75°	3	3	2	0	0	4
85°	0	0	0	0	0	0
90°	3	9	20	21	20	7
95°	102	358	1094	566	337	107
105°	331	511	1973	2911	2792	348
115°	582	712	1636	3168	3576	575
125°	797	913	1475	2489	2924	710
135°	955	1069	1435	2010	2275	738
145°	1111	1194	1416	1720	1851	695
155°	1254	1303	1403	1543	1594	578
165°	1365	1379	1410	1464	1472	385
175°	1417	1416	1411	1429	1426	135
180°	1416	1416	1416	1416	1416	



TEST NUMBER: P518933

CATALOG NUMBER: SQ4-BB-150U-100D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3102.6	3102.6	3102.6	3102.6	3102.6
2.5°	3109.8	3080.5	3088.2	3088.0	3079.8
5°	3041.1	3010.3	3033.6	3044.4	3056.1
7.5°	2912.6	2888.5	2933.3	2966.9	2991.3
10°	2812.9	2792.4	2850.5	2896.3	2930.0
12.5°	2697.7	2681.8	2752.0	2814.8	2858.0
15°	2508.2	2499.4	2587.8	2674.6	2731.9
17.5°	2305.3	2305.0	2405.9	2513.7	2582.7
20°	2166.0	2170.4	2278.6	2397.5	2478.2
22.5°	2026.7	2037.0	2152.5	2276.5	2368.9
25°	1819.3	1833.9	1963.4	2097.7	2196.0
27.5°	1619.9	1641.3	1777.5	1917.1	2036.9
30°	1489.0	1514.0	1652.6	1799.5	1922.8
32.5°	1360.5	1390.2	1525.3	1680.7	1806.3
35°	1167.8	1197.2	1326.9	1483.1	1618.1
37.5°	968.8	997.5	1124.3	1278.0	1423.9
40°	839.1	871.4	992.2	1141.2	1289.4
42.5°	721.4	753.7	867.3	1013.7	1153.7
45°	559.9	593.6	693.5	828.5	957.7
47.5°	426.0	462.7	550.3	672.4	790.1
50°	346.7	383.4	469.8	577.5	690.5
52.5°	283.1	318.6	396.6	498.0	601.6
55°	201.1	234.9	303.2	389.3	478.8
57.5°	139.0	168.1	229.4	301.2	371.4
60°	100.6	128.5	186.1	244.5	301.7
62.5°	66.9	92.5	148.9	193.6	232.1
65°	22.5	43.1	96.1	115.9	129.1
67.5°	11.4	13.8	50.4	53.2	57.6
70°	9.0	9.0	24.0	25.6	30.0
72.5°	6.6	6.6	9.6	12.3	13.2
75°	3.0	3.0	1.5	0.0	0.0
77.5°	1.5	1.5	1.2	0.0	0.0
80°	1.5	1.5	0.0	0.0	0.0
82.5°	0.3	0.3	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.6	1.8	4.0	4.3	4.0
90°	3.0	9.0	19.8	21.3	19.8
92.5°	43.3	157.7	311.2	135.1	97.8
95°	102.1	358.4	1094.1	566.2	336.8
97.5°	164.0	411.0	1705.4	1411.3	1036.5
100°	210.3	432.3	1895.6	1976.9	1598.4
102.5°	252.9	461.8	1962.6	2405.7	2122.6
105°	330.7	510.9	1973.3	2910.8	2791.6
107.5°	402.6	567.1	1887.1	3225.8	3265.5
110°	458.7	607.7	1810.3	3310.4	3478.8



TEST NUMBER: P518933

CATALOG NUMBER: SQ4-BB-150U-100D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	508.6	648.1	1739.5	3293.5	3576.3
115°	582.1	711.7	1636.5	3168.1	3576.3
117.5°	654.0	775.6	1568.6	2976.4	3439.2
120°	697.9	817.1	1528.4	2838.9	3311.2
122.5°	739.3	856.1	1504.0	2691.5	3167.3
125°	796.9	913.2	1475.0	2489.1	2924.1
127.5°	850.0	964.1	1458.0	2323.9	2706.5
130°	879.2	996.9	1450.6	2221.9	2567.6
132.5°	909.7	1026.2	1443.3	2129.9	2448.1
135°	955.4	1068.6	1435.4	2009.8	2275.0
137.5°	1001.4	1108.4	1428.7	1912.4	2128.4
140°	1033.1	1132.9	1426.3	1849.7	2041.9
142.5°	1063.6	1157.5	1421.4	1793.1	1961.4
145°	1110.8	1194.3	1415.6	1720.3	1851.4
147.5°	1153.8	1227.7	1408.9	1654.4	1755.1
150°	1185.5	1251.1	1406.5	1618.6	1699.0
152.5°	1214.8	1272.0	1405.2	1585.3	1651.5
155°	1254.1	1303.2	1403.4	1543.2	1593.9
157.5°	1294.9	1329.2	1403.7	1513.9	1547.2
160°	1318.1	1346.4	1404.9	1495.4	1519.2
162.5°	1336.4	1359.9	1406.1	1480.6	1498.5
165°	1365.3	1378.7	1409.5	1464.5	1472.0
167.5°	1385.1	1394.4	1409.8	1450.7	1454.3
170°	1397.3	1401.8	1411.0	1444.5	1444.5
172.5°	1407.1	1408.0	1411.0	1437.2	1436.0
175°	1417.1	1415.6	1411.0	1429.2	1426.3
177.5°	1420.5	1416.9	1410.7	1422.8	1419.3
180°	1415.6	1415.6	1415.6	1415.6	1415.6

(END OF REPORT)