

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518595

Luminaire Tested: **SQ4-BB-0U-050D-840-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518595
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-0U-050D-840-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3798.1 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Direct

Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518595
CATALOG NUMBER: SQ4-BB-0U-050D-840-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P518595

CATALOG NUMBER: SQ4-BB-0U-050D-840-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	50	71	61	54	49	59	53	49	58	53	49	57	52	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9792	9792	9792
5°	9634	9611	9682
10°	9014	9135	9390
15°	8195	8455	8926
20°	7274	7653	8323
25°	6335	6837	7647
30°	5426	6022	7007
35°	4499	5112	6234
40°	3457	4088	5312
45°	2499	3095	4274
50°	1702	2307	3390
55°	1107	1669	2635
60°	635	1175	1904
65°	168	718	964
70°	83	221	277
75°	37	18	0
80°	27	0	0
85°	0	0	0



TEST NUMBER: P518595

CATALOG NUMBER: SQ4-BB-0U-050D-840-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	290.6	7.7
10°-20°	743.1	19.6
20°-30°	930.3	24.5
30°-40°	859.2	22.6
40°-50°	577.4	15.2
50°-60°	298.2	7.9
60°-70°	93.4	2.5
70°-80°	5.9	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1963.9	51.7
0°-40°	2823.1	74.3
0°-60°	3698.7	97.4
0°-90°	3798.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3798.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3184	3184	3184	3184	3184	
5°	3121	3089	3113	3124	3136	289
15°	2574	2565	2656	2745	2804	717
25°	1867	1882	2015	2153	2254	856
35°	1198	1228	1362	1522	1660	742
45°	575	609	712	850	983	451
55°	206	241	311	400	491	193
65°	23	44	99	119	132	39
75°	3	3	2	0	0	4
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P518595

CATALOG NUMBER: SQ4-BB-0U-050D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3183.9	3183.9	3183.9	3183.9	3183.9
2.5°	3191.3	3161.2	3169.1	3168.9	3160.5
5°	3120.8	3089.1	3113.1	3124.1	3136.2
7.5°	2988.9	2964.2	3010.2	3044.6	3069.6
10°	2886.6	2865.6	2925.1	2972.1	3006.8
12.5°	2768.3	2752.1	2824.1	2888.6	2932.8
15°	2573.9	2564.9	2655.6	2744.7	2803.5
17.5°	2365.7	2365.4	2468.9	2579.6	2650.3
20°	2222.7	2227.3	2338.3	2460.3	2543.1
22.5°	2079.8	2090.3	2208.9	2336.1	2431.0
25°	1866.9	1882.0	2014.8	2152.6	2253.5
27.5°	1662.4	1684.3	1824.1	1967.4	2090.3
30°	1528.0	1553.6	1695.9	1846.7	1973.2
32.5°	1396.2	1426.6	1565.3	1724.7	1853.7
35°	1198.4	1228.5	1361.7	1521.9	1660.5
37.5°	994.1	1023.7	1153.7	1311.5	1461.2
40°	861.1	894.2	1018.2	1171.1	1323.2
42.5°	740.3	773.4	890.0	1040.2	1183.9
45°	574.6	609.2	711.6	850.2	982.8
47.5°	437.2	474.8	564.7	690.1	810.8
50°	355.8	393.5	482.1	592.6	708.6
52.5°	290.5	327.0	407.0	511.0	617.4
55°	206.4	241.0	311.2	399.5	491.4
57.5°	142.6	172.5	235.4	309.1	381.1
60°	103.2	131.8	191.0	250.9	309.6
62.5°	68.7	94.9	152.8	198.7	238.1
65°	23.1	44.2	98.6	118.9	132.5
67.5°	11.7	14.1	51.8	54.6	59.1
70°	9.2	9.2	24.6	26.3	30.8
72.5°	6.8	6.8	9.9	12.7	13.6
75°	3.1	3.1	1.5	0.0	0.0
77.5°	1.5	1.5	1.2	0.0	0.0
80°	1.5	1.5	0.0	0.0	0.0
82.5°	0.3	0.3	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)