

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562755

Luminaire Tested: **SQ4-PC3-075U-100D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562755
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-100D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10376.8 lumens
Efficiency: N/A
Efficacy: 125.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562755
CATALOG NUMBER: SQ4-PC3-075U-100D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562755

CATALOG NUMBER: SQ4-PC3-075U-100D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56				
1	99	95	91	88	92	88	85	82	76	74	72	65	63	62	55	54	52	48				
2	90	83	77	72	84	77	72	67	67	63	59	57	54	52	48	46	44	40				
3	82	73	65	60	76	68	62	56	59	54	50	51	47	44	43	40	38	34				
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32	29				
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28	25				
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	28	25	22				
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19				
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13160	13160	13160
5°	13259	13173	13124
10°	13226	13165	13128
15°	13157	13157	13144
20°	13071	13109	13109
25°	12947	13041	13001
30°	12790	12944	12888
35°	12599	12793	12703
40°	12391	12566	12439
45°	12166	12252	12062
50°	11847	11847	11658
55°	11472	11323	11153
60°	10918	10699	10528
65°	10092	9889	9802
70°	8835	8907	8871
75°	7108	7861	7909
80°	5051	6666	6737
85°	3077	5589	5589



TEST NUMBER: P562755

CATALOG NUMBER: SQ4-PC3-075U-100D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.5	2.0
10°-20°	581.1	5.6
20°-30°	879.9	8.5
30°-40°	1054.9	10.2
40°-50°	1075.7	10.4
50°-60°	939.0	9.0
60°-70°	672.2	6.5
70°-80°	346.2	3.3
80°-90°	89.3	0.9
90°-100°	328.4	3.2
100°-110°	903.5	8.7
110°-120°	932.6	9.0
120°-130°	747.2	7.2
130°-140°	586.8	5.7
140°-150°	449.7	4.3
150°-160°	323.3	3.1
160°-170°	197.7	1.9
170°-180°	66.6	0.6
0°-30°	1663.5	16.0
0°-40°	2718.4	26.2
0°-60°	4733.1	45.6
0°-90°	5840.9	56.3
90°-120°	2164.4	20.9
90°-150°	3948.2	38.0
90°-180°	4536.0	43.7
0°-180°	10376.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2140	2140	2140	2140	2140	
5°	2147	2126	2134	2128	2126	204
15°	2066	2049	2066	2066	2064	583
25°	1908	1894	1922	1916	1916	878
35°	1678	1674	1704	1692	1692	1049
45°	1399	1395	1408	1391	1387	1077
55°	1070	1056	1056	1040	1040	954
65°	693	678	680	674	674	686
75°	299	313	331	333	333	323
85°	44	67	79	81	79	59
90°	2	6	10	13	13	5
95°	49	179	581	248	158	52
105°	162	248	996	1516	1415	170
115°	286	348	798	1590	1804	282
125°	394	449	724	1226	1436	352
135°	476	528	704	991	1121	367
145°	550	587	693	844	910	345
155°	622	642	689	759	781	286
165°	673	681	692	720	724	190
175°	696	698	693	702	701	66
180°	696	696	696	696	696	

TEST NUMBER: P562755

CATALOG NUMBER: SQ4-PC3-075U-100D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2139.5	2139.5	2139.5	2139.5	2139.5
2.5°	2152.2	2133.6	2139.5	2134.6	2126.8
5°	2147.4	2126.1	2133.6	2127.6	2125.6
7.5°	2132.0	2110.7	2120.5	2116.5	2114.5
10°	2117.7	2096.4	2107.8	2103.8	2101.9
12.5°	2098.7	2078.9	2092.0	2088.0	2087.6
15°	2066.2	2048.8	2066.2	2066.2	2064.2
17.5°	2025.4	2009.5	2028.2	2029.3	2028.2
20°	1996.9	1979.4	2002.8	2000.9	2002.8
22.5°	1962.0	1947.7	1972.7	1967.6	1969.5
25°	1907.7	1894.2	1921.6	1915.7	1915.7
27.5°	1843.5	1833.9	1863.7	1857.4	1857.4
30°	1800.8	1791.1	1822.5	1814.6	1814.6
32.5°	1753.2	1746.6	1776.6	1767.1	1767.1
35°	1677.9	1674.1	1703.7	1691.8	1691.8
37.5°	1600.3	1596.8	1623.6	1609.3	1604.6
40°	1543.2	1541.3	1565.0	1549.2	1549.2
42.5°	1486.2	1484.2	1504.8	1485.8	1485.8
45°	1398.6	1394.7	1408.5	1390.6	1386.7
47.5°	1303.1	1299.2	1307.9	1288.4	1286.5
50°	1238.1	1234.3	1238.1	1220.3	1218.3
52.5°	1171.6	1164.6	1165.2	1147.4	1147.0
55°	1069.8	1056.2	1055.9	1040.0	1040.0
57.5°	962.0	944.2	945.7	932.2	930.3
60°	887.5	868.1	869.7	857.7	855.8
62.5°	814.6	792.1	796.8	783.3	782.9
65°	693.4	677.9	679.5	673.5	673.5
67.5°	576.9	562.5	572.9	568.1	567.8
70°	491.3	481.6	495.3	495.2	493.3
72.5°	412.1	411.7	428.7	428.7	429.9
75°	299.1	312.7	330.8	332.8	332.8
77.5°	199.7	223.7	243.7	244.4	244.1
80°	142.6	169.8	188.2	192.1	190.2
82.5°	96.7	125.3	140.7	144.6	142.6
85°	43.6	66.8	79.2	81.2	79.2
87.5°	13.0	27.8	33.8	34.3	31.2
90°	1.5	5.8	10.4	13.3	13.3
92.5°	20.4	87.4	151.4	58.1	47.7
95°	48.9	179.3	580.7	248.3	158.5
97.5°	79.7	198.8	886.2	682.8	481.8
100°	102.2	210.9	982.2	991.4	808.8
102.5°	123.5	225.2	1007.1	1229.9	1062.5
105°	161.5	248.4	995.5	1516.1	1414.7
107.5°	197.6	277.0	938.9	1656.3	1686.4
110°	223.7	296.1	896.3	1691.2	1795.5



TEST NUMBER: P562755

CATALOG NUMBER: SQ4-PC3-075U-100D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	247.4	317.5	853.6	1668.7	1827.5
115°	285.9	348.2	798.5	1590.0	1804.4
117.5°	322.7	380.0	763.5	1479.5	1722.0
120°	345.2	400.2	748.1	1396.7	1647.3
122.5°	365.3	420.4	737.4	1324.2	1562.0
125°	394.1	449.1	724.4	1225.5	1435.5
127.5°	421.3	473.7	715.8	1143.1	1327.3
130°	435.5	489.1	711.1	1094.1	1262.2
132.5°	452.1	505.7	707.5	1051.1	1202.9
135°	475.5	527.7	703.7	991.1	1121.4
137.5°	497.5	545.8	700.4	942.5	1050.0
140°	514.0	559.0	699.2	910.3	1007.4
142.5°	528.3	569.7	696.9	881.5	964.7
145°	549.6	587.3	693.3	844.4	909.6
147.5°	572.4	604.9	691.5	811.5	863.7
150°	586.6	615.6	690.3	793.5	834.0
152.5°	599.7	626.3	689.2	777.9	811.5
155°	622.2	642.5	688.9	759.0	780.7
157.5°	638.5	655.0	688.9	743.4	758.5
160°	650.3	663.4	688.9	735.0	746.6
162.5°	659.8	670.5	690.0	727.9	737.1
165°	672.6	681.2	691.8	720.1	724.4
167.5°	681.4	688.1	693.3	713.5	714.6
170°	687.4	691.7	693.3	711.1	711.1
172.5°	692.1	694.1	693.3	707.5	706.3
175°	696.3	697.7	693.3	702.2	700.7
177.5°	697.4	697.4	692.7	699.8	697.4
180°	696.3	696.3	696.3	696.3	696.3

(END OF REPORT)