

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P520323

Luminaire Tested: **SQ4-F-125U-100D-840-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P520323
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G3-1910-536-19)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-F-125U-100D-840-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 27085.5 lumens
Efficiency: N/A
Efficacy: 132.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 205.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520323
CATALOG NUMBER: SQ4-F-125U-100D-840-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P520323

CATALOG NUMBER: SQ4-F-125U-100D-840-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43	37
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	38	36	31
3	80	71	63	57	73	65	59	53	54	49	45	44	41	38	35	32	30	26
4	73	62	54	48	67	57	50	45	48	43	39	39	35	32	31	28	26	22
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	33	38	33	29	32	28	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	21	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	22	26	22	19	21	18	16	13
9	49	37	30	24	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13453	13453	13453
5°	13514	13328	13430
10°	13445	13276	13380
15°	13364	13182	13287
20°	13226	13069	13177
25°	13082	12929	13030
30°	12922	12784	12848
35°	12760	12602	12670
40°	12548	12403	12415
45°	12327	12157	12118
50°	12009	11865	11837
55°	11655	11526	11446
60°	11302	11099	11062
65°	10750	10509	10421
70°	9989	9746	9557
75°	8918	8634	8456
80°	7339	7072	6753
85°	4344	4767	4873



TEST NUMBER: P520323

CATALOG NUMBER: SQ4-F-125U-100D-840-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	412.9	1.5
10°-20°	1175.7	4.3
20°-30°	1765.6	6.5
30°-40°	2107.1	7.8
40°-50°	2159.8	8.0
50°-60°	1923.3	7.1
60°-70°	1433.7	5.3
70°-80°	776.2	2.9
80°-90°	182.2	0.7
90°-100°	1097.8	4.1
100°-110°	2957.1	10.9
110°-120°	3103.4	11.5
120°-130°	2518.3	9.3
130°-140°	1975.0	7.3
140°-150°	1516.3	5.6
150°-160°	1090.2	4.0
160°-170°	666.1	2.5
170°-180°	224.6	0.8
0°-30°	3354.2	12.4
0°-40°	5461.4	20.2
0°-60°	9544.5	35.2
0°-90°	11936.7	44.1
90°-120°	7158.2	26.4
90°-150°	13167.9	48.6
90°-180°	15149.0	55.9
0°-180°	27085.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4374	4374	4374	4374	4374	
5°	4378	4369	4317	4356	4350	415
15°	4197	4183	4140	4173	4173	1182
25°	3855	3846	3810	3831	3840	1776
35°	3399	3384	3357	3363	3375	2122
45°	2834	2820	2795	2780	2786	2181
55°	2174	2177	2150	2129	2135	1946
65°	1477	1471	1444	1429	1432	1461
75°	750	742	727	712	712	799
85°	123	135	135	138	138	172
90°	6	18	36	39	39	15
95°	167	597	1800	920	637	175
105°	547	851	3270	4893	4592	575
115°	966	1182	2723	5262	5952	950
125°	1318	1514	2445	4133	4864	1177
135°	1587	1772	2376	3334	3776	1225
145°	1836	1979	2347	2851	3061	1151
155°	2084	2160	2326	2558	2640	959
165°	2260	2286	2335	2428	2439	637
175°	2350	2347	2338	2370	2365	223
180°	2347	2347	2347	2347	2347	



TEST NUMBER: P520323

CATALOG NUMBER: SQ4-F-125U-100D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4374.5	4374.5	4374.5	4374.5	4374.5
2.5°	4391.3	4381.9	4343.3	4374.4	4369.6
5°	4377.5	4368.6	4317.4	4356.3	4350.4
7.5°	4336.6	4327.8	4282.6	4318.5	4313.2
10°	4305.4	4296.6	4251.3	4287.3	4284.4
12.5°	4264.6	4255.8	4210.5	4246.5	4243.6
15°	4197.3	4182.7	4140.3	4173.3	4173.3
17.5°	4108.4	4097.3	4058.0	4085.7	4086.3
20°	4041.2	4032.4	3993.2	4023.2	4026.2
22.5°	3974.0	3965.2	3921.1	3948.8	3954.2
25°	3855.1	3846.3	3810.0	3831.2	3840.0
27.5°	3732.5	3719.6	3683.9	3702.7	3709.1
30°	3638.9	3633.0	3599.9	3609.1	3617.9
32.5°	3540.4	3534.6	3506.2	3510.8	3526.6
35°	3398.7	3384.1	3356.7	3363.0	3374.6
37.5°	3231.2	3224.1	3197.6	3194.2	3205.3
40°	3125.5	3113.8	3089.5	3083.6	3092.5
42.5°	3010.2	2998.4	2969.4	2963.6	2974.7
45°	2834.2	2819.6	2795.2	2780.3	2786.2
47.5°	2637.3	2637.3	2612.1	2594.9	2603.7
50°	2510.0	2510.0	2479.9	2465.2	2474.0
52.5°	2377.9	2380.3	2347.9	2340.0	2337.1
55°	2173.8	2176.6	2149.7	2128.8	2134.7
57.5°	1976.8	1970.3	1938.9	1925.2	1928.1
60°	1837.5	1828.7	1804.4	1783.8	1798.4
62.5°	1695.8	1691.6	1667.6	1644.1	1642.3
65°	1477.2	1471.3	1444.1	1429.2	1432.1
67.5°	1259.8	1252.8	1227.9	1206.5	1214.2
70°	1110.9	1110.9	1083.9	1071.7	1062.9
72.5°	974.0	962.2	942.2	925.2	918.7
75°	750.5	741.8	726.6	711.6	711.6
77.5°	546.4	538.8	529.0	518.7	515.8
80°	414.4	411.4	399.3	395.9	381.3
82.5°	291.8	291.2	284.1	276.2	275.6
85°	123.1	134.9	135.1	138.1	138.1
87.5°	22.8	39.2	40.8	36.7	36.7
90°	6.0	17.7	35.9	38.9	38.9
92.5°	72.9	257.6	509.3	245.2	170.4
95°	167.4	597.1	1799.6	920.2	636.7
97.5°	267.2	683.5	2822.5	2358.0	1778.1
100°	343.8	717.9	3147.8	3293.5	2732.2
102.5°	417.9	766.3	3255.4	3994.0	3533.4
105°	547.0	851.0	3270.4	4892.7	4591.6
107.5°	669.0	940.2	3131.0	5354.5	5432.3
110°	750.3	1007.5	3004.3	5497.9	5781.4

TEST NUMBER: P520323

CATALOG NUMBER: SQ4-F-125U-100D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	836.4	1074.9	2882.3	5466.1	5932.0
115°	965.6	1181.9	2723.3	5262.0	5951.8
117.5°	1083.3	1286.2	2600.1	4936.1	5704.3
120°	1159.9	1355.7	2537.9	4702.2	5491.4
122.5°	1226.8	1420.3	2492.5	4463.0	5249.9
125°	1318.3	1514.1	2445.3	4133.0	4863.6
127.5°	1406.2	1599.1	2415.4	3841.8	4494.2
130°	1458.8	1651.7	2403.4	3674.9	4247.8
132.5°	1511.5	1702.0	2391.5	3528.0	4054.1
135°	1587.3	1771.5	2376.5	3334.2	3775.6
137.5°	1659.7	1836.2	2368.7	3169.7	3532.2
140°	1709.9	1879.4	2361.6	3068.5	3395.9
142.5°	1762.5	1920.3	2356.8	2974.1	3250.0
145°	1835.5	1978.7	2346.6	2850.6	3061.1
147.5°	1914.3	2038.9	2336.4	2746.8	2912.2
150°	1967.0	2075.2	2331.7	2681.6	2818.9
152.5°	2014.8	2108.9	2329.3	2628.4	2740.0
155°	2083.5	2159.5	2325.7	2557.8	2639.6
157.5°	2143.9	2203.0	2326.3	2508.1	2563.1
160°	2182.2	2232.0	2328.7	2479.1	2520.0
162.5°	2215.7	2256.0	2331.1	2454.9	2484.2
165°	2260.0	2286.2	2334.7	2427.6	2439.3
167.5°	2295.8	2311.0	2337.6	2406.5	2411.2
170°	2319.8	2325.6	2337.6	2394.5	2394.5
172.5°	2334.1	2335.3	2340.1	2382.5	2382.5
175°	2349.7	2346.7	2337.6	2370.4	2364.6
177.5°	2356.2	2351.5	2339.5	2358.4	2353.8
180°	2346.6	2346.6	2346.6	2346.6	2346.6

(END OF REPORT)