

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P562923

Luminaire Tested: **SQ4-PC3-100U-075D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562923  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-100U-075D-840-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10481.6 lumens  
Efficiency: N/A  
Efficacy: 134.4 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 78  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562923  
CATALOG NUMBER: SQ4-PC3-100U-075D-840-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P562923

CATALOG NUMBER: SQ4-PC3-100U-075D-840-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	87	84	81	78	69	67	65	56	54	53	43	42	41	35
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	31	30	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	22
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22	19
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	22	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	13
9	49	37	29	24	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9904	9904	9904
5°	9979	9914	9878
10°	9954	9908	9880
15°	9903	9903	9893
20°	9837	9866	9866
25°	9744	9815	9784
30°	9626	9742	9700
35°	9482	9628	9561
40°	9325	9457	9361
45°	9156	9221	9079
50°	8916	8916	8774
55°	8634	8522	8393
60°	8216	8051	7923
65°	7594	7443	7377
70°	6650	6703	6676
75°	5349	5917	5953
80°	3801	5016	5069
85°	2315	4206	4206



TEST NUMBER: P562923

CATALOG NUMBER: SQ4-PC3-100U-075D-840-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.4	1.5
10°-20°	437.3	4.2
20°-30°	662.3	6.3
30°-40°	794.0	7.6
40°-50°	809.6	7.7
50°-60°	706.7	6.7
60°-70°	505.9	4.8
70°-80°	260.6	2.5
80°-90°	67.8	0.6
90°-100°	438.6	4.2
100°-110°	1210.8	11.6
110°-120°	1248.7	11.9
120°-130°	1003.5	9.6
130°-140°	788.6	7.5
140°-150°	604.8	5.8
150°-160°	434.7	4.1
160°-170°	265.8	2.5
170°-180°	89.6	0.9
0°-30°	1252.0	11.9
0°-40°	2045.9	19.5
0°-60°	3562.2	34.0
0°-90°	4396.5	41.9
90°-120°	2898.1	27.6
90°-150°	5295.0	50.5
90°-180°	6085.0	58.1
0°-180°	10481.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1616	1600	1606	1601	1600	153
15°	1555	1542	1555	1555	1554	438
25°	1436	1426	1446	1442	1442	661
35°	1263	1260	1282	1273	1273	790
45°	1053	1050	1060	1047	1044	810
55°	805	795	795	783	783	718
65°	522	510	511	507	507	516
75°	225	235	249	250	250	243
85°	33	50	60	61	60	45
90°	3	6	12	14	15	6
95°	64	237	796	327	213	69
105°	216	333	1332	2034	1915	230
115°	387	467	1073	2124	2416	380
125°	530	604	972	1646	1932	472
135°	638	707	946	1333	1503	494
145°	740	792	934	1135	1221	463
155°	835	862	926	1018	1050	385
165°	904	915	930	967	974	255
175°	936	938	932	946	942	89
180°	936	936	936	936	936	

TEST NUMBER: P562923

CATALOG NUMBER: SQ4-PC3-100U-075D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1619.8	1605.8	1610.2	1606.5	1600.7
5°	1616.2	1600.2	1605.7	1601.2	1599.8
7.5°	1604.6	1588.5	1595.9	1592.9	1591.4
10°	1593.8	1577.8	1586.4	1583.4	1581.9
12.5°	1579.5	1564.6	1574.4	1571.5	1571.2
15°	1555.1	1541.9	1555.1	1555.0	1553.6
17.5°	1524.3	1512.4	1526.4	1527.3	1526.4
20°	1502.9	1489.8	1507.3	1505.9	1507.3
22.5°	1476.6	1465.8	1484.7	1480.8	1482.3
25°	1435.8	1425.6	1446.2	1441.7	1441.7
27.5°	1387.5	1380.2	1402.7	1397.9	1397.9
30°	1355.3	1348.0	1371.7	1365.7	1365.7
32.5°	1319.5	1314.5	1337.1	1329.9	1329.9
35°	1262.8	1259.9	1282.2	1273.3	1273.3
37.5°	1204.4	1201.8	1222.0	1211.2	1207.7
40°	1161.4	1160.0	1177.8	1165.9	1165.9
42.5°	1118.5	1117.1	1132.5	1118.2	1118.2
45°	1052.6	1049.7	1060.1	1046.6	1043.7
47.5°	980.7	977.8	984.3	969.7	968.2
50°	931.8	928.9	931.8	918.4	916.9
52.5°	881.7	876.5	877.0	863.5	863.3
55°	805.1	794.9	794.7	782.7	782.7
57.5°	724.0	710.6	711.8	701.6	700.1
60°	667.9	653.4	654.5	645.5	644.1
62.5°	613.1	596.2	599.7	589.5	589.2
65°	521.8	510.2	511.4	506.9	506.9
67.5°	434.2	423.4	431.2	427.6	427.3
70°	369.8	362.5	372.7	372.7	371.2
72.5°	310.1	309.8	322.6	322.7	323.5
75°	225.1	235.3	249.0	250.5	250.5
77.5°	150.3	168.4	183.4	184.0	183.7
80°	107.3	127.8	141.6	144.6	143.1
82.5°	72.8	94.3	105.9	108.8	107.3
85°	32.8	50.3	59.6	61.1	59.6
87.5°	10.1	21.2	26.3	26.5	24.5
90°	3.0	5.9	12.0	13.5	15.0
92.5°	27.0	112.0	200.2	73.1	56.9
95°	64.4	237.3	795.7	327.1	212.8
97.5°	106.7	265.8	1178.7	907.5	657.2
100°	137.9	282.9	1320.1	1329.5	1080.4
102.5°	167.8	302.3	1347.7	1642.6	1406.4
105°	215.8	333.0	1332.1	2033.7	1915.0
107.5°	266.7	371.0	1257.8	2222.3	2265.7
110°	302.7	396.5	1200.3	2262.9	2403.5



TEST NUMBER: P562923

CATALOG NUMBER: SQ4-PC3-100U-075D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	335.1	425.3	1146.3	2230.8	2438.3
115°	386.6	467.2	1072.9	2123.9	2415.5
117.5°	431.6	511.8	1024.6	1973.5	2305.2
120°	461.5	540.6	1005.5	1871.7	2205.7
122.5°	490.3	565.9	989.9	1776.6	2093.0
125°	530.5	603.7	972.5	1645.8	1931.5
127.5°	564.6	637.9	962.3	1535.2	1781.7
130°	587.4	660.7	957.5	1467.6	1691.8
132.5°	609.0	678.7	952.7	1410.8	1613.8
135°	638.3	707.2	945.5	1333.0	1502.9
137.5°	671.3	734.0	941.9	1267.7	1412.7
140°	689.3	750.8	939.5	1224.1	1351.6
142.5°	709.7	766.5	937.1	1185.4	1297.7
145°	740.2	791.5	933.5	1134.8	1221.2
147.5°	769.6	814.4	930.2	1092.1	1159.2
150°	791.2	827.8	929.0	1066.6	1120.8
152.5°	808.0	842.2	927.8	1044.8	1089.7
155°	834.6	862.5	926.0	1018.2	1050.4
157.5°	859.2	880.6	926.3	998.8	1020.7
160°	873.6	892.6	927.5	987.8	1004.0
162.5°	885.6	902.3	928.7	978.2	990.8
165°	903.6	915.3	930.5	966.7	974.0
167.5°	917.4	924.4	932.0	959.7	962.0
170°	924.5	930.4	932.0	956.0	956.0
172.5°	930.5	934.1	932.0	951.2	950.0
175°	936.5	938.0	932.0	945.5	942.5
177.5°	938.9	937.8	931.7	940.1	937.7
180°	936.5	936.5	936.5	936.5	936.5

(END OF REPORT)