

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562947

Luminaire Tested: **SQ4-PC3-100U-100D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562947
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-100D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11926.1 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 92.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562947
CATALOG NUMBER: SQ4-PC3-100U-100D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562947

CATALOG NUMBER: SQ4-PC3-100U-100D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41
2	89	81	75	70	82	75	70	66	64	60	56	53	50	48	43	41	39	35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33	29
4	74	63	55	49	68	59	52	46	50	45	40	42	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	38	32	27	33	28	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13160	13160	13160
5°	13259	13173	13124
10°	13226	13165	13128
15°	13157	13157	13144
20°	13071	13109	13109
25°	12947	13041	13001
30°	12790	12944	12888
35°	12599	12793	12703
40°	12391	12566	12439
45°	12166	12252	12062
50°	11847	11847	11658
55°	11472	11323	11153
60°	10918	10699	10528
65°	10092	9889	9802
70°	8835	8907	8871
75°	7108	7861	7909
80°	5051	6666	6737
85°	3077	5589	5589



TEST NUMBER: P562947

CATALOG NUMBER: SQ4-PC3-100U-100D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.5	1.7
10°-20°	581.1	4.9
20°-30°	879.9	7.4
30°-40°	1054.9	8.8
40°-50°	1075.7	9.0
50°-60°	939.0	7.9
60°-70°	672.2	5.6
70°-80°	346.2	2.9
80°-90°	89.5	0.8
90°-100°	438.6	3.7
100°-110°	1210.8	10.2
110°-120°	1248.7	10.5
120°-130°	1003.5	8.4
130°-140°	788.6	6.6
140°-150°	604.8	5.1
150°-160°	434.7	3.6
160°-170°	265.8	2.2
170°-180°	89.6	0.8
0°-30°	1663.5	13.9
0°-40°	2718.4	22.8
0°-60°	4733.1	39.7
0°-90°	5841.1	49.0
90°-120°	2898.1	24.3
90°-150°	5295.0	44.4
90°-180°	6085.0	51.0
0°-180°	11926.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2140	2140	2140	2140	2140	
5°	2147	2126	2134	2128	2126	204
15°	2066	2049	2066	2066	2064	583
25°	1908	1894	1922	1916	1916	878
35°	1678	1674	1704	1692	1692	1049
45°	1399	1395	1408	1391	1387	1077
55°	1070	1056	1056	1040	1040	954
65°	693	678	680	674	674	686
75°	299	313	331	333	333	323
85°	44	67	79	81	79	59
90°	3	6	12	14	15	6
95°	64	237	796	327	213	69
105°	216	333	1332	2034	1915	230
115°	387	467	1073	2124	2416	380
125°	530	604	972	1646	1932	472
135°	638	707	946	1333	1503	494
145°	740	792	934	1135	1221	463
155°	835	862	926	1018	1050	385
165°	904	915	930	967	974	255
175°	936	938	932	946	942	89
180°	936	936	936	936	936	



TEST NUMBER: P562947

CATALOG NUMBER: SQ4-PC3-100U-100D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2139.5	2139.5	2139.5	2139.5	2139.5
2.5°	2152.2	2133.6	2139.5	2134.6	2126.8
5°	2147.4	2126.1	2133.6	2127.6	2125.6
7.5°	2132.0	2110.7	2120.5	2116.5	2114.5
10°	2117.7	2096.4	2107.8	2103.8	2101.9
12.5°	2098.7	2078.9	2092.0	2088.0	2087.6
15°	2066.2	2048.8	2066.2	2066.2	2064.2
17.5°	2025.4	2009.5	2028.2	2029.3	2028.2
20°	1996.9	1979.4	2002.8	2000.9	2002.8
22.5°	1962.0	1947.7	1972.7	1967.6	1969.5
25°	1907.7	1894.2	1921.6	1915.7	1915.7
27.5°	1843.5	1833.9	1863.7	1857.4	1857.4
30°	1800.8	1791.1	1822.5	1814.6	1814.6
32.5°	1753.2	1746.6	1776.6	1767.1	1767.1
35°	1677.9	1674.1	1703.7	1691.8	1691.8
37.5°	1600.3	1596.8	1623.6	1609.3	1604.6
40°	1543.2	1541.3	1565.0	1549.2	1549.2
42.5°	1486.2	1484.2	1504.8	1485.8	1485.8
45°	1398.6	1394.7	1408.5	1390.6	1386.7
47.5°	1303.1	1299.2	1307.9	1288.4	1286.5
50°	1238.1	1234.3	1238.1	1220.3	1218.3
52.5°	1171.6	1164.6	1165.2	1147.4	1147.0
55°	1069.8	1056.2	1055.9	1040.0	1040.0
57.5°	962.0	944.2	945.7	932.2	930.3
60°	887.5	868.1	869.7	857.7	855.8
62.5°	814.6	792.1	796.8	783.3	782.9
65°	693.4	677.9	679.5	673.5	673.5
67.5°	576.9	562.5	572.9	568.1	567.8
70°	491.3	481.6	495.3	495.2	493.3
72.5°	412.1	411.7	428.7	428.7	429.9
75°	299.1	312.7	330.8	332.8	332.8
77.5°	199.7	223.7	243.7	244.4	244.1
80°	142.6	169.8	188.2	192.1	190.2
82.5°	96.7	125.3	140.7	144.6	142.6
85°	43.6	66.8	79.2	81.2	79.2
87.5°	13.3	27.8	34.1	34.3	31.5
90°	3.0	5.9	12.0	13.5	15.0
92.5°	27.0	112.0	200.2	73.1	56.9
95°	64.4	237.3	795.7	327.1	212.8
97.5°	106.7	265.8	1178.7	907.5	657.2
100°	137.9	282.9	1320.1	1329.5	1080.4
102.5°	167.8	302.3	1347.7	1642.6	1406.4
105°	215.8	333.0	1332.1	2033.7	1915.0
107.5°	266.7	371.0	1257.8	2222.3	2265.7
110°	302.7	396.5	1200.3	2262.9	2403.5



TEST NUMBER: P562947

CATALOG NUMBER: SQ4-PC3-100U-100D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	335.1	425.3	1146.3	2230.8	2438.3
115°	386.6	467.2	1072.9	2123.9	2415.5
117.5°	431.6	511.8	1024.6	1973.5	2305.2
120°	461.5	540.6	1005.5	1871.7	2205.7
122.5°	490.3	565.9	989.9	1776.6	2093.0
125°	530.5	603.7	972.5	1645.8	1931.5
127.5°	564.6	637.9	962.3	1535.2	1781.7
130°	587.4	660.7	957.5	1467.6	1691.8
132.5°	609.0	678.7	952.7	1410.8	1613.8
135°	638.3	707.2	945.5	1333.0	1502.9
137.5°	671.3	734.0	941.9	1267.7	1412.7
140°	689.3	750.8	939.5	1224.1	1351.6
142.5°	709.7	766.5	937.1	1185.4	1297.7
145°	740.2	791.5	933.5	1134.8	1221.2
147.5°	769.6	814.4	930.2	1092.1	1159.2
150°	791.2	827.8	929.0	1066.6	1120.8
152.5°	808.0	842.2	927.8	1044.8	1089.7
155°	834.6	862.5	926.0	1018.2	1050.4
157.5°	859.2	880.6	926.3	998.8	1020.7
160°	873.6	892.6	927.5	987.8	1004.0
162.5°	885.6	902.3	928.7	978.2	990.8
165°	903.6	915.3	930.5	966.7	974.0
167.5°	917.4	924.4	932.0	959.7	962.0
170°	924.5	930.4	932.0	956.0	956.0
172.5°	930.5	934.1	932.0	951.2	950.0
175°	936.5	938.0	932.0	945.5	942.5
177.5°	938.9	937.8	931.7	940.1	937.7
180°	936.5	936.5	936.5	936.5	936.5

(END OF REPORT)