

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P562633

Luminaire Tested: **SQ4-PC3-050U-075D-840-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562633
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-075D-840-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14828.7 lumens
Efficiency: N/A
Efficacy: 140.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 105.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562633
CATALOG NUMBER: SQ4-PC3-050U-075D-840-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P562633

CATALOG NUMBER: SQ4-PC3-050U-075D-840-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	96	92	88	93	89	86	83	78	75	73	67	65	64	57	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	37	34	30
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16
10	48	36	28	23	45	34	27	22	30	24	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9904	9904	9904
5°	9979	9914	9878
10°	9954	9908	9880
15°	9902	9902	9893
20°	9837	9866	9866
25°	9744	9815	9785
30°	9625	9742	9700
35°	9482	9628	9561
40°	9326	9457	9361
45°	9156	9221	9078
50°	8917	8917	8774
55°	8634	8522	8394
60°	8217	8052	7923
65°	7595	7443	7377
70°	6649	6703	6676
75°	5351	5917	5953
80°	3802	5017	5071
85°	2315	4210	4210



TEST NUMBER: P562633

CATALOG NUMBER: SQ4-PC3-050U-075D-840-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	304.8	2.1
10°-20°	874.6	5.9
20°-30°	1324.5	8.9
30°-40°	1587.9	10.7
40°-50°	1619.1	10.9
50°-60°	1413.4	9.5
60°-70°	1011.9	6.8
70°-80°	521.2	3.5
80°-90°	135.4	0.9
90°-100°	443.8	3.0
100°-110°	1205.5	8.1
110°-120°	1239.5	8.4
120°-130°	991.0	6.7
130°-140°	778.7	5.3
140°-150°	597.1	4.0
150°-160°	429.4	2.9
160°-170°	262.6	1.8
170°-180°	88.5	0.6
0°-30°	2503.9	16.9
0°-40°	4091.8	27.6
0°-60°	7124.4	48.0
0°-90°	8792.8	59.3
90°-120°	2888.8	19.5
90°-150°	5255.5	35.4
90°-180°	6036.0	40.7
0°-180°	14828.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3220	3220	3220	3220	3220	
5°	3232	3200	3212	3202	3200	307
15°	3110	3084	3110	3110	3107	877
25°	2872	2851	2892	2884	2884	1322
35°	2526	2520	2564	2546	2546	1580
45°	2105	2099	2120	2093	2087	1621
55°	1610	1590	1589	1566	1566	1435
65°	1044	1020	1023	1014	1014	1032
75°	450	471	498	501	501	487
85°	66	101	119	122	119	89
90°	3	12	21	27	27	7
95°	65	243	773	336	226	69
105°	214	333	1326	2019	1899	227
115°	380	462	1061	2111	2405	375
125°	523	596	960	1618	1908	466
135°	630	700	933	1318	1486	487
145°	728	781	922	1120	1204	457
155°	823	852	916	1005	1034	380
165°	892	903	918	957	960	252
175°	924	927	922	933	930	88
180°	924	924	924	924	924	

TEST NUMBER: P562633

CATALOG NUMBER: SQ4-PC3-050U-075D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3220.4	3220.4	3220.4	3220.4	3220.4
2.5°	3239.5	3211.5	3220.4	3213.0	3201.4
5°	3232.4	3200.3	3211.5	3202.5	3199.6
7.5°	3209.1	3177.0	3191.8	3185.8	3182.9
10°	3187.6	3155.6	3172.7	3166.7	3163.8
12.5°	3159.0	3129.3	3148.9	3142.9	3142.3
15°	3110.1	3083.9	3110.1	3110.0	3107.1
17.5°	3048.7	3024.8	3052.9	3054.6	3052.9
20°	3005.7	2979.5	3014.7	3011.8	3014.7
22.5°	2953.3	2931.7	2969.4	2961.7	2964.6
25°	2871.6	2851.2	2892.4	2883.5	2883.5
27.5°	2774.9	2760.4	2805.4	2795.8	2795.8
30°	2710.5	2696.0	2743.3	2731.4	2731.4
32.5°	2639.0	2629.1	2674.2	2659.8	2659.8
35°	2525.7	2519.8	2564.4	2546.5	2546.5
37.5°	2408.8	2403.5	2444.0	2422.3	2415.3
40°	2322.9	2320.0	2355.7	2331.8	2331.8
42.5°	2237.0	2234.1	2265.0	2236.4	2236.4
45°	2105.2	2099.4	2120.1	2093.2	2087.3
47.5°	1961.5	1955.7	1968.6	1939.4	1936.4
50°	1863.7	1857.9	1863.7	1836.8	1833.9
52.5°	1763.5	1753.0	1753.9	1727.1	1726.5
55°	1610.2	1589.8	1589.3	1565.5	1565.5
57.5°	1448.0	1421.2	1423.6	1403.2	1400.3
60°	1335.9	1306.7	1309.1	1291.1	1288.2
62.5°	1226.2	1192.3	1199.3	1179.0	1178.4
65°	1043.7	1020.3	1022.8	1013.8	1013.8
67.5°	868.3	846.8	862.4	855.2	854.6
70°	739.5	724.9	745.5	745.4	742.5
72.5°	620.2	619.7	645.3	645.3	647.1
75°	450.3	470.7	498.0	501.0	501.0
77.5°	300.6	336.7	366.8	368.0	367.4
80°	214.7	255.5	283.3	289.2	286.3
82.5°	145.5	188.7	211.7	217.6	214.7
85°	65.6	100.6	119.3	122.2	119.3
87.5°	19.7	42.4	51.9	53.0	48.3
90°	3.0	11.7	20.8	26.8	26.8
92.5°	26.8	121.5	211.0	90.6	76.7
95°	65.4	242.7	772.8	336.3	225.9
97.5°	108.2	268.0	1184.8	921.8	647.4
100°	136.7	285.0	1310.9	1328.8	1073.1
102.5°	165.3	301.9	1344.1	1643.4	1417.9
105°	214.0	333.2	1325.7	2018.6	1899.4
107.5°	264.5	369.8	1249.0	2212.3	2245.4
110°	300.2	396.1	1192.0	2250.4	2392.8

TEST NUMBER: P562633

CATALOG NUMBER: SQ4-PC3-050U-075D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	331.1	422.4	1134.9	2218.8	2433.2
115°	380.5	461.9	1061.2	2111.2	2404.7
117.5°	426.8	504.7	1014.2	1958.6	2289.4
120°	457.8	533.3	992.8	1856.3	2184.8
122.5°	483.9	559.5	978.5	1753.8	2070.6
125°	523.2	595.8	960.1	1617.7	1908.3
127.5°	558.2	630.3	950.0	1514.5	1763.9
130°	579.6	649.4	945.2	1449.7	1673.5
132.5°	601.0	670.8	940.5	1394.4	1592.6
135°	630.2	699.9	933.4	1317.7	1486.2
137.5°	661.7	725.0	929.8	1249.9	1391.7
140°	680.7	741.7	927.4	1206.7	1334.6
142.5°	699.7	756.1	925.0	1173.0	1279.9
145°	728.3	780.6	921.5	1119.6	1203.8
147.5°	760.4	805.1	918.5	1077.5	1143.8
150°	781.8	819.5	918.5	1053.4	1105.8
152.5°	798.4	831.5	916.1	1031.8	1074.8
155°	823.4	852.4	915.5	1005.3	1034.4
157.5°	847.7	870.4	915.5	987.4	1009.4
160°	862.0	882.4	915.5	975.4	992.8
162.5°	876.3	892.0	917.9	965.7	978.5
165°	891.7	903.4	918.5	957.2	960.1
167.5°	907.8	913.6	921.5	947.1	949.4
170°	912.5	918.4	921.5	942.3	942.3
172.5°	917.3	920.8	921.5	937.5	937.5
175°	924.4	927.3	921.5	933.3	930.4
177.5°	926.8	926.8	919.7	929.1	924.4
180°	924.4	924.4	924.4	924.4	924.4

(END OF REPORT)